



## Special Purpose Contacts Selection Guide

Glenair Part Number	Part Description	Contact Size	Type	Product Page
859-012	Grommet Sealing Plugs (MS27488 Type)	0-23	Sealing Plug	D-3
809-001	Series 80 Mighty Mouse Pin Contact	23	Crimp Contact	D-4
809-002	Series 80 Mighty Mouse Socket Contact	23	Crimp Contact	D-5
830-004	Pneumatic Socket Contact for Series 79, Series 80 and D38999 Series II	12	Pneumatic	D-6
830-005	Pneumatic Socket Contact for Series 79, Series 80 and D38999 Series I, III, IV	12	Pneumatic	D-6
830-003	Pneumatic Pin Contact for Series 79, Series 80 and D38999 Series I, II, III, IV	12	Pneumatic	D-7
850-010	PCB Pin Contact to fit D38999/20 and /24	12-22	PCB Pin	D-8
850-011	PCB Socket Contact to fit D38999/20 and /24	12-22	PCB Socket	D-9
850-013	High Power Socket Contact	8	Power Socket	D-10
850-014	High Power Pin Contact	8	Power Pin	D-11
850-015	M39029/56 Type Socket Contact with Solder Cup	10-22	Solder Cup	D-12
850-016	Pin Contact with Solder Cup	10-22	Solder Cup	D-14
850-017	M39029/58 Type Pin Contact with Solder Cup	12-22	Solder Cup	D-16
850-018	M39029/56-348 Type Socket Contact	22	Crimp Contact	D-18
850-019	M39029/58-360 Type Pin Contact	22	Crimp Contact	D-19
850-020	M39029/57 Type Socket Contact	22	Crimp Contact	D-20
857-027	M39029/58 Type High Power Pin with PC Tails	8	PCB Power	D-21
857-028	M39029/56 Type High Power Socket with PC Tails	8	PCB Power	D-22
687-348	Wire to Contact Crimp Adapter	4-22	Crimp Adapter	D-23
850-023	M39029/87 Thermocouple Pin Contact	16-22	Thermocouple	D-24
850-024	M39029/88 Thermocouple Socket Contact; Series I, II, IV	16-22	Thermocouple	D-26
850-025	M39029/89 Thermocouple Socket Contact; Series II	16-22	Thermocouple	D-28