

Autoshrink™ D Cold-Action Shrink Boots and Tubing



777-023 Shielded, Straight Wall Tubing



Shielded, straight wall tubing provides a fast and durable repair solution for shielded wires. Integrated ArmorLite™ shielding restores EMI/EMP protection while repairing cable jacketing. Autoshrink™ D Tubing is RoHS compliant, halogen free, and highly resistant to sunlight and ozone damage. Boots are water-tight when installed with 779-005 adhesive. Service temperature range is -65°C to 225°C. Choose tube based on wire bundle diameter. 10 colors available.

How to Order					
Sample Part Number	777	-023	A	0250	-3
Product Series	777 = Autoshrink™				
Basic Part Number	-023 = Shielded tubing, Autoshrink™ D				
Braid Material/ Finish	A = ArmorLite™				
Size Code	See dimensions table				
Color Code	See color table				

NOTES

1. Adhesive 779-005 sold separately
2. Material:
 - Tubing: Duraelectric™ D, .062 (1.6) wall thickness
 - Braid: ArmorLite™

Color Code	
Code	Color
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Gray
9	White

Dimensions				
Size Code	Tube I.D. Recofvedd Shrinkage (Ref)	As Supplied Core I.D.(Ref)	Wire Bundle Range Reference	
			Min	Max
0250	.250	.80 (20.32)	.30 (8.89)	.65 (16.51)

