

M85528/1 Mounting Flange, Full Perimeter

M85528/1-10 A

Basic Part No. _____ A = Primer Coat
Shell Size _____ Required

Note: part superceded by M85049/94




TABLE I

| Shell Size | Thread UNJC-3B | A | | B | | C | | D | |
|---------------|-------------------|---------------|--------|---------------|--------|---------------|--------|---------------|-------|
| | | ±.003 (.1) | (mm) | ±.015 (.4) | (mm) | -.010 (.3) | (mm) | ±.030 (.8) | (mm) |
| 8 | 4-40 | .594 | (15.1) | .880 | (22.4) | .570 | (14.5) | .136 | (3.5) |
| 10 | 4-40 | .719 | (18.3) | 1.005 | (25.5) | .700 | (17.8) | .136 | (3.5) |
| 12 | 4-40 | .812 | (20.6) | 1.098 | (27.9) | .820 | (20.8) | .136 | (3.5) |
| 14 | 4-40 | .906 | (23.0) | 1.192 | (30.3) | .945 | (24.0) | .136 | (3.5) |
| 16 | 4-40 | .969 | (24.6) | 1.255 | (31.9) | 1.070 | (27.2) | .136 | (3.5) |
| 18 | 4-40 | 1.062 | (27.0) | 1.348 | (34.2) | 1.196 | (30.4) | .136 | (3.5) |
| 20 | 4-40 | 1.156 | (29.4) | 1.500 | (38.1) | 1.320 | (33.5) | .136 | (3.5) |
| 22 | 4-40 | 1.250 | (31.8) | 1.625 | (41.3) | 1.440 | (36.6) | .136 | (3.5) |
| 24 | 6-32 | 1.375 | (34.9) | 1.750 | (44.5) | 1.570 | (39.9) | .153 | (3.9) |
| 25 | 6-32 | 1.500 | (38.1) | 1.891 | (48.0) | 1.658 | (42.1) | .153 | (3.9) |

1. For complete dimensions see applicable Military Specification.
2. Metric dimensions (mm) are indicated in parentheses.