

LOCTITE

Henkel

Revision Number: 002.3

Issue date: 01/10/2010

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	CS-AB Copper Based Anti-Seize Lubricant	IDH number:	234292
Product type:	Lubricant	Item number:	51277
		Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: 860.571.5100		
One Henkel Way	Emergency telephone: 860.571.5100		
Rocky Hill, Connecticut 06067	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION**EMERGENCY OVERVIEW**

Physical state:	Paste	HEALTH:	*1
Color:	Copper	FLAMMABILITY:	1
Odor:	Mild	PHYSICAL HAZARD:	0
		Personal Protection:	See MSDS Section 8

CAUTION: MAY CAUSE EYE AND SKIN IRRITATION.

Relevant routes of exposure: Skin, Eyes**Potential Health Effects**

Inhalation: This product has low volatility and is not expected to cause respiratory tract irritation during normal conditions of use. Inhalation of copper fumes may result in metal fume fever. Symptoms include metallic taste, discoloration of skin or hair.

Skin contact: Prolonged or repeated contact may cause irritation.

Eye contact: Contact with eyes will cause irritation.

Ingestion: Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Principal hazard of ingestion is aspiration into the lungs and subsequent pneumonia.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Distillates (petroleum), hydrotreated heavy naphthenic	64742-52-5	20 - 60
Calcium stearate	1305-82-0	10 - 30
Mineral oil light naphthenic hydrotreated, <2% DMSO	64742-53-6	10 - 30
Copper	7440-50-8	10 - 30
Graphite	7782-42-5	5 - 15
Quartz (SiO ₂)	14808-60-7	0.1 - 1

4. FIRST AID MEASURES**Inhalation:** Move to fresh air. If symptoms persist, seek medical advice.