

# Glenair Environmental Shrink-Boot Adapters and Series 770 Boots

Easy-to-use, semi-rigid heat-shrinkable boots offer excellent electrical, mechanical and environmental protection. Made from flame-retardant elastomeric material, these adhesive-lined boots are resistant to high temperature and chemicals. Shrink boot material is flame retardant, and the "2" option can be specified for compliance to NES smoke and toxicity requirements.

Heating the boot causes the boot to shrink while an adhesive lining bonds the boot to the connector and cable and fills small gaps for a complete seal. Choose straight cable exit or right angle exit.

Heat-shrinkable boots are ideal for environmental protection of connector wire terminations in most harsh environments including tactical military equipment. The products also supply a modicum of strain-relief.

Glenair offers a full range of sizes and shapes to accommodate mil-standard circular and rectangular connectors and backshells. Boots are also available for Series 80 Mighty Mouse connectors and accessories.



This catalog contains a wide selection of connector accessory backshells that accommodate shrink boots. These products may now be ordered with Glenair Series 770 Shrink Boots:

A Complete Range of Glenair Composite Shrink Boot Adapters	Part Number	Page
Shrink Boot Adapter with Rotatable Coupling Nut ; Straight, 45° and 90°	310-045	A-2
Shrink Boot Adapter with Direct Coupling - Straight	310-017	A-4
Lamp Base EMI/RFI Environmental Adapter with Shrink Boot Porch and Direct Coupling - Straight	311-063	A-8
EMI/RFI Banding Backshell Shield Sock with Shrink Boot Porch and Self Locking Rotatable Coupling - Straight, 45° and Ultra Low Profile 90°. Uses Micro Band to Attach Shield	319-134	A-16
TEMI/RFI Shield Sock Strain Relief with Shrink Boot Porch and Self Locking Rotatable Coupling - Straight, 45° and 90°	319-136	A-18
Knit Braid Style EMI/RFI O-Ring Equipped Shield Termination Backshell with Shrink Boot Adapter and Rotatable Coupling	380-132	A-54
EMI/RFI Micro-Banding Backshell with Shrink Boot Groove and Self Locking Rotatable Coupling - Straight, 45° and Ultra Low Profile 90°	440-144	A-70
EMI/RFI Banding Backshell with Shrink Boot Groove and Self Locking Rotatable Coupling - Standard Profile Straight, 45° and 90°	447-325	A-72
EMI/RFI Micro-Banding Backshell with Shrink Boot Groove and Self Locking Rotatable Coupling - Standard Profile Straight, 45° and 90°	447-326	A-74
EMI/RFI Banding Backshell with Qwik-Ty Strain Relief and Shrink Boot Groove - Standard Profile Straight and 90°	447-327	A-76
Shrink Boot Conduit Fitting for Glenair Series 74 Helical Convuluted Tubing	712S269	C-22