



SERIES 185-002 EYE-BEAM® GMA  
MIL-DTL-83526 /20 & /21 compliant  
hermaphroditic expanded beam connectors



Cable harnesses and assemblies

**FA03937 GMA JAM NUT MOUNT OR WALL MOUNT RECEPTACLE CABLE HARNESS**

Reference Part Number*	
<b>Sample Part Number</b>	<b>FA03937</b> -80      -1      -3      -1      -4      -36-12
<b>Basic number</b>	GMA Fiber Optic cable
<b>GMA Connector Type</b>	70 = Wall mount receptacle (low profile) 80 = Jam nut mount receptacle (low profile)
<b>Fiber Type</b>	1 = SM 9/125    2 = MM 50/125    3 = MM 62.5/125
<b>Wavelength</b>	1 = MM 850 nm    2 = MM 1300 nm    3 = SM 1310 nm    4 = SM 1550 nm
<b>Pigtail Connector Type</b>	0 = ST M83522/16 style      4 = SC duplex      7 = LC duplex 1 = ST connector      5 = SMA connector (906)      8 = SMA connector (905) 2 = FC connector      6 = LC connector      9 = Customer specified 3 = SC connector
<b>Number of Fibers</b>	2 = 2 channel    4 = 4 channel
<b>Length (L1, L2)</b>	in inches

\* Use this part number for reference only. A unique Glenair part number will be assigned to your cable order

