



**M28876/5**  
**In-Line Receptacle**  
for use with MIL-PRF-29504/14 and /15 Termini



**MIL-PRF-28876 QPL in-line receptacle connector**

| Table I    |              |              |              |              |
|------------|--------------|--------------|--------------|--------------|
| Shell Size | ØA Max       | ØB Max       | ØC Max       | D            |
| 11         | 0.750 (19.1) | 0.960 (24.4) | 0.963 (24.5) | 0.768 (19.5) |
| 13         | 0.875 (22.2) | 1.085 (27.6) | 1.088 (27.6) | 0.893 (22.7) |
| 15         | 1.062 (27.0) | 1.255 (31.9) | 1.275 (32.4) | 1.080 (27.4) |
| 23         | 1.500 (38.1) | 1.763 (44.8) | 1.719 (43.7) | 1.518 (38.6) |

