





180-072 (07)

Fiber Optic Test Adapter, Receptacle
MIL-DTL-38999 Series I

MIL-DTL-38999 test adapter (receptacle)

How To Order



07 Receptacle Adapter
U.S. PATENT NO. 5,960,137

Material and Finish

- Shell: See Table II
- Insert: Hi-Grade Engineering Thermoplastic
- Alignment Sleeve: Zirconia Ceramic
- Retaining Clips: Copper Alloy
- Lock Cap, Lock Nut: Al Alloy/Anodize

Notes

For fiber optic test probe jumper, see Glenair drawing ABC54705

180-072 (07)
Fiber Optic Test Adapter, Receptacle
MIL-DTL-38999 Series I



Test Probes
and Kits

Table I: Shell Size and Insert Arrangements

Shell Size & Insert Arrangement	Shell Size Code Ref.	Ø B Max
11-2	B	.750 (19.1)
13-4	C	.875 (22.2)
15-5	D	1.000 (25.4)
15-97	D	1.000 (25.4)
17-8	E	1.187 (30.1)
19-11	F	1.250 (31.8)
21-16	G	1.375 (34.9)
23-21	H	1.500 (38.1)
23-99	H	1.500 (38.1)
25-20	J	1.625 (41.3)
25-29	J	1.625 (41.3)
25-37A	J	1.625 (41.3)
25-37B	J	1.625 (41.3)

Table II: Material and Finish

Code	Material	Finish
M	Aluminum Alloy	Electroless Nickel
NF		Cadmium/Olive Drab

