

Series 22  
Geo-Marine® Connectors



Quick Selection Guide



**High-Pressure Environmental/Hermetic Jam Nut Bulkhead Receptacle, Front Mount**  
220-00 (Standard) and 220-10 (Scoop-Proof)

B-2



**High-Pressure Environmental/Hermetic In-Line Receptacle Connector**  
220-01 (Standard) and 220-11 (Scoop-Proof)

B-4



**High-Pressure Environmental/Hermetic Square Flange Mount Receptacle Connector**  
220-02 (Standard) and 220-12 (Scoop-Proof)

B-6



**Hermetic Solder-Mount Bulkhead Receptacle Connector, Front Mount**  
220-03 (Standard) 220-13 (Scoop-Proof)

B-8



**High-Pressure Environmental/Hermetic Jam Nut Receptacle with Accessory Threads, Rear Mount**  
220-04 (Standard) and 220-14 (Scoop-Proof)

B-10



**High-Pressure Environmental Cable Plug**  
220-06 (Standard) and 220-16 (Scoop-Proof)

B-12



**High-Pressure Environmental/Hermetic Jam Nut Receptacle, Rear Box Mount**  
220-07 (Standard) and 220-17 (Scoop-Proof)

B-14



**High-Pressure Environmental Box-Mount Plug**  
220-09 (Standard) and 220-19 (Scoop-Proof)

B-16



**High-Pressure Environmental/Hermetic Jam Nut Mount Bulkhead Feed-Through**  
227-039 (Standard) and 227-040 (Scoop-Proof)

B-18

