
















# Geo-Marine® Special Purpose, Custom Application Connector Capabilities



## Quick Selection Guide

	<b>High-Pressure Environmental Plug with Quick Disconnect Lanyard</b> 227-015	D-2
	<b>High-Pressure Environmental Cable Plug with Wire Mesh Cable Grip</b> 227-158	D-3
	<b>High-Pressure Environmental In-Line Gender Changer</b> 227-152	D-5
	<b>High-Pressure Environmental Square Flange Wall-Mount Gender Changer</b> 940-016	D-6
	<b>High-Pressure Environmental Sav-Con® Connector Saver (Non Scoop-Proof)</b> 940-014	D-8
	<b>High-Pressure Environmental Jam Nut Mount Sav-Con® Connector Saver</b> 940-015	D-9
	<b>High-Pressure Environmental Sav-Con® Connector Saver (Scoop-Proof)</b> 940-025	D-10
	<b>Hermetic Receptacle With Triangular Flange Mount</b> 227-162H	D-12
	<b>High-Pressure Environmental Box Mount Plug with Circular Flange</b> 227-163	D-13
	<b>Stainless Steel Harsh Environment Connector Receptacle Assembly</b> 257-003	D-15
	<b>Stainless Steel Harsh Environment Receptacle Assembly with PCB Contacts</b> 257-005	D-18
	<b>Stainless Steel Harsh Environment Connector Receptacle Assembly</b> 257-007	D-19
	<b>Stainless Steel Harsh Environment Connector Receptacle Assembly</b> 257-012	D-22
	<b>Flange Mount and Weld Mount Stainless Steel Connector Receptacle Assemblies</b> 257-163 and 257-164	D-23
	<b>Stainless Steel Plug and Receptacle Assemblies</b> 257-165 and 257-166	D-25
	<b>10KPSI Series Underwater Interconnect Assemblies</b>	D-27