



Commital P/N	Shell size	Sleeve	A	B	C	F thread	L Max.
IT 3057-10A	18	IT 3420-10	33	16.0	10.2	1.0000 - 20UNEF	28.5
IT 3057-12A	20 - 22	IT 3420-12	35	19.0	10.2	1.1875 - 18UNEF	24.0
IT 3057-16A	24 - 28	IT 3420-16	43	23.8	10.5	1.4375 - 18UNEF	26.0
IT 3057-20A	32	IT 3420-20	51	31.7	12.5	1.7500 - 18UNS	28.0
IT 3057-24A	36	IT 3420-24	58	35.0	14.0	2.0000 - 18UNS	29.4
IT 3057-28A	40	IT 3420-28	65	41.2	14.0	2.2500 - 16UN	42.8

**Application Notes:**

1. General duty cable clamp suitable for jacketed or multi-conductor cable or wire bundles protected by shrink tubing.
2. Standard materials configuration consists of aluminum alloy with cadmium free conductive finish and black passivation.
3. Other types of front and rear connector accessories are available.  
See our website and/or contact the factory for complete information.