



Contact size	Rated current according to NFF61-030		Max. Contact resist.
	1 contact	A II contacts	
20	10 A	5 A	3.0 mΩ
16	15 A	8 A	2.5 mΩ
12	20 A	16 A	1.3 mΩ
8	25 A	25 A	0.9 mΩ



PL 607-XXP
PL 607-XXS
Insulating Grommet



Glenair Part Number		
Arrangement	Male (Pin)	Female (Socket)
20-4	PL 60720-4P	PL 60720-4S
20-7	PL 60720-7P	PL 60720-7S
22-23	PL 60722-23P	PL 60722-23S
18-19	PL 60718-19P	PL 60718-19S
20-15	PL 60720-15P	PL 60720-15S
22-14	PL 60722-14P	PL 60722-14S
24-10	PL 60724-10P	PL 60724-10S
24-A55	PL 60724-A55P	PL 60724-A55S
28-21	PL 60728-21P	PL 60728-21S
32-A13	PL 60732-A13P	PL 60732-A13S
36-10	PL 60736-10P	PL 60736-10S
36-A22	PL 60736-22P	PL 60736-22S
40-A35	PL 60740-A35P	PL 60740-A35S
40-A60	PL 60740-A60P	PL 60740-A60S
40-70	PL 60740-70P	PL 60740-70S