


SERIES 927-072  
**Hazardous Zone Plug**  
 for Ex cable gland




**927-072-026 PLUG WITH ENVIRONMENTAL CABLE ADAPTER FOR EX CABLE GLAND**

How To Order							
Sample Part Number	927-072	-026	-36-66	P1	F9	Y	/A0
Series	927-072						
Style	-026 = Ex Cable Gland						
Shell Size - Insert Arrangement	See pages 22- 31						
Contact Type and Plating	P = Pin Contact, S = Socket Contact 1 = Silver Plated, 2 = Gold Plated						
Shell Material and Finish	F9 = Aluminium Alloy, Anodize Hardcoat						
Alternate Key Position	X, Y, Z, W (See Table on page 32) Omit for normal position						
Cable Range	A0, B0, C0 (See Table next page) Ex Cable Gland not supplied						



Dimensions									
Shell Size	A2	B	C	Backshell Thread for Ex Gland	H	K1	K2	L2	M
10SL	105	55.6	46	M20x1.5 M16x1.5	41	24	24	91	25
14S	128	55.6	49	M20x1.5 M16x1.5	45	27	26	111	28
16	150	63.9	54	M20x1.5 M16x1.5	49	30	32	135	34
18	151	63.9	59	M25x1.5 M20x1.5 M16x1.5	52	34	36	135	38.2
28	180	63.9	72	M40x1.5 M32x1.5 M25x1.5 M20x1.5 M16x1.5	65	48	48	165	54
36	201	63.9	88	M50x1.5 M40x1.5 M32x1.5 M25x1.5 M20x1.5 M16x1.5	78	60	61	185	63.5

SERIES 927-072  
**Hazardous Zone Plug**  
 for Ex cable gland



Cable Range Dimensions for Ex Cable Gland			
Shell Size	Cable Type	Cable Range Designator	Backshell Thread for Ex Gland
36	Armored/ Unarmored cable	A0	M50x1.5
		B0	M40x1.5
		C0	M32x1.5
		D0	M25x1.5
		E0	M20x1.5
		F0	M16x1.5
28	Armored/ Unarmored cable	A0	M40x1.5
		B0	M32x1.5
		C0	M25x1.5
		D0	M20x1.5
		E0	M16x1.5
18	Armored/ Unarmored cable	A0	M25x1.5
		B0	M20x1.5
		C0	M16x1.5
16 14S 10SL	Armored/ Unarmored cable	A0	M20x1.5
B0		M16x1.5	