



X

Attachment Options

| Dia. Code | Ring I.D. | | Ring O.D. | | |
|--|---|-----------|-----------|-----------|-------|
| | In. | mm. | In. | mm. | |
| Small Ring for Attaching to a Panel with a Screw | ±.005 | ±0.13 | Max. | Max. | |
| | 01 | .126 | 3.20 | .31 | 7.9 |
| | 02 | .145 | 3.68 | .31 | 7.9 |
| | 04 | .188 | 4.78 | .31 | 7.9 |
| 06 | .197 | 5.00 | .31 | 7.9 | |
| Large Solid Ring for Attaching to a Jam Nut Receptacle | Dia. Code | Ring I.D. | | Ring O.D. | |
| | | In. | mm. | In. | mm. |
| | ± .010 | ±0.25 | ± .015 | ± 0.38 | |
| | 14 | .385 | 9.78 | .510 | 12.95 |
| | 15 | .445 | 11.30 | .565 | 14.35 |
| | 16 | .570 | 14.48 | .685 | 17.40 |
| | 17 | .635 | 16.13 | .760 | 19.30 |
| | 18 | .695 | 17.65 | .820 | 20.82 |
| | 19 | .885 | 22.48 | 1.010 | 25.65 |
| | 20 | 1.070 | 27.17 | 1.195 | 30.35 |
| 21 | 1.135 | 28.83 | 1.250 | 31.75 | |
| 22 | 1.210 | 30.73 | 1.312 | 33.32 | |
| Nylon Rope With Slip Knot (SK) for Attaching Covers to Cable | -65° to +100°C., black, very flexible, very good abrasion resistance, good resistance to fuels, .120" (3mm) diameter. Length includes .5" (13mm) diameter loop. | | | | |

Dimensions

| Size Code | Shell Size Reference | | Ø A Max. | | B Threads |
|-----------|----------------------|-------|----------|-------|-------------------|
| | 800/801 803/804 | 805 | In. | mm. | |
| 05 | 5 | N/A | .350 | 8.89 | .250-32 UNEF-2B |
| 06 | 6 | N/A | .415 | 10.54 | .3125-32 UNEF-2B |
| 11 | N/A | 8 | .465 | 11.81 | .3750-32 UNEF-2B |
| 07 | 7 | 9 | .530 | 13.46 | .4375-28 UNEF-2B |
| 08 | 8 | 10 | .595 | 14.35 | .5000-28 UNEF-2B |
| 09 | 9 | 11 | .650 | 16.51 | .5625-24 UNEF-2B |
| 10 | 10 | 12 | .715 | 18.16 | .6250-24 UNEF-2B |
| 12 | 11/12/13 | 13 | .785 | 19.94 | .6875-24 UNEF-2B |
| 13 | N/A | 15 | .830 | 21.08 | .7500-20 UNEF-2B |
| 14 | 14/15/16/17 | 18/19 | 1.020 | 25.91 | .9375-20 UNEF-2B |
| 16 | 19 | 21 | 1.155 | 29.34 | 1.0625-18 UNEF-2B |
| 17 | 21 | 23 | 1.270 | 32.26 | 1.1875-18 UNEF-2B |

Lanyard Options

| | |
|--|--|
| Nylon Rope (G) | -65° to +100°C., black, very flexible, very good abrasion resistance, good resistance to fuels, .120" (3mm) diameter |
| Polyurethane Coated Wire Rope (U) | Black polyurethane over stainless steel rope, -65° to +125°C., very flexible, excellent abrasion resistance, excellent resistance to fuels, .080" (2mm) diameter |
| Fluoropolymer Jacketed Wire Rope (H) | Translucent FEP jacket over stainless steel, -65° to +200°C., fair flexibility, good abrasion resistance, .100" diameter |
| Sash Chain (S) | Stainless steel, #8 chain, .240" (6mm) |

Dimensions in Inches (millimeters) are subject to change without notice.