



Receptacle Holder

Plug Holder

| Shell Size | | Recommended Torque (+/- 5 Inch-Pounds) | | A Dia. Max. | B Dia. Max. | C Dim. Max. |
|------------|-----------|---|-----------|----------------|----------------|----------------|
| Com'l | Mil. Ref. | Metal | Composite | | | |
| 09 | A | 60 | 35 | .577 (14.7) | .438 (11.1) | 1.031 (26.2) |
| 11 | B | 80 | 35 | .709 (18.0) | .566 (14.4) | 1.031 (26.2) |
| 13 | C | 110 | 40 | .829 (21.1) | .678 (17.2) | 1.031 (26.2) |
| 15 | D | 120 | 40 | .954 (24.2) | .803 (20.4) | 1.031 (26.2) |
| 17 | E | 120 | 40 | 1.107 (28.1) | .928 (23.6) | 1.031 (26.2) |
| 19 | F | 120 | 40 | 1.190 (30.2) | 1.033 (26.2) | 1.031 (26.2) |
| 21 | G | 140 | 80 | 1.315 (33.4) | 1.158 (29.4) | 1.031 (26.2) |
| 23 | H | 140 | 80 | 1.440 (36.6) | 1.283 (32.6) | 1.031 (26.2) |
| 25 | J | 140 | 80 | 1.565 (39.8) | 1.408 (35.8) | 1.031 (26.2) |

NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 09, 11 and 13; 3/8" - Shell sizes 15 and up.
4. Composite values apply when using Glenair 600-091 and 600-007 tools.