

## CONNETTORE UNIPOLARE C1

C1-06-3KV1000A / C1-02-3KV1000A

Connettore unipolare di potenza specifico per connessioni di testata.

CARATTERISTICHE TECNICHE:

- Corrente di lavoro a 20°C: 1000A max
- Tensione di lavoro: 3000 Vcc max
- Tensione di prova: 7000 Vca
- Peso del connettore volante: 6 Kg (stimato senza cavo)
- Temperatura di esercizio: -40°C +120°C
- Tenuta ambientale: IP67
- Resistenza al fuoco secondo NF F 16-102: Esigenza 3
- Categoria di sovratensione 0V4 secondo CEI EN 50124-I
- Grado di inquinamento PD4 secondo CEI EN 50124-I



**Connettore fisso**  
*Fixed connector*

**Connettore volante**  
*Free connector*

## C1 SINGLE POLE CONNECTOR

C1-06-3KV1000A / C1-02-3KV1000A

Single pole power connectors for wagon to wagon connection.

TECHNICAL CHARACTERISTICS:

- Working current at 20°C: 1000A max
- Working voltage: 3000 Vdc max
- Test voltage: 7000 Vac
- Plug connector weight: 6 Kg (without cable)
- Range of temperature: from -40°C to +120°C
- Protection rating: IP67
- Fire resistance according to NF F 16-102: Exigence 3.
- Overvoltage rate according to CEI EN 50124-I: 0V4
- Pollution rate according to CEI EN 50124-I: PD4