

The faster 4/8 pole industrial Ethernet interconnect system



How to Order Standard Insert Arrangement

How To Order	
Sample Part Number	ITH G 030 A 5C 32-Q4 S Y B0 N0 F6
Product Series	ITH = 5015 type reverse-bayonet connector with rigid insert
Plug Grounding Fingers	For 06 size 18 Plug connectors only Omit for standard
Style	030 = Rear Panel Mounting Receptacle 06 = Straight Plug
Class	A = non environmental R = environmental
Number of keys	5C = 5 keys
Shell Size - Insert Arrangements	See below
Contact Gender	P = Pin contacts (male) S = Socket contacts (female)
Alternate Insert Rotation	Omit for normal, consult factory for alternative rotation
Connector less contact	B0 = contact not supplied (order separately)
Accessory	N0 = without Backshell. Please consult the factory
Plating	F6 = Electrodeposition of black paint (cataphoresis), RoHS compliant F7 = Black Zinc Nickel, RoHS compliant

FRONT VIEW RECEPTACLE CONNECTOR



18-Q1



32-Q4



36-Q5



40-Q7