

Semper Tan Tubular Braid




TABLE I

Dash No.	Nominal I.D.	Wire Bundle Accomodation Range Ref.	
		Min.	Max.
004	.125 (3.2)	.090 (2.3)	.250 (6.4)
008	.250 (6.4)	.125 (3.2)	.375 (9.5)
012	.375 (9.5)	.312 (7.9)	.500 (12.7)
016	.500 (12.7)	.250 (6.4)	.750 (19.1)
024	.750 (19.1)	.500 (12.7)	1.250 (31.8)
040	1.250 (31.8)	.750 (19.1)	1.500 (38.1)

Series 77 Full Nelson Desert Tan Shrink Boots




Table 1: Boot Size Selection Guide

Boot Size	Adapter Diameter				Min. Cable Diameter	
	Inches		Millimeters		In.	mm.
	Min	Max	Min	Max		
02	.350	.625	8.89	15.88	.175	4.45
03	.450	.850	11.43	21.59	.225	5.72
04	.575	1.000	14.61	25.40	.250	6.35
05	.750	1.200	19.05	30.48	.300	7.62
06	.950	1.350	24.13	34.29	.375	9.53
07	1.150	1.600	29.21	40.64	.425	10.80
08	1.600	2.000	40.60	50.80	.650	16.50
09	1.780	2.550	45.20	64.80	.700	17.80