

852-119
852-120

- 12 GHz
- Size 8
- 75 Ohm
- Solder+Crimp Termination
- 12G-SDI
- Use with Belden 4855R 4K UHD Video Cable



Pin Contact

Socket Contact

75 ohm. 12 GHz. Size 8. 4K UHD video. Snap-in, rear release coax contacts fit Glenair Series 80 Mighty Mouse connectors, Glenair Series 23 SuperNine and MIL-DTL-38999 connectors with size 8 contact cavities. 75 ohm nominal impedance. These contacts are designed for use with Belden 4855R 12G-SDI SMPTE cable. DC - 12 GHz frequency range. Center contact is solder termination. Terminate shield with hex crimp. Supplied as unassembled kit with assembly instruction sheet.

CONNECTOR COMPATIBILITY

- MIL-DTL-38999
with size 8 contact cavities
- Series 233 SuperNine
with size 8 contact cavities
- Series 80 Mighty Mouse
with size 8 contact cavities

CONSTRUCTION

- Center contact, body, clamp nut, ferrule: copper alloy, gold over nickel plating
- Dielectrics: fluoropolymer
- Sealing boot: fluorosilicone rubber, glass-filled thermoplastic

SPECIFICATIONS

- Operating temperature of Belden cable: -35 °C to +75 °C
- Frequency range: DC - 12 GHz
- Return loss: SMPTE ST 2081-1:2015, ST2082-1:2015
- Impedance: 75 ohms
- Dielectric withstanding voltage: 500 Vac rms
- Insulation resistance: 5000 megohms
- Durability: 500 mating cycles


REMOVAL TOOL

859-022
(M81969/14-06)




PART NUMBER				
Coax Cable	Pin Part Number		Socket Part Number	
	With Sealing Boot	No Sealing Boot	With Sealing Boot	No Sealing Boot
4855R (Belden)	852-119-01F	852-119-01	852-120-01F	852-120-01


852-119-01 PIN CONTACT



852-120-01 SOCKET CONTACT



SEALING BOOT



Slide boot over cable, rubber end first, before terminating cable to contact. Install wired contact into connector, then slide boot into connector grommet to provide moisture seal.

Part Number	Cable Range
859-042-02	.130/.170 (3.3/4.3)

CRIMP TOOLS

Center contact is solder termination, no crimp tool is necessary. Terminate cable shield to contact with crimp tool and hex die set.



Tool	Part Number
Crimp Tool	809-129 (M22520/5-01)
Die Set, .178 Hex	859-051 (M22520/5-05)

COAX CONTACTS