



Glenair Series ITS

MIL-DTL-5015 Type Reverse Bayonet Connectors

Summary of Connector Styles and Backshells

A


Receptacles

Plugs

Selected Shell Styles

ITS 00

Front Panel Mount Square Flange Receptacle with Accessory Threads




ITS 02

Front Panel Mount Square Flange Receptacle. No Accessory Thread




ITS 01

In Line Cylindrical Receptacle with Accessory Thread




ITS 030

Rear Panel Mount Square Flange Receptacle with Accessory Thread




ITS 03

Rear Panel Mount Square Flange Receptacle. No Accessory Thread




ITS 05

Dummy Plug Stowage Receptacle




ITS 07

Rear Panel Mount Jam Nut Receptacle. No Accessory Thread




ITS 070

Rear Panel Mount Jam Nut Receptacle with Accessory Thread




ITS PP

Through Bulkhead Square Flange Receptacle.




26

Panel Mounting Plug




06

Standard Coupling Nut



06 GG


Rubber Covered Coupling Nut



A/R
Standard Backshell



PG/M
PG and Metric Thread Straight Adapter




N2N5
Long Backshell with Cable Clamp Type "C"



RS
Lipped Backshell



GR
Backshell with Rotating Coupling Nut Shrink Boot Adapter



PHM
Cable Clamp

PHM-EMI67
EMI/RFI Cable Clamp

Glenair Series ITS
MIL-DTL-5015 Type Reverse Bayonet Connectors
Summary of Connector Styles and Backshells



Backshells and Accessories

Adapters and Cable Clamps

