

REFERENCE INFORMATION

Materials, contact arrangements,
Performance specifications

pg. 61

**220-06 (STANDARD)
AND 220-16 (SCOOP-PROOF)**
High-Pressure Environmental Cable Plug



pg. 77

**220-01 (STANDARD) AND
220-11 (SCOOP-PROOF)**
In-Line Receptacle Connector



pg. 78

**220-00 (STANDARD) AND
220-10 (SCOOP-PROOF)**
Jam Nut Bulkhead Receptacle,
Front Mount



pg. 79

**220-02 (STANDARD) AND 220-12
(SCOOP-PROOF)**
Square Flange Mount Receptacle
Connector



pg. 80

**220-03 (STANDARD)
AND 220-13 (SCOOP-PROOF)**
Receptacle Connector, Front Mount



pg. 81

**220-04 (STANDARD)
AND 220-14 (SCOOP-PROOF)**
Jam Nut Receptacle with Accessory
Threads, Rear Mount



pg. 82

**220-07 (STANDARD)
AND 220-17 (SCOOP-PROOF)**
Jam Nut Receptacle, Rear Box Mount



pg. 83

**220-09 (STANDARD)
AND 220-19 (SCOOP-PROOF)**
High-Pressure Environmental
Box-Mount Plug



pg. 84

**227-039 (STANDARD)
AND 220-040 (SCOOP-PROOF)**
Jam Nut, Bulkhead Feed-through



pg. 85

290-011
Fixed SST molding adapter



pg. 87

290-012
Variable entry SST molding adapter



pg. 87

290-003
Straight, 45° or 90° Strain-relief backshell




pg. 89

290-004
Straight or 90° Environmental Strain
Relief backshell



pg. 89

297W-003
EMI/RFI Strain Relief Backshell



pg. 91

**ACCESSORIES AND CUSTOM
OVERMOLDED
CABLE ASSEMBLIES**



pg. 93