



## SAE-AS39029 Crimp Contact Selection Guide

A

Military Part Number	Glenair Part Number	Contact Size	Wire Accommodation	Pin / Socket	BIN Color Striping			Product Page
					1	2	3	
M39029/56-348	850-001-22-348	22	22-28 AWG	Socket	Orange	Yellow	Grey	A-6
M39029/56-351	850-001-20-351	20	20-24 AWG	Socket	Orange	Green	Brown	
M39029/56-352	850-001-16-352	16	16-20 AWG	Socket	Orange	Green	Red	
M39029/56-353	850-001-12-353	12	12-14 AWG	Socket	Orange	Green	Orange	
M39029/56-527	850-001-10-527	10	10 AWG	Socket	Green	Red	Violet	
M39029/57-354	850-003-22-354	22	22-28 AWG	Socket	Orange	Green	Yellow	A-8
M39029/57-357	850-003-20-357	20	20-24 AWG	Socket	Orange	Green	Violet	
M39029/57-358	850-003-16-358	16	16-20 AWG	Socket	Orange	Green	Grey	
M39029/57-359	850-003-12-359	12	12-14 AWG	Socket	Orange	Green	White	
M39029/58-360	850-002-22-360	22	22-28 AWG	Pin	Orange	Blue	Black	A-10
M39029/58-363	850-002-20-363	20	20-24 AWG	Pin	Orange	Blue	Orange	
M39029/58-364	850-002-16-364	16	16-20 AWG	Pin	Orange	Blue	Yellow	
M39029/58-365	850-002-12-365	12	12-14 AWG	Pin	Orange	Blue	Green	
M39029/58-528	850-002-10-528	10	10 AWG	Pin	Green	Red	Grey	
M39029/63-368	850-021-20-368	20	20-24 AWG	Socket	Orange	Blue	Grey	A-12
M39029/64-369	850-022-20-369	20	20-24 AWG	Pin	Orange	Blue	White	A-13

### BIN Color Coding

0 BLACK	1 BROWN	2 RED	3 ORANGE	4 YELLOW	5 GREEN	6 BLUE	7 VIOLET	8 GREY	9 WHITE
------------	------------	----------	-------------	-------------	------------	-----------	-------------	-----------	------------

# SAE-AS39029 Crimp Contact Selection Guide



AS39029

A

Military Part Number	Glenair Part Number	Contact Size	Wire Accommodation	Pin / Socket	BIN Color Striping			Product Page
M39029/83-450	850-004-20-450	20	22-26 AWG	Pin	Yellow	Green	Black	A-14
M39029/83-451	850-004-20-451	20	28-32 AWG	Pin	Yellow	Green	Brown	
M39029/83-508	850-004-20-508	20	20-24 AWG	Pin	Green	Black	Grey	
M39029/84-452	850-005-20-452	20	22-26 AWG	Socket	Yellow	Green	Red	A-16
M39029/84-453	850-005-20-453	20	28-32 AWG	Socket	Yellow	Green	Orange	
M39029/84-509	850-005-20-509	20	20-24 AWG	Socket	Green	Black	White	
M39029/106-614	850-006-22-614	22	22-28 AWG	Socket	Blue	Brown	Yellow	A-18
M39029/106-615	850-006-20-615	20	20-24 AWG	Socket	Blue	Brown	Green	
M39029/106-616	850-006-16-616	16	16-20 AWG	Socket	Blue	Brown	Blue	
M39029/106-617	850-006-12-617	12	12-14 AWG	Socket	Blue	Brown	Violet	
M39029/106-618	850-006-10-618	10	10 AWG	Socket	Blue	Brown	Grey	
M39029/107-620	850-007-22-620	22	22-28 AWG	Pin	Blue	Red	Black	A-20
M39029/107-621	850-007-20-621	20	20-24 AWG	Pin	Blue	Black	Brown	
M39029/107-622	850-007-16-622	16	16-20 AWG	Pin	Blue	Red	Red	
M39029/107-623	850-007-12-623	12	12-14 AWG	Pin	Blue	Red	Orange	
M39029/107-624	850-007-10-624	10	10 AWG	Pin	Blue	Red	Yellow	

BIN Color Coding									
0 BLACK	1 BROWN	2 RED	3 ORANGE	4 YELLOW	5 GREEN	6 BLUE	7 VIOLET	8 GREY	9 WHITE