


## Ordering Information: El Ochito<sup>®</sup> White Contacts, Type II



EL OCHITO<sup>®</sup> CONTACT ORDERING INFORMATION

### El Ochito<sup>®</sup> Contacts: How To Order



**Data Protocol:** Cat 6A up to 10G, Cat 8 up to 40G Ethernet  
El Ochito<sup>®</sup> White

Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito <sup>®</sup> Type II	
				Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
• EN3545 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-061-01 A185193-01P	858-062-01 A185193-01S
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-061-02 A185193-02P	858-062-02 A185193-02S
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-061-03 A185193-03P	858-062-03 A185193-03S
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-061-04 A185193-04P	858-062-04 A185193-04S
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-061-05 A185193-05P	858-062-05 A185193-05S
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-061-06 A185193-06P	858-062-06 A185193-06S
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-061-07 A185193-07P	858-062-07 A185193-07S
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-061-08 A185193-08P	858-062-08 A185193-08S
• SuperNine <sup>®</sup> (Series 23) • HiPer-D <sup>®</sup> (Series 28) Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-005-01 A185097-01	858-006-01 A185097-01
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-005-02 A185097-02	858-006-02 A185097-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-005-03 A185097-03	858-006-03 A185097-03
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-005-04 A185097-04	858-006-04 A185097-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-005-05 A185097-05	858-006-05 A185097-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-005-06 A185097-06	858-006-06 A185097-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-005-07 A185097-07	858-006-07 A185097-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-005-08 A185097-08	858-006-08 A185097-08

## Ordering Information: El Ochito<sup>®</sup> White Contacts, Type II

El Ochito <sup>®</sup> Contacts: How To Order							
 <b>Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet</b> El Ochito <sup>®</sup> White							
Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito <sup>®</sup> Type II	
				Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
• Series 792 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-043-01 AI85134-01	858-042-01 AI85134-02
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-043-02 AI85134-02	858-042-02 AI85134-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-043-03 AI85134-02	858-042-03 AI85134-02
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-043-04 AI85134-04	858-042-04 AI85134-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-043-05 AI85134-05	858-042-05 AI85134-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-051-06 AI85149-06	858-052-06 AI85149-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-043-07 AI85134-07	858-042-07 AI85134-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-043-08 AI85134-08	858-042-08 AI85134-08
• Series 806 • Series 816 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-051-01 AI85134-01	858-052-01 AI85134-02
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-051-02 AI85134-02	858-052-02 AI85134-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-051-03 AI85134-02	858-052-03 AI85134-02
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-051-04 AI85134-04	858-052-04 AI85134-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-051-05 AI85134-05	858-052-05 AI85134-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-051-06 AI85149-06	858-052-06 AI85149-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-051-07 AI85134-07	858-052-07 AI85134-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-051-08 AI85134-08	858-052-08 AI85134-08

EL OCHITO<sup>®</sup> CONTACT ORDERING INFORMATION