

Series 806 Mil-Aero Connectors

Series 806 Tools and Accessories Selection Guide



CRIMP TOOLS, POSITIONERS AND HEX DIES



809-015 Standard M22520/2-01 Crimper

Use with size #20HD and #22HD Series 806 contacts.

[Page 153](#)



Positioners

Bayonet-type positioners hold contacts at correct height for crimping with 809-015 (M22520/2-01) crimp tool.

[Page 153](#)



809-129 Standard M22520/5-01 Crimper

Use with size #8 twinax and quadrax Series 806 contacts.


[Page 154](#)



Hex-Dies for

Hex-die crimp affixes coax, twinax and quadrax connectors to end of cable.

[Page 154](#)



829-025 Standard M22520/23-01 Crimper

Use with size #8 Series 806 contacts.

[Page 155](#)



829-025 Standard M22520/23-02 Crimper

Indenter Die Assembly for Series 806 contacts.

[Page 155](#)




Locator

Aluminum locator holds contact at correct depth for crimping.

[Page 155](#)

INSERTION / EXTRACTION TOOLS, GROMMET SEALING PLUGS AND DUMMY CONTACT SEALING PLUGS




809-015

Insertion/Extraction tools

Use with size 20HD, 22HD, and 16 Series 806 contacts.


[Page 156](#)



Insertion/Extraction tools

For size 12 power and coax,


[Page 157](#)



Termination Instructions

For use with #22HD contacts used in Series 806 connectors

[Page 158](#)



Grommet Sealing Plug and Dummy Contact Sealing Plugs


[Page 159](#)

Series 806 Mil-Aero Connectors

Series 806 Tools and Accessories Selection Guide



CONTACT TESTER



809-456

Contact Retention Tester for Series 806

Offers rapid termination of cable shield to band platform

[Page 157](#)

SHIELD TERMINATION




601-108

Nano Band Installation Tool

Offers rapid termination of cable shield to band platform

[Page 159](#)

HOLDING TOOLS



600-221

Connector Holding Tool

Assist in installation of backshell by holding connector in place

[Page 160](#)

SPANNER WRENCH




Jam-Nut Wrench

For use with low-profile jam-nuts (809-044)

[Page 163](#)

SQ FLANGE NUT PLATE




480-003
Nut Plate

Full perimeter nut plate for use with unwired connectors. Use 3/4 perimeter nut plate for wired connectors

[Page 161](#)

PANEL GASKET




930-017

Square Flange Panel Basket

Creates a seal between square flange and mounting panel

[Page 162](#)

O-RING SEALS



M25988/3 or 249-003

O-ring Seal

Fluorosilicone or Viton seals provide sealing between receptacle and the mounting panel

[Page 162](#)

LOW PROFILE JAM-NUT



809-044

Ideally suited for panels with tightly spaced multiple connectors

[Page 163](#)

HEX JAM-NUT




806-035

Standard jam-nut

[Page 164](#)

PROTECTIVE COVER




667-441

Protective Cover

Protect unmated connectors with aluminum or SST covers

[Page 165](#)

DUMMY STOWAGE



667-441

Stowage Receptacle

Protect cabled plug connectors with aluminum or SST dummy stowage receptacles.

[Page 168](#)