



Series 80 Mighty Mouse Contact Arrangements

B

Series 80 Mighty Mouse Contact Arrangements

Contact Size		Contact Quantity					Contact Arrangement					
		#23	#20	#20HD	#16	#12	Series 800	Series 801	Series 802	Series 803	Series 804	Series 805
Size #23 Contacts 5 Amp Max. Current 500 VAC #22-#28 AWG		3					5-3	5-3	5-3	5-3	5-3	Not Avail.
		4					6-4	6-4	6-4	6-4	6-4	8-4
		6					6-6	6-6	6-6	6-6	6-6	8-6
		7					6-7	6-7	6-7	6-7	6-7	8-7
		10					7-10	7-10	7-10	7-10	7-10	9-10
		13					8-13	8-13	8-13	8-13	8-13	10-13
		19					9-19	9-19	9-19	9-19	9-19	11-19
		26					10-26	10-26	10-26	10-26	10-26	12-26
		37					12-37	13-37	12-37	12-37	12-37	15-37
		55					Not Avail.	16-55	14-55	14-55	14-55	18-55
85					Not Avail.	17-85	15-85	Not Avail.	Not Avail.	19-85		
130					Not Avail.	21-130	21-130	Not Avail.	Not Avail.	23-130		
Size #20HD Contacts 7.5 Amp Max. Current 750 VAC #20-#24 AWG				3			6-23	6-23	6-23	6-23	6-23	8-23
				5			7-25	7-25	7-25	7-25	7-25	9-25
				8			8-28	8-28	8-28	8-28	8-28	10-28
				10			9-210	9-210	9-210	9-210	9-210	11-210
				20			12-220	13-220	12-220	12-220	12-220	15-220
				35			Not Avail.	16-235	14-235	14-235	14-235	18-235
				41			Not Avail.	17-241	15-241	Not Avail.	Not Avail.	19-241
		69			Not Avail.	21-269	21-269	Not Avail.	Not Avail.	23-269		
Size #16 Contacts 13 Amp Max. Current 1800 VAC #16-#20 AWG					1		6-1	6-1	6-1	6-1	6-1	8-1
					2		8-2	8-2	8-2	8-2	8-2	10-2
					4		9-4	9-4	9-4	9-4	9-4	11-4
					5		10-5	10-5	10-5	10-5	10-5	12-5
					7		12-7	13-7	12-7	12-7	12-7	15-7
Size #16 Coaxial Contacts 50-75 Ohms					12		Not Avail.	16-12	14-12	14-12	14-12	18-12
					14		Not Avail.	17-14	15-14	Not Avail.	Not Avail.	19-14
					22		Not Avail.	21-22	21-22	Not Avail.	Not Avail.	23-22
Size #12 Contacts 23 Amp Max. Current 1800 VAC #12-#14 AWG						1	7-1	7-1	7-1	7-1	7-1	9-1
						2	10-2	10-2	10-2	10-2	10-2	12-2
						2	12-2	13-2	12-2	12-2	12-2	15-2
						3	12-3	13-3	12-3	12-3	12-3	15-3
Contact Arrangements with Mixed Size (Combo) Layouts		4	2				8-200	8-200	8-200	8-200	8-200	10-200
		8	2				9-201	9-201	9-201	9-201	9-201	11-201
		4			2		9-200	9-200	9-200	9-200	9-200	11-200
		8			2		10-202	10-202	10-202	10-202	10-202	12-202
		4				2	10-201	10-201	10-201	10-201	10-201	12-201
		6				2	12-200	13-200	12-200	12-200	12-200	15-200
		10				2	12-201	13-201	12-201	12-201	12-201	15-201
12				1	10-200	10-200	10-200	10-200	10-200	12-200		
Series 800	Series 801	Series 802	Series 803	Series 804	Series 805							