

BRAIDED WIRE PROTECTION

Bulk tubular non-metallic braid for wire harness protection



103-013 Unbonded tubular braid, Nomex[®], flame resistant



GY Gray

GN Green

W White

R Red

OR Orange

TN Desert Tan

Standard Black

How To Order			
Sample Part Number	103-013	-008	W
Basic No.	Unbonded tubular braid, Nomex [®]		
Braid Diameter No.	See Table I		
Color option	W = White R = Red GN = Green GY = Gray TN = Desert Tan OR = Orange Omit = for standard Black		

Table I			
Dash No.	Nominal I.D.	Wire Bundle Accomodation Range Ref.	
		Min.	Max.
-002	.062 (1.6)	.039 (1.0)	.090 (2.3)
-004	.125 (3.2)	.090 (2.3)	.160 (4.1)
-006	.188 (4.8)	.109 (2.8)	.240 (6.1)
-008	.250 (6.4)	.125 (3.2)	.312 (7.9)
-012	.375 (9.5)	.250 (6.4)	.450 (11.4)
-016	.500 (12.7)	.312 (7.9)	.625 (15.9)
-020	.625 (15.9)	.394 (10.0)	.787 (20.0)
-024	.750 (19.1)	.500 (12.7)	.900 (22.9)
-032	1.000 (25.4)	.787 (20.0)	1.375 (34.9)
-040	1.250 (31.8)	.750 (19.1)	1.390 (35.3)
-048	1.500 (38.1)	1.100 (27.9)	1.750 (44.5)
-064	2.000 (50.8)	1.750 (44.5)	2.250 (57.2)



- Soft, unbonded yarn, tubular braid, Nomex[®]
- -55° to +200°C temperature range
- 90,000 PSI yield tensile strength
- 25% elongation
- Excellent chemical resistance
- Good abrasion resistance
- Will not melt



General-duty abrasion-resistant unbonded yarn, Nomex[®] is well-suited for mechanical protection of soldier Personal Area Network cabling. Available in a broad range of colors, the soft, flexible, and durable material resists fraying and piling common to less robust yarns. In addition to improved flame resistance, unbonded braid, Nomex[®] offers superior flexibility compared to bonded solutions.

NOTES

1. Material - DuPont[™] Nomex[®] per MIL-C-572G, Type: PAA Form Y. DuPont[™] and Nomex[®] are trademarks or registered trademarks of E.I. duPont de Nemours and Company.
2. Minimum order length = 100 ft. (30.5m)