

Tapered tubular metal braid

ArmorLite™, AmberStrand®, nickel-, silver-, or tin-copper

100-041

TAPERED TUBULAR METAL BRAID, AMBERSTRAND®, ARMORLITE™, NICKEL/COPPER, SILVER/COPPER OR TIN/COPPER



Dash nos. 02-12 flared or folded back in this area

How To Order					
Sample Part Number	100-041	-06	T	10	A
Basic No.	Tapered tubular metal braid				
Braid Diameter No.	See Table I				
Braid Material	L = 100% ArmorLite N = Nickel/Copper S = Silver/Copper T = Tin/Copper A = 100% AmberStrand® B = 75% / 25% AmberStrand®				
Length	in 1 inch increments				
Wire Gage Option (N, S, and T materials only)	A = 36 AWG Omit = Standard 34 AWG				




Table I: Part Numbers and Sizes				
Braid Diameter Number	A (large end dia.)		B (small end dia.)	
	+ .10 - .00	(2.5) (0.0)	+ .10 - .00	(2.5) (0.0)
-01	.30	(7.6)	.15	(3.8)
-02	.45	(11.4)	.30	(7.6)
-03	.60	(15.2)	.30	(7.6)
-04	.75	(19.1)	.30	(7.6)
-05	.75	(19.1)	.50	(12.7)
-06	1.05	(26.7)	.50	(12.7)
-07	1.05	(26.7)	.75	(19.1)
-08	1.20	(30.5)	.75	(19.1)
-09	1.20	(30.5)	1.00	(25.4)
-10	1.50	(38.1)	.75	(19.1)
-11	1.50	(38.1)	1.00	(25.4)
-12	1.50	(38.1)	1.20	(30.5)
-13	.88	(22.4)	.50	(12.7)
-14	1.38	(35.1)	.75	(19.1)

MATERIAL/FINISH

Copper with Nickel, Silver, or Tin finish. 18° to 30°, 34 or 36 AWG, 85% minimum coverage

ArmorLite - Stainless Steel / Nickel plated

AmberStrand (A) - Composite / Nickel plated

AmberStrand (B) - Composite 75%, Nickel Copper 25%