





**233-105-05**  
**MIL-DTL-38999 Series III Type**  
**In-Line Environmental Receptacle Connector**



Consult factory for available insert arrangements.

**APPLICATION NOTES**

- |  |   |
|--|---|
| <p>1. Material/ Finishes:<br/>                 Shells - See Table II<br/>                 Insulator- High Grade Rigid Dielectric/ N.A<br/>                 Seals- Fluorosilicone/ N.A.</p> | <p>3. Insert arrangement in accordance with MIL-STD-1560.<br/>                 4. Insert arrangement shown is for reference only.<br/>                 5. Blue Color Band indicates rear release retention system.<br/>                 7. Metric Dimensions (mm) are indicated in parentheses.</p> |
| <p>2. Assembly to be identified with Glenair's name, part number and date code space permitting.</p>   |   |

**233-105-05**  
**MIL-DTL-38999 Series III Type**  
**In-Line Environmental Receptacle Connector**



**TABLE II: FINISH**

SYM	MATERIAL	FINISH	MIL SYM
<b>M</b>	Aluminum	Electroless Nickel	<b>F</b>
<b>NF</b>		Cadmium O.D. Over Electroless Nickel	<b>W</b>
<b>ZN</b>		Zinc Ni, Olive Drab	<b>Z</b>
<b>ZE</b>		Zinc Ni, No Chromate	
<b>ZR</b>		Zinc Ni, Black (Tri-Valent CR)	
<b>AL</b>		Pure-Dense Electro-Deposited Aluminum	<b>P</b>
<b>MT</b>		Ni-PTFE 1000 Hour Grey™	<b>T</b>
<b>XM</b>	Composite	Electroless Nickel	<b>M</b>
<b>XMT</b>		Ni-PTFE 1000 Hour Grey™	
<b>XO</b>		No Finish	
<b>XW</b>		Cadmium O.D. over Electroless Nickel	<b>J</b>
<b>Z1</b>	Stainless Steel	Passivate	
<b>ZC</b>		Zinc Colbalt	
<b>ZL</b>		Electro-Deposited Nickel	
<b>ZW</b>		Cadmium O.D. over Nickel	
<b>AB</b>	Marine Bronze	None (Clean Only)	

\*Consult Factory for Additional Plating Options

**TABLE III: SHELL SIZE**

Shell Size Code	Shell Size	A Thread	G	H	S Max Dia	J Thread
A	09	.6250-.1P-.3L-TS-2A	.144 (3.7) .083 (2.1)	.823 (20.9) .768 (19.5)	.858 (21.8)	M12 x 1.0-6g 0.100R
B	11	.7500-.1P-.3L-TS-2A	.144 (3.7) .083 (2.1)	.823 (20.9) .768 (19.5)	.984 (25.0)	M15 x 1.0-6g 0.100R
C	13	.8750-.1P-.3L-TS-2A	.144 (3.7) .083 (2.1)	.823 (20.9) .768 (19.5)	1.157 (29.4)	M18 x 1.0-6g 0.100R
D	15	1.0000-.1P-.3L-TS-2A	.144 (3.7) .083 (2.1)	.823 (20.9) .768 (19.5)	1.280 (32.5)	M22 x 1.0-6g 0.100R
E	17	1.1875-.1P-.3L-TS-2A	.144 (3.7) .083 (2.1)	.823 (20.9) .768 (19.5)	1.406 (35.7)	M25 x 1.0-6g 0.100R
F	19	1.2500-.1P-.3L-TS-2A	.144 (3.7) .083 (2.1)	.823 (20.9) .768 (19.5)	1.516 (38.5)	M28 x 1.0-6g 0.100R
G	21	1.3750-.1P-.3L-TS-2A	.171 (65.2) .083 (39.8)	.791 (20.0) .736 (18.7)	1.642 (41.7)	M31 x 1.0-6g 0.100R
H	23	1.5000-.1P-.3L-TS-2A	.171 (65.2) .083 (39.8)	.791 (20.0) .736 (18.7)	1.768 (44.9)	M34 x 1.0-6g 0.100R
J	25	1.6250-.1P-.3L-TS-2A	.171 (65.2) .083 (39.8)	.791 (20.0) .736 (18.7)	1.890 (48.0)	M37 x 1.0-6g 0.100R