

# Series 75 Flexible Metal-Core Conduit System Introduction and Quick Selection Guide



## The Ultimate in Highly Flexible, Crush-Proof EMI/RFI Protection


**Glenair Series 75 Metal-Core Conduit** is a helically wound, continuous solder metal conduit, delivering the highest level of EMI/RFI shielding and crush-proof strength available for mission-critical interconnect wiring applications. Metal-core conduit is the material of choice for TEMPEST secure communications and intensive EMI/RFI environments, and is offered in brass, nickel/iron, or stainless steel. Specify braided shielding and jacketing for additional mechanical and environmental protection. State-of-the-art construction IAW MIL-C-13909/A-A-52240, MIL-PRF-24758A and MIL-DTL-28840.

**Series 75 Do-It-Yourself Fittings** are the best choice when ease of assembly and installation is a requirement, or when producing prototype wire-routing systems in unpredictable lengths. Glenair's offerings include the compact, lightweight RP Plus family of backshells and fittings, plus heavy-duty environmental metal and weight-saving hybrid composite fittings built for rugged reliability in topside applications.

**Prefer a Turnkey Solution?** Factory terminated assemblies offer weight reduction and size savings, as well as highly durable tamper-proof fittings.




Metal-Core  
Conduit Configurations,  
pages D-2 – D-11




Turnkey Factory Terminated  
Series 75 Assemblies, p. D-14 - D-15



Low-profile  
RP Plus system,  
pages D-16 – D-23



Heavy-Duty  
Environmental  
System: Metal,  
pages D-24 – D-31



Heavy-Duty  
Environmental  
System:  
Composite,  
pages D-32 – D-39

Part No.	Description	Page No.
<b>Flexible Metal-Core Conduit Configurations</b>		
	Conduit Configuration Options and Material Properties	D-2 – D-6
<b>750-190</b>	Metal-Core Helical Conduit	D-7
<b>750-191</b>	Metal-Core Conduit with Braid	D-8
<b>750-192</b>	Metal-Core Conduit with Braid and Jacket	D-9
<b>750-193</b>	Metal-Core Conduit with 2 Braids	D-10
<b>750-194</b>	Metal-Core Conduit with 2 Braids and Jacket	D-11
<b>750-195</b>	Metal-Core Conduit with 3 Braids	D-12
<b>750-196</b>	Metal-Core Conduit with 3 Braids and Jacket	D-13
<b>Turnkey Factory Terminated Assemblies</b>		
	Factory Terminated Conduit Assemblies - How to Order	D-14
	Point-to-Point Conduit Assembly Basic Part Numbers	D-15
<b>Low-profile RP Plus Fittings</b>		
<b>712-832</b>	Conduit to Connector Backshell	D-16
<b>712-849</b>	Conduit to Bulkhead Fitting	D-18
<b>712-850</b>	Conduit to Transition or End Fitting Backshell	D-20
<b>712-878</b>	Conduit to Conduit Splice	D-22
<b>Heavy-Duty Environmental System: Metal</b>		
<b>712-834</b>	Conduit to Connector Backshell	D-24
<b>712-836</b>	Conduit to Bulkhead Fitting	D-26
<b>712-835</b>	Conduit to Transition or End Fitting Backshell	D-28
<b>712-837</b>	Conduit-to-Conduit Splice	D-30
<b>Heavy-Duty Environmental System: Composite</b>		
<b>712-843</b>	Conduit to Connector Backshell	D-32
<b>712-845</b>	Conduit to Bulkhead Fitting	D-34
<b>712-844</b>	Conduit to Transition or End Fitting Backshell	D-36
<b>712-846</b>	Conduit to Conduit Splice	D-38
<b>Legacy MIL-C-24758 System</b>		
<b>712-386</b>	Conduit to Connector Backshell	D-40
<b>712-188</b>	Conduit to Bulkhead Fitting	D-42
<b>712-387</b>	Conduit to Transition or End Fitting Backshell	D-44
<b>712-388</b>	Conduit-to-Conduit Splice	D-46
	Installation Procedures	D-48

