


790-081

Series 79 Micro-Crimp Mateable, Rear Panel Mount
Hermetic Receptacle, Pin Face
with Pre-Wired Terminations




Series 79
Micro-Crimp



Mounting Hardware	
P Jackpost	Connector supplies with non-removable jackpost. Shell size "M" has 6-32-UNC thread. Shell sizes "H" and "L" have 4-40 UNC-2B thread. all other sizes have 2-56 UNC-2B thread.
G Guide Pin	Connector supplied with non-removable guide pins for blind mate applications. Mates with option "S" guide socket on corresponding plug connector.
S Guide Socket	Connector supplied with non-removable guide sockets for blind mate applications. Mates with option "G" guide pin on corresponding plug connector.

Shell Sizes A, B, C, D, E, F, J, & K
(See Table I For Dimensions)



CONTACTS AND STANDARD WIRE SIZES AVAILABLE**	
Contact Size	Wire Size (AWG)
#23	22
#16	16
#12	12

** Consult factory for other wire sizes (special)

TABLE I: SHELL SIZE A, B, C, D, E, F, J, AND K DIMENSIONS								
Shell Sizes	A Oal	B Bsc	C Bsc	D Max	E Max	F Max	G Max	H Typ Unc 2-B
A	1.490 (37.85)	0.925 (23.50)	0.565 (14.35)	0.401 (10.19)	0.760 (19.30)	0.350 (8.89)	1.215 (30.86)	#4-40
B	1.680 (42.67)	1.075 (27.30)	0.715 (18.16)	0.551 (14.00)	0.910 (23.11)	0.500 (12.70)	1.365 (34.67)	
C	1.785 (45.34)	1.225 (31.12)	0.865 (21.97)	0.701 (17.81)	1.060 (26.92)	0.650 (16.51)	1.515 (38.48)	
D	1.975 (50.17)	1.325 (33.65)	0.965 (24.51)	0.801 (20.35)	1.160 (29.46)	0.750 (19.05)	1.615 (41.02)	
E	2.075 (52.71)	1.475 (37.47)	1.115 (28.32)	0.951 (24.16)	1.310 (33.27)	0.900 (22.86)	1.765 (44.83)	
F	2.175 (55.24)	1.625 (41.28)	1.265 (32.13)	1.101 (27.97)	1.460 (37.08)	1.050 (26.67)	1.915 (48.64)	
J	2.665 (67.69)	1.975 (50.17)	1.615 (41.02)	1.460 (37.08)	1.810 (45.97)	1.405 (35.69)	2.265 (57.53)	
K	2.960 (75.18)	2.375 (60.33)	2.015 (51.18)	1.860 (47.24)	2.210 (56.13)	1.805 (45.85)	2.665 (67.69)	


APPLICATION NOTES

- Material/Finish:
Shell* - 300 Series CRES/passivate or 300 Series CRES/Nickel Plate
Contacts - Nickel iron alloy/gold plate
Insulator - Individual glass beads/N.A.
Seals - Fluorosilicone blend/N.A.
Mating Hardware - CRES/passivated
*Consult factory for other shell finishes and O-Ring materials.
- Metric dimensions (mm) are indicated in parentheses.
- See Pages L-7 and L-8 for panel cut-out information.
- Test Criteria:
Hermeticity - 1×10^{-5} scc He/sec @1 ATM Delta
DWV - #23 pins: 500 VAC pin-to-shell
#16 pins: 1800 VAC pin-to-shell
#12 pins: 1800 VAC pin-to-shell
I.R. - 5,000 megohms minimum @500 VDC
- Glenair 790-081 will mate with any series 79 plug with socket contacts and same shell and insert, and is designed to utilize 799-016 EMI backshells.




790-081
Series 79 Micro-Crimp Mateable, Rear Panel Mount
Hermetic Receptacle, Pin Face
with Pre-Wired Terminations

Shell Sizes G (See Table II For Dimensions)



Shell Sizes H and L (See Table II For Dimensions)



Shell Sizes M (See Table II For Dimensions)




TABLE II: SHELL SIZE G, H, L AND M DIMENSIONS

Shell Size	J Oal	K Bsc	L Bsc	M Max	N Max	P Max	R Max	S Typ UNC 2-B
G	2.130 (54.10)	1.575 (40.00)	1.215 (30.86)	1.079 (27.41)	1.410 (35.81)	1.020 (25.91)	1.861 (47.27)	#4-40
H	2.900 (73.66)	2.236 (56.79)	1.800 (45.72)	1.450 (36.83)	2.045 (51.94)	1.385 (35.18)	2.500 (63.50)	#6-32
L	3.100 (78.74)	2.472 (62.79)	2.036 (51.71)	1.686 (42.82)	2.281 (57.94)	1.625 (41.28)	2.736 (69.49)	#6-32
M	3.475 (88.27)	2.770 (70.36)	2.200 (55.88)	1.745 (44.32)	2.485 (63.12)	1.690 (42.93)	3.085 (78.36)	#8-32