

HIGH-SPEED
MICRO-D



Smallest and lightest
aerospace-grade
high-speed
connector solution



Miniaturized Micro-D Connector / TwistPin contact solution with 10+ Gb/sec. performance per differential pair

High-speed datalink applications such as aircraft avionics and other high data rate and bandwidth equipment require both optimized data transmission performance as well as robust mechanical and EMC performance. Micro-D connector packaging with high-retention-force TwistPin contacts has a proven track record in standard signal and power applications. Now Glenair has developed a Micro-D solution—intermountable in existing Micro-D panel cutouts—that brings high-speed datalink performance to these mission-critical platforms. The High-Speed Micro-D is a 1 Amp pre-wired cable and PCB solution with 10+ Gb/sec. performance per differential pair. Auxiliary EMC ground springs on plug and integral contact separation architecture ensures data integrity and low attenuation performance.

High-Speed Micro-D connectors and cables are optimized for high-speed digital datalink protocols with machined-shell packaging, low attenuation contact spacing, and ultra low PPS dielectric insulators.



- Pre-wired factory cordsets and PCB connectors
- Unique contact isolation and spacing for optimal high-speed performance
- Standard layouts support maximum #28 AWG wire
- Ultra-low dielectric material combined with optimized contact size and spacing
- Precision-machined shells with gold or nickel plating
- Hybrid contact solutions available with 3 amp and 1 amp TwistPin contacts (perfect for USB 3.0 SuperSpeed applications)

HIGH-SPEED Micro-D



The miniature high-speed connector with mil-spec pedigree connector and contact packaging

SUPPORTED HIGH-SPEED PROTOCOLS


Shell Sizes and contact arrangements optimized for today's popular high-speed protocols



21	21	25	21
Display Port 1.2	HDMI 2.0	DVI-D Dual	DVI-D Single
9	15	9	15
eSATA/SATA 3	USB 3.0	USB 2.0	Up To: Cat 6A (10GBASE-T)

Micro-D High-Speed configurations include wired assemblies and straight or 90° PCB-mount connectors. Insert arrangements feature 1 Amp Nanominiature TwistPin contacts. Hybrid 1Amp/3Amp arrangements for USB 3.0 SuperSpeed are also available. All designs have been tested for today's popular high-speed protocols.


EMI SHIELDING AND ENVIRONMENTAL SEALING



Plug connectors feature a gold-plated stainless steel ground spring for EMI protection, and a silicone gasket for environmental sealing.

High-Speed Micro-D contact arrangements face view pin connector

- high-speed signal pair
- signal-pair drain wire
- low-speed signal or power contacts



MATERIALS AND FINISHES

Connector Shell: Aluminum Alloy 6061
 Insulator: Polyphenylene Sulfide (PPS)
 Flange Seal: Fluorosilicone Rubber, Blue
 Pin Contact: Copper Alloy, Gold over Nickel Plating
 Socket Contact: Copper Alloy, Gold over Nickel Plating
 Ground Spring: Stainless Steel, Gold Plating
 Hardware: 300 Series Stainless Steel, Passivated
 Epoxy Resin Hysol EE4215 and Stycast 2850FT/Catalyst 11

*Contact factory for custom configurations supporting up to 3 Amps.

**Add (10 Ounces) X (# of 3 Amp Contacts) for mating force for configurations with 3 Amp contacts

PERFORMANCE SPECIFICATIONS



Current Rating: 1 Amp*
 DWV: 600 VAC Sea Level
 Insulation Resistance: 5000 Megohms Minimum (500 VDC)
 Contact Resistance: 80 Milliohms Maximum
 Operating Temperature: -55°C To 125°C
 Mating Force: (7 Ounces) X (# of 1 Amp Contacts)**
 Durability: 500 Mating Cycles



How-to-order GHSM Shielded Cable Assembly Connectors

How To Order High-Speed Micro-D Wired Connectors	
Sample Part Number	GHSM 2 R -31 P -A 8 J 1 -18 L A
Series	GHSM = Glenair High-Speed Micro-D
Shell Finish	2 = Nickel 5 = Gold
Insulator Material	R = PPS
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 67
Contact Type	P = Pin (Single-End Plug) S = Socket (Single-End Receptacle) GP = Double-End Cable, Pin Connectors Both Ends GS = Double-End Cable, Socket Connectors Both Ends CS = Double-End Cable, Pin and Socket
High Speed Cable Type	A = Glenair Cable 963-043-26 (100 Ohm, +105°C Max) B = Glenair Cable 963-129-28 (90 Ohm)
Discrete Wire Gage (AWG)	8 = #28 0 = #30 (J Wire Type only)
Discrete Wire Type	K = M22759/11 600 VRMS Teflon (TFE) J = M22759/33 600 VRMS Modified Cross-Linked Tefzel (ETFE)
Discrete Wire Color	1 = White 7 = Ten Color Repeating
Wire Length	Wire Length in Inches, 6 Inch Minimum
Mounting Hardware¹	L, M, P, S, (See Mounting Hardware Designations table below)
Shield and Jacket Option	X - ArmorLite Braided Microfilament Stainless Steel shield with E-CTFE Halar "Expando" Jacket W - ArmorLite Braided Microfilament Stainless Steel shield Z - 75% Braided AmberStrand shield with E-CTFE Halar "Expando" Jacket V - 75% Braided AmberStrand shield T - 100% Braided AmberStrand shield with E-CTFE Halar "Expando" Jacket S - 100% Braided AmberStrand shield C - Braided shield (Nickel Over Copper) with E-CTFE Halar "Expando" Jacket A - Braided shield (Nickel over Copper) N - No Shield, No Jacket (customer to install)



1 - Hardware is always required to ensure connector pair is fully mated when installed



Mounting Hardware Designations			
P Jackpost	M Hex Head Jackscrew	S Slot Head Jackscrew	L Hex Head Jackscrew, Non-Removable



How-to-order GHSM-BSS Board Straight Surface Mount Connectors

How To Order High-Speed Micro-D Board Straight Surface Mount Connectors	
Sample Part Number	GHSM 2 R -25 S BSS PU
Series	GHSM = Glenair High-Speed Micro-D
Shell Finish	2 = Nickel 5 = Gold
Insulator Material	R = PPS
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 67
Contact Type	P = Pin (Plug) S = Socket (Receptacle)
Termination Type	BSS = Board Straight Surface Mount
Jackpost Option (see table below)	PN = Extended Jackpost for .062" PCB RN = Extended Jackpost for .196" PCB PU = Short Jackpost and Threaded Insert Rear Panel Jackpost with Threaded Insert R2U = .032" Panel R3U = .047" Panel R4U = .062" Panel R5U = .094" Panel R6U = .125" Panel R7U = .080" Panel






How-to-order GHSM-HBR Hybrid Board Right-Angle connectors

How To Order High-Speed Micro-D Hybrid Board Right Angle Connectors										
Sample Part Number	GHSM	2	R	-25	S	HBR	P	T	-110	
Series	GHSM = Glenair High-Speed Micro-D									
Shell Finish	2 = Nickel 5 = Gold									
Insulator Material	R = PPS									
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 67									
Contact Type	P = Pin (Plug) S = Socket (Receptacle)									
Termination Type	HBR = Hybrid Board Right Angle									
Jackpost Option (see table below)	P = Jackpost		Jackposts for Rear Panel Mounting							
	L = Hex Head Jackscrew (non-removable)		R1 = .032" Panel	R2 = .047" Panel	R3 = .062" Panel	R4 = .093" Panel	R5 = .125" Panel	R6 = .080" Panel		
Threaded Insert Option	T = Threaded Insert in Board Mounting Hole Omit for Thru-Hole									
Right-Angle Lead Length	-.080, -.110, -.140, -.172 (Length in Inches ±.015)									



How-to-order GHSRPM Rear-Panel Mount Cable Assembly Connectors

How To Order High-Speed Micro-D Wired Connectors	
Sample Part Number	GHSRPM 2 R -31 P -A 8 J 1 -18 R3 N
Series	GHSRPM = Glenair High-Speed Micro-D, Rear Panel Mount
Shell Finish	2 = Nickel 5 = Gold
Insulator Material	R = PPS
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 67
Contact Type	P = Pin (Plug) S = Socket (Receptacle)
High Speed Cable Type	A = Glenair Cable 963-043-26 (100 Ohm, +105°C Max) B = Glenair Cable 963-129-28 (90 Ohm)
Discrete Wire Gage (AWG)	8 = #28 0 = #30 (J Wire Type only)
Discrete Wire Type	K = M22759/11 600 VRMS Teflon (TFE) J = M22759/33 600 VRMS Modified Cross-Linked Tefzel (ETFE)
Discrete Wire Color	1 = White 7 = Ten Color Repeating
Wire Length	Wire Length in Inches, 6 Inch Minimum
Mounting Hardware	R1 = .032" Panel R2 = .047" Panel R3 = .062" Panel R4 = .093" Panel R5 = .125" Panel R6 = .080" Panel
O-Ring Material	C = Conductive N = Non-Conductive (Nitrile)







HIGH-SPEED Micro-D



How-to-order GHSRPM-BSS Rear-Panel Board Straight Surface Mount connectors

How To Order High-Speed Micro-D Board Straight Surface Mount Connectors	
Sample Part Number	GHSRPM 2 R -25 P BSS R3 N
Series	GHSRPM = Glenair High-Speed Micro-D, Rear Panel Mount
Shell Finish	2 = Nickel 5 = Gold
Insulator Material	R = PPS
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 67
Contact Type	P = Pin (Plug) S = Socket (Receptacle)
Termination Type	BSS = Board Straight Surface Mount
Rear Panel Mount Hardware Option	R2U = .032" Panel R3U = .047" Panel R4U = .062" Panel R5U = .094" Panel R6U = .125" Panel R7U = .080" Panel
O-Ring Material	C = Conductive N = Non-Conductive (Nitrile)



How-to-order GHSRPM-HBR Rear-Panel Hybrid Board Right-Angle Connectors

How To Order High-Speed Micro-D Hybrid Board Right Angle Connectors											
Sample Part Number	GHSRPM	2	R	-25	P	HBR	R3	T	N	-.110	
Series	GHSRPM = Glenair High-Speed Rear-Panel Micro-D										
Shell Finish	2 = Nickel 5 = Gold										
Insulator Material	R = PPS										
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 67										
Contact Type	P = Pin (Plug) S = Socket (Receptacle)										
Termination Type	HBR = Hybrid Board Right Angle										
Rear Panel Mount Hardware Option	R1 = .032" Panel R2 = .047" Panel R3 = .062" Panel R4 = .093" Panel R5 = .125" Panel R6 = .080" Panel										
Threaded Insert Option	T = Threaded Insert in Board Mounting Hole Omit for Thru-Hole										
O-Ring Material	C = Conductive N = Non-Conductive (Nitrile)										
Right-Angle Lead Length	-.080, -.110, -.140, -.172 (Length in Inches ±.015)										

