

GHV-001 kV Seal Size #12 13.5 kV contacts for Glenair SuperNine and D38999 Series I, III, and IV

kV SEAL™ CONTACT ASSEMBLIES



kV SEAL CONTACT FEATURES

- 13.5 kVDC operating voltage
- Drop-in performance in Glenair Signature SuperNine and MIL-DTL-38999 Series I, III, and IV connectors
- Intermateable with Teledyne Reynolds Hi-Mate and Connectronics Corp. HyKons

PERFORMANCE SPECIFICATIONS



- IR: 5000 Megohms at 500 VDC
- DWV: 18 kVDC, 10uA max leakage current at sea level / ambient conditions
- Temperature: -55° to +125°
- Add Mod Code **1223**** to part number to include high-altitude DWV testing in final inspection

MATERIAL / FINISH

- Inner Contact, Pin/Socket - copper alloy / gold over nickel
- Contact Insulator Body - high-grade rigid dielectric
- kV Seal - fluorosilicone blend
- Wire Overmold - silicone blend
- Wire - fluoropolymer primary insulation (standard). Silicone-coated fluoropolymer available.
- Assemblies using option **T** etched wire packaged in UV-resistant bags

HOW TO ORDER						
Sample Part Number	GHV-001	-A	PP	T	0	-36
Series	GHV-001 = kV Seal 13.5 kVDC High-Voltage Contact Assembly, Size #12					
Contact Envelope / Wire Gauge	A = #24 AWG wire B = #22 AWG wire (See Table II)					
Contact Gender and Assembly Type	P = Pin (AS39029/58 type), with flying lead S = Socket (AS39029/56 type), with flying lead PP = Double-ended Pin assembly SS = Double-Ended Socket assembly PS = Double-ended Pin and Socket assembly					
Wire Finish	S = Silicone-Coated Fluoropolymer T = Continuously-Etched Fluoropolymer					
Wire Color Code	0 = Black (per MIL-STD-681)					
Total Length	in inches (e.g. -36 = 36 inches) 12" minimum needed for testing					


TABLE II - CONTACT ENVELOPE / WIRE GAUGE PERFORMANCE					
Sym	Contact Envelope		Wire Gauge	Current Rating	OP Voltage Through 70K ft.
	Pin	Socket			
A	AS39029/58-365	AS39029/56-353	24	3	13.5 kVDC
B			22	5	




P - Pin Contact with Flying Lead: **GHV-001-*P**.***




PP - Double-Ended Pin Assembly: **GHV-001-*PP**.***



S - Socket Contact with Flying Lead: **GHV-001-*S**.***



SS - Double-Ended Socket Assembly: **GHV-001-*SS**.***



PS - Pin and Socket Assembly: **GHV-001-*PS**.***