

Series 80 Mighty Mouse Connectors and Cables Table of Contents



Contacts, Crimp Tools and Assembly Tools		Product Selection Guide.....A-1 Size #23 ContactsA-3 Size #20HD Contacts.....A-6 Size #12,#16, #20 Contacts.....A-7 Size #12, #16, Coax Contacts.....A-8 Pneumatic ContactsA-10 Sealing Plugs.....A-10	Crimp Tools A-11 Insertion/Removal Tools..... A-13 Contact Retention Tester A-13 Band-Master ATS [®] Tools..... A-14 Jam Nut Tightening Tools..... A-15 Twisted Pair Termination to High Speed Mighty Mouse Instructions A-17	A
General Information and Reference		Product Selection Guide.....B-1 Contact Arrangements.....B-2 Printed Circuit Board LayoutsB-8 Torque Values.....B-39	Series 80 Product SpecB-40 Space Flight InformationB-47 Modification Codes.....B-50 Material/Finish Codes.....B-51	B
Series 800 Connectors <i>UNF Threads</i>		Selection Guide.....C-1 Contact Arrangements.....C-2 General InformationC-4 Plugs.....C-6 Crimp ReceptaclesC-8	PCB Receptacles C-12 Right Angle PCB Recep.....C-15 Hermetic ReceptaclesC-20 Bulkhead Feedthrough.....C-24 CordsetsC-21	C
Series 801 Connectors <i>Rugged Double-Start ACME Threads</i>		Selection Guide.....D-1 Contact Arrangements.....D-2 General InformationD-5 Plugs.....D-9 Receptacles.....D-15 PCB Receptacles.....D-20	Right Angle PCB Recep.....D-23 Square Flange PCB Recep.....D-28 Hermetic ReceptaclesD-30 Bulk Head FeedthroughH.....D-34 Connector Savers.....D-36 CordsetsD-38	D
Series 802 Connectors <i>"AquaMouse" 3500 PSI</i>		Selection Guide.....E-1 Contact Arrangements.....E-2 General InformationE-5 PlugsE-6	Receptacles.....E-8 PCB Receptacle.....E-12 Hermetic ReceptaclesE-16 Bulkhead Feedthrough.....E-21 CordsetsE-23	E
Series 803 Connectors <i>Bayonet</i>		Selection Guide.....F-1 Contact Arrangements.....F-2 General InformationF-4 PlugsF-6 Receptacles.....F-8	PCB ReceptaclesF-12 Hermetic ReceptaclesF-14 Bulkhead Feedthrough.....F-16 CordsetsF-18	F
Series 804 Connectors <i>Push-Pull</i>		Selection Guide.....G-1 Contact Arrangements.....G-2 General InformationG-6 PlugsG-7 Receptacles.....G-12 PCB Receptacle.....G-20 Hermetic ReceptaclesG-23	Bulkhead Feedthrough.....G-26 Quick-Release Plug & Receptacle...G-28 CordsetsG-32 USB Cordset Hub & Patch CableG-38 Radio ConnectorsG-42 USB Flash Drive.....G-44 Series 824 Locking Push/Pull.....G-45	G
Series 805 Connectors <i>Triple-Start ACME Threads</i>		Selection Guide.....H-1 Contact Arrangements.....H-2 General InformationH-7 PlugsH-8 Receptacles.....H-13 PCB Receptacles.....H-18 Hermetic ReceptaclesH-22	Square Flange PCB Recep.....H-27 Right Angle PCB Recep.....H-29 Cat-Master Plug/Recep.....H-33 Bulkhead Feedthrough.....H-39 Connector Savers.....H-41 CordsetsH-43	H
Filtered Connectors <i>Planar Array Low-Pass</i>		Selection Guide.....J-1 Contact Arrangements.....J-3 PCB Footprints.....J-4 Series 801 Filtered Receptacles.....J-8	Series 804 Filtered Receptacles J-14 Series 805 Filtered Receptacles J-16 Series 805 Filtered Adapter..... J-20 Series 800 Filtered Receptacles J-22	J



Series 80 Mighty Mouse Connectors and Cables Table of Contents

K

New Size #8 Contact Arrangements

For Series 801 and 805 Connectors



Selection Guide.....	K-1
General Information.....	K-2
Contact Arrangements.....	K-5
PCB Footprints.....	K-6
Series 801 Plug and Receptacle.....	K-9
Series 805 Plug and Receptacle.....	K-16
#8 Power Contacts.....	K-22

75 Ohm Coax Contacts.....	K-24
50 Ohm Coax Contacts.....	K-26
Quadrax Contacts.....	K-28
Concentric Twinax Contacts.....	K-30
Differential Twinax Contacts.....	K-32
M39029 Coax Contacts.....	K-34

L

Series 811 Connectors

High Density



Selection Guide.....	L-1
General Information.....	L-2
Prewired In-Line Plugs.....	L-6
Prewired In-Line Receptacles.....	L-7
Square Flange Pigtail Receptacles.....	L-8

Jam Nut Pigtail Receptacles.....	L-10
Jam Nut PCB Receptacles.....	L-12
Square Flange PCB Receptacles.....	L-13
Harsh Environment Cordsets.....	L-15

M

Series 80 Connectors

With Stinger Contacts



Selection Guide.....	M-1
General Information.....	M-2
Insert Arrangements.....	M-3
Series 841 Plug.....	M-4
Series 841 Receptacle.....	M-6

Series 844 Plug.....	M-10
Series 844 Receptacle.....	M-12
Series 845 Plug.....	M-16
Series 845 Receptacle.....	M-18
Series 80 Stinger™ Contact Tools.....	M-23

N

Series 80 Overview:

Mighty Mouse High-Speed, High-Bandwidth Interconnect Solutions



High Speed Introduction.....	N-1
High Speed Connectors.....	N-4
Product Overview.....	N-6
Contacts and Tools.....	N-10

P

Series 801 High-Speed Connectors

Double-Start Acme Threads



Selection Guide.....	P-1
General Information.....	P-2
Plugs.....	P-4

Receptacles.....	P-6
PCB Receptacles.....	P-10
Cordsets.....	P-13

Q

Series 804 High-Speed Connectors

Quick-Disconnect Push-Pull Mighty Mouse



Selection Guide.....	Q-1
General Information.....	Q-2
Plugs.....	Q-4

Crimp Receptacles.....	Q-6
PCB Receptacles.....	Q-10
Cordsets.....	Q-12

R

Series 805 High-Speed Connectors

Triple-Start Acme Threads




Selection Guide.....	R-1
General Information.....	R-2
Plugs.....	R-4
Receptacles.....	R-6
Cordsets.....	R-11

S

Ultra-Twinax Size #12

Low-Impedance High-Speed Twinax



Selection Guide.....	S-1
General Information.....	S-2
Contacts.....	S-4

Plugs.....	S-10
In-Line Receptacles.....	S-12

T

SuperSeal Mighty Mouse Series 801

Micro USB Connectors



Selection Guide.....	T-1
General Information.....	T-2
Micro "B" USB Plug.....	T-5
Micro "AB" USB Receptacle.....	T-6
Front & Rear Micro "B" USB Plug.....	T-7

Front and Rear Micro "AB" USB Receptacles.....	T-8
Sav-Con with Micro "B" USB Plug and Micro "AB" USB Receptacle.....	T-9

Series 80 Mighty Mouse Connectors and Cables Table of Contents



Cordsets for High-Speed Differential Impedance




Selection GuideU-1
 General InformationU-2
 Connector Selection Guide.....U-3
 How To Order Cordsets.....U-4
 Cable and Jacket SpecificationsU-5

Strain Relief SpecificationsU-6
 Wiring SchematicsU-8
 USB 2.0 Cordsets U-11
 RJ-45 Ethernet Cordsets U-13

U

High-Speed Cable *Optimized for High-Speed Protocols*



Selection Guide..... V-1
 General Information V-2
 Parallel Pair Data Cable..... V-3
 Tactical Cat 5e Ethernet Cable V-4
 Avionic Cat 6e Ethernet Cable V-5

Cat 7 Ethernet Cable V-6
 USB 2.0 Cable V-7
 USB 3.0 Cable V-8
 IEEE 13394 Cable..... V-9
 SATA/eSATA Cable V-10

V

Fiber Optic Mighty Mouse *For Series 801, 802 and 805*



Selection Guide.....W-1
 Contact InformationW-2
 General InformationW-4
 Fiber Optic Termini.....W-5
 Series 801 Plug W-11

Series 801 Receptacle W-13
 Series 802 Plug W-18
 Series 802 Receptacle W-20
 Series 805 Plug W-24
 Series 805 Receptacle W-26

W

Series 80 Accessories



Selection Guide.....X-1
 Accessory Thread TableX-2
 Heat-Shrinkable Boots..... X-3
 Jam and Hex NutsX-10
 Gaskets and O-Rings.....X-12
 Mounting Flange.....X-18

Shorting Caps.....X-19
 Strain Relief Clamps.....X-22
 EMI AdaptersX-25
 BackshellsX-29
 Protective Covers.....X-41
 Dummy Receptacles.....X-73

X

Part Number Index



Index

...and don't miss this late-breaking new product innovation



page G-40

Gold plated crimp contacts for #12 to #30 AWG wire

Series 824 Mighty Mouse LOCKING PUSH-PULL CONNECTORS

Introducing the new Mighty Mouse Series 824 Locking Push-Pull Connector: all the familiar size, weight and performance advantages of the industry-standard Mighty Mouse 804 push-pull connector with a revolutionary low-profile locking coupling mechanism.

- Fast mating, locking quick-release coupling mechanism
- 31 insert arrangements
- Integrated cable shield termination platform

Specifications	
Current Rating	#23 - 5 AMPS, #16 - 13 A., #12 - 23 A.
Dielectric Withstanding Voltage	#23 - 500 VAC RMS, #12 and #16 - 1800 VAC RMS
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C to +150° C
Shock / Vibration	100 g / 16 g
Shell-to-Shell Resistance, Nickel Plated	2 milliohms maximum
Durability	2000 mating cycles
Breakaway Force	50 pounds minimum