


# Series 801 Mighty Mouse Double-Start ACME Threads Square Flange Receptacle

801-009-12 and 801-010-22 - Dimensions



Fiber Optic  
Mighty Mouse

## Rear panel mount receptacle - shell style 12 and 22



**Integral Band Platform**  
801-009-12 and 801-009-22

**Accessory Thread**  
801-010-12 and 801-010-22

Shell Size	Dimensions						V Clinch Nut	W
	A Thread	B Thread	C BSC	Ø T	U SQ			
5	.3125-.05P-.1L-DS-2A	.2500-32 UNEF-2A	0.363	0.774	0.623	2-56	0.030	
6	.3750-.05P-.1L-DS-2A	.3125-32 UNEF-2A	0.423	0.860	0.683			
7	.4375-.05P-.1L-DS-2A	.4375-28 UNEF-2A	0.483	0.944	0.743			
8	.5000-.05P-.1L-DS-2A	.5000-28 UNEF-2A	0.545	1.032	0.805			
9	.5625-.05P-.1L-DS-2A	.5625-24 UNEF-2A	0.607	1.180	0.927	4-40	0.060	
10	.6250-.05P-.1L-DS-2A	.6250-24 UNEF-2A	0.670	1.268	0.990			
11	.6875-.05P-.1L-DS-2A	.6875-24 UNEF-2A	0.715	1.331	1.035			
13	.8125-.1P-.2L-DS-2A	.6875-24 UNEF-2A	0.812	1.470	1.132			
16	1.0000-.1P-.2L-DS-2A	.9375-20 UNEF-2A	0.981	1.708	1.301			
17	1.0625-.1P-.2L-DS-2A	.9375-20 UNEF-2A	1.060	1.822	1.382			
19	1.1875-.1P-.2L-DS-2A	1.0625-18 UNEF-2A	1.191	2.006	1.511			
21	1.3125-.1P-.2L-DS-2A	1.1875-18 UNEF-2A	1.322	2.190	1.642			

Series 801 Front and Rear Mount Panel Cutout			
Ø R	G BSC	H Holes	4X Ø H
0.423	0.390	0.096	
0.483	0.453	0.091	
0.545	0.515		
0.607	0.578		
0.670	0.640		
0.715	0.703		
0.812	0.828	0.130	
0.981	1.015	0.126	
1.060	1.078		
1.191	1.203		
1.322	1.328		

### NOTES

1. Grommet protrudes for power/combo/#8 arrangements.
2. For all #8 arrangements, add .100" to length of banding platform.
3. For all #8 arrangements, add .340" to overall length.

Dimensions in Inches (millimeters) are subject to change without notice.