

# Series 84 Mighty Mouse Stinger™ Contact Termination and Removal Tools



## Termination tools for size #28 contacts



These crimp tools perform precision eight indent crimps for gas-tight wire terminations and excellent tensile strength. Adjustment wheel has 8 settings. Ratchet mechanism prevents improper crimps. Use with bayonet-type positioners. Check calibration with M22520/3 gages. Length is 6.75 inches, weight is approx. 10 oz.

**A** Standard M22520/2-01 crimper. Use with size #28 Stinger™ Mighty Mouse contacts. Requires positioner, ordered separately.

**B** Positioner. Use with **A** crimper, ordered separately. Positioner holds contact at proper depth. Contact to remain in protective sleeve during crimping.







Figure	Part Number	Military Part Number	Daniels Part Number
A	809-015	M22520/2-01	AFM8
B	859-077	(none)	K267-4

**M**

## Stinger™ Contact tools



Tooling for Size #28 Contact System		
Tool	Glenair part Number	Reference view
Insertion Tool	859-078-000	 (shown less protective cover)
Extraction Tool With Protective Cover	859-079-000	 (shown less protective cover)
Extraction Tool Protective Cover Only (Spare/Extra)	859-079-001	
Extraction Tool Replaceable Tip (Spare/ Extra)	859-079-002	

**Notes:**

1. All tools are the same for both pin and socket contacts
2. Insertion tool is recommended for contact with O-ring seal, contacts without O-ring seal are insertable by hand, without tool
3. Insertion tool is designed for wire diameter of .035 inches maximum

Dimensions in Inches (millimeters) are subject to change without notice.