



Series 805 Mighty Mouse Triple-Start Crimp Receptacle

805-003 and 805-004 Ordering Information



Three Shell Mounting Options

Jam nut with O-ring for rear panel mounting, square flange for front or rear panel mounting, or in-line receptacles for free-hanging cables.

Gold-Plated Crimp Contacts

are held in place with beryllium copper retention clips. Contacts are removable.

Two Shell Styles: Choose integral band platform for direct attachment of a cable shield. Install a boot, or overmold a boot over the band platform. An accessory thread is available for attaching strain reliefs and backshells.

W

How To Order	
Sample Part Number	805-004 -02 NF 9-10 P A
Series (See Table I)	<p>805-003 = Receptacle with Banding Platform</p> <p>805-004 = Receptacle with Accessory Thread</p>
Shell Style (See Table II)	<p>-01 = In-line</p> <p>-02 = Square Flange Front or Rear Mount</p> <p>-12 = Square Flange Rear Mount Non-Locking Clinch Nuts</p> <p>-22 = Square Flange Rear Mount Locking Clinch Nuts</p> <p>-07 = Jam Nut for Rear Panel Mounting</p>
Shell Material and Finish	<p>C = Aluminum / Black Anodize (Non-Conductive); RoHS Compliant</p> <p>M = Aluminum / Electroless Nickel; RoHS Compliant</p> <p>MT = Aluminum / Nickel-PTFE RoHS Compliant</p> <p>NF = Aluminum / Cadmium with Olive Drab Chromate</p> <p>ZNU = Aluminum / Zinc-Nickel with Black Chromate</p> <p>Z1 = Stainless Steel / Passivated; RoHS Compliant</p> <p>ZB = Stainless Steel / Olive Drab Chromate over Cadmium</p> <p>ZC = Stainless Steel / Zinc Cobalt Alloy/Black Chromate</p>
Shell Size - Insert Arr	See Contact Arrangements Page W-3, W-6, W-8
Contact Type	<p>Connector supplied without termini. Please indicate pin or socket.</p> <p>A = Pin Connector, less termini</p> <p>B = Socket Connector, less termini</p>
Shell Key Positions (See Table III)	A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. E F = Pos. F



Table I: Series
 <p>805-003 Receptacle with Banding Platform</p>
 <p>805-004 Receptacle with Accessory Thread</p>





Table III Keyway Positions		
		
Position	A	B
Normal (A)	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°

Table II: Shell Style		
 <p>-01 In-line Receptacle</p>	 <p>-02, -12, -22 Square Flange</p>	 <p>-07 Jam Nut</p>

Dimensions in Inches (millimeters) are subject to change without notice.