




**770-008**  
**Straight Heat Shrink Boot**  
 For Use in Naval Shipboard Electronic Equipment



As Supplied



Recovered

## APPLICATION NOTES

- Please refer to the AEGIS Boot Approval document at:  
[http://www.glenair.com/navy\\_connectors/index.htm](http://www.glenair.com/navy_connectors/index.htm)

**770-008**  
**Straight Heat Shrink Boot**  
 For Use in Naval Shipboard Electronic Equipment



CSGA

**TABLE I: Size, NAVSEA Part No., and Dimensions**

| Size | NAVSEA Part No. | Ae<br>Min Dia<br>Expanded | Ar<br>Max Dia<br>Recovered | Ce<br>Min Dia<br>Expanded | Cr<br>Max Dia<br>Recovered | PO<br>±10%    |
|------|-----------------|---------------------------|----------------------------|---------------------------|----------------------------|---------------|
| 00   | 5617649         | .827 (21.0)               | .551 (14.0)                | .630 (16.0)               | .209 (5.3)                 | 5.315 (135.0) |
| 01   | 5617649-1       | .984 (25.0)               | .650 (16.5)                | .984 (25.0)               | .331 (8.4)                 | 6.024 (153.0) |
| 02   | 5617649-2       | 1.299 (33.0)              | .799 (20.3)                | 1.299 (33.0)              | .429 (10.9)                | 6.024 (153.0) |
| 03   | 5617649-3       | 1.693 (43.0)              | .902 (22.9)                | 1.693 (43.0)              | .559 (14.2)                | 6.890 (175.0) |
| 04   | 5617649-4       | 2.087 (53.0)              | 1.098 (27.6)               | 2.087 (53.0)              | .701 (17.8)                | 6.890 (175.0) |
| 05   | 5617649-5       | 2.835 (72.0)              | 1.449 (36.8)               | 2.835 (72.0)              | .949 (24.1)                | 7.244 (184.0) |

**TABLE II: Material**

| No. | Compound | Material Description      |
|-----|----------|---------------------------|
| 2   | 2010     | Low Smoke Hazard Material |

**TABLE III: Adhesive**

| Symbol | Adhesive Description               |
|--------|------------------------------------|
| W1BLK  | 120°C Zero Halogen/Hot Melt, Black |

D