



**600H005**  
**Plug and Receptacle Holder**  
**MIL-DTL-38999 Series III**



**TABLE I: Dash Number, Torque and Dimensions**

Connector Shell Size	MIN/MAX IN-LB			A Dia Max	B Dia Max	C Dim Max
	Aluminum	Composite	Stainless Steel High Vibration Applications			
<b>09, A</b>	30/40	20/25	91/101	.577 (14.7)	.438 (11.1)	1.031 (26.2)
<b>11, B</b>	30/40	20/30	115/125	.709 (18.0)	.566 (14.4)	1.031 (26.2)
<b>13, C</b>	35/45	25/35	115/125	.829 (21.1)	.678 (17.2)	1.031 (26.2)
<b>15, D</b>	35/45	25/35	139/149	.954 (24.2)	.803 (20.4)	1.031 (26.2)
<b>17, E</b>	35/45	30/40	139/149	1.107 (28.1)	.928 (23.6)	1.031 (26.2)
<b>19, F</b>	35/45	30/40	175/185	1.190 (30.2)	1.033 (26.2)	1.031 (26.2)
<b>21, G</b>	75/85	35/45	199/209	1.315 (33.4)	1.158 (29.4)	1.031 (26.2)
<b>23, H</b>	75/85	35/45	223/233	1.440 (36.6)	1.283 (32.6)	1.031 (26.2)
<b>25, J</b>	75/85	35/45	259/269	1.565 (39.8)	1.408 (35.8)	1.031 (26.2)

**APPLICATION NOTES**

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 08, 10, 12; 3/8" - Shell sizes 14 and up.
4. Composite values apply when using Glenair 600-091, 600-157 or 600-007 tools.

Dimensions in inches (millimeters) and are subject to change without notice.