


Glenair EMI Covers offer the same EMI protection as a mated connector from electromagnetic interference as a result of electromagnetic induction emitted from intended external sources such as radio transmissions or electromagnetic radiation from unintentional sources such as electric power transmission lines. These covers feature a solid one piece construction machined from your choice of aluminum, stainless steel or titanium. Standard aluminum finishes include cadmium or electroless nickel plating. Available with or without lanyard attachment. Covers are in accordance with interface dimensions for MIL-DTL-32139/3 and /4.

How to Order Nano Dual Row EMI Cover	
Sample Part Number	899-011 -25 P S J F 3 -126
Series	899-011 = Plug or Receptacle Cover
Insert Arrangement	9, 15, 21, 25, 31, 37, 41, 51, 65, 69, 85; See Dimensions Table
Body Style	P = Plug S = Receptacle
Cover Material and Finish	A1 = Aluminum Shell, Cadmium Plating S = Stainless Steel, Passivated A2 = Aluminum Shell, Electroless Nickel Plating T = Titanium, Unplated
Hardware	J = Jackscrew T = Female Thread Female threads are available on plug covers only if cover material is titanium or stainless steel.
Attachment Type	N = No Lanyard F = Stainless Steel Wire Rope, Nylon Jacket, Black, Ø .034 G = Flexible Dacron Cord, MIL-DTL-5040, Type 1, Natural, (Dia)1/16 H = Stainless Steel Wire Rope, Teflon Jacket, Black, Ø .034 K = No Lanyard/No Eyelet Attachment Point
Attachment Length	Attachment Length in Inches; Omit for No Lanyard
Attachment Diameter	See Attachment Diameter Table; Omit for No Lanyard

OPTION K




OPTION G



Attachment Diameter	
Attachment Diameter Dash No.	-098 -126 -140 -156 -167 -188 -197 -218
ID	Ø .098 (2.49) Ø .126 (3.20) Ø .140 (3.56) Ø .156 (3.96) Ø .167 (4.24) Ø .188 (4.78) Ø .197 (5.00) Ø .223/.218 (5.66/5.54)
OD	Ø .300 (7.62) Ø .300 (7.62) Ø .300 (7.62) Ø .300 (7.62) Ø .300 (7.62) Ø .300 (7.62) Ø .300 (7.62) Ø .300 (7.62)





D