

# 660-104

## Protective Cover for SMA Receptacle








### SMA Receptacle Cover



**TABLE 1 MATERIAL / FINISH**

Aluminum		Stainless Steel	
<b>M</b>	Electroless Nickel	<b>Z1</b>	Passivate
<b>NF</b>	Olive Drab Cadmium	<b>ZM</b>	Nickel-plated
<b>MT</b>	Nickel-PTFE		
<b>ZR</b>	Black Zinc-Nickel		

**TABLE 2 ATTACHMENT TYPE**




<b>D</b>	 <b>SST Bead Chain</b> .125 (3.2) diameter, size 6, -65 to +200 °C
<b>F</b>	 <b>Wire Rope, Blue Nylon Jacket</b> 6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C
<b>G</b>	 <b>Black Nylon Rope</b> Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter, -55 to +100 °C
<b>H</b>	 <b>Wire Rope, Clear FEP Jacket</b> Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C
<b>S</b>	 <b>Sash Chain</b> #8 sash chain, stainless steel. Length tolerance is ± one link .280 (71)
<b>T</b>	 <b>SST Wire Rope, No Jacket</b> Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C
<b>U</b>	 <b>SST Wire Rope, Black Polyurethane</b> Black polyurethane coating, very flexible, excellent abrasion resistance, .080" (2mm) diameter, -55 to +125 °C

660-103 protective cover fits SMA plug connectors. Aluminum, stainless steel, or composite. Stainless steel fittings. Silicone gasket.

### PART NUMBER

		660-104	Z1	D	101	-5
<b>Base P/N</b>	<b>660-104</b>					
<b>Material/Finish</b>	See Table 1					
<b>Attachment Type</b>	<b>N</b> No Attachment See Table 2 for Attachment Types					
<b>Attachment Ring</b>	Omit for Attachment Type N <b>00</b> No Ring See Table 3 for Attachment Ring Codes					
<b>Attachment Length</b>	Omit for Attachment Type N Length in One Inch Increments					

**TABLE 3 ATTACHMENT RING**

EYELET		
	<b>Code</b>	<b>Eyelet I.D.</b>
	<b>06</b>	.125 (3.2)
	<b>01</b>	.140 (3.6)
	<b>02</b>	.182 (4.6)
	<b>04</b>	.197 (5.0)
SOLID RING		
	<b>Code</b>	<b>Ring I.D.</b>
	<b>095</b>	.312 (7.9)
	<b>100</b>	.391 (9.9)
	<b>101</b>	.516 (13.1)
	<b>102</b>	.583 (14.8)
	<b>103</b>	.641 (16.3)
	<b>104</b>	.708 (18.0)
	<b>105</b>	.766 (19.5)
	<b>106</b>	.896 (22.2)
	<b>107</b>	1.016 (25.8)
SPLIT RING		
	<b>Code</b>	<b>Ring I.D.</b>
	<b>52</b>	.485 (12.3)
	<b>54</b>	.640 (16.3)
	<b>56</b>	.750 (19.1)
	<b>58</b>	.890 (22.6)
	<b>60</b>	1.015 (25.8)

