

# 660-107

## Protective Cover for TNC Plug

### TNC Plug Cover



660-107 protective cover fits TNC plug connectors. Aluminum or stainless steel, with stainless steel fittings. Silicone gasket.








### PART NUMBER

|                          |                                                                                          |          |          |            |           |
|--------------------------|------------------------------------------------------------------------------------------|----------|----------|------------|-----------|
|                          | <b>660-107</b>                                                                           | <b>M</b> | <b>H</b> | <b>095</b> | <b>-4</b> |
| <b>Base P/N</b>          | <b>660-107</b>                                                                           |          |          |            |           |
| <b>Material/Finish</b>   | See Table 1                                                                              |          |          |            |           |
| <b>Attachment Type</b>   | <b>N</b> No Attachment<br>See Table 2 for Attachment Types                               |          |          |            |           |
| <b>Attachment Ring</b>   | Omit for Attachment Type N<br><b>00</b> No Ring<br>See Table 3 for Attachment Ring Codes |          |          |            |           |
| <b>Attachment Length</b> | Omit for Attachment Type N<br>Length in One Inch Increments                              |          |          |            |           |




### TABLE 1 MATERIAL / FINISH

| Aluminum  |                    | Stainless Steel |               |
|-----------|--------------------|-----------------|---------------|
| <b>M</b>  | Electroless Nickel | <b>Z1</b>       | Passivate     |
| <b>NF</b> | Olive Drab Cadmium | <b>ZM</b>       | Nickel-plated |
| <b>MT</b> | Nickel-PTFE        |                 |               |
| <b>ZR</b> | Black Zinc-Nickel  |                 |               |

### TABLE 2 ATTACHMENT TYPE

|          |                                                                                                                                                                                                                                                   |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>D</b> | <br><b>SST Bead Chain</b><br>.125 (3.2) diameter, size 6, -65 to +200 °C                                                                                       |
| <b>F</b> | <br><b>Wire Rope, Blue Nylon Jacket</b><br>6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C                     |
| <b>G</b> | <br><b>Black Nylon Rope</b><br>Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter, -55 to +100 °C                                           |
| <b>H</b> | <br><b>Wire Rope, Clear FEP Jacket</b><br>Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C           |
| <b>S</b> | <br><b>Sash Chain</b><br>#8 sash chain, stainless steel.<br>Length tolerance is ± one link .280 (71)                                                           |
| <b>T</b> | <br><b>SST Wire Rope, No Jacket</b><br>Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C                             |
| <b>U</b> | <br><b>SST Wire Rope, Black Polyurethane</b><br>Black polyurethane coating, very flexible, excellent abrasion resistance, .080" (2mm) diameter, -55 to +125 °C |

### TABLE 3 ATTACHMENT RING

| EYELET                                                                              |            |              |
|-------------------------------------------------------------------------------------|------------|--------------|
|                                                                                     | Code       | Eyelet I.D.  |
|  | <b>06</b>  | .125 (3.2)   |
|                                                                                     | <b>01</b>  | .140 (3.6)   |
|                                                                                     | <b>02</b>  | .182 (4.6)   |
|                                                                                     | <b>04</b>  | .197 (5.0)   |
| SOLID RING                                                                          |            |              |
|                                                                                     | Code       | Ring I.D.    |
|  | <b>095</b> | .312 (7.9)   |
|                                                                                     | <b>100</b> | .391 (9.9)   |
|                                                                                     | <b>101</b> | .516 (13.1)  |
|                                                                                     | <b>102</b> | .583 (14.8)  |
|                                                                                     | <b>103</b> | .641 (16.3)  |
|                                                                                     | <b>104</b> | .708 (18.0)  |
|                                                                                     | <b>105</b> | .766 (19.5)  |
|                                                                                     | <b>106</b> | .896 (22.2)  |
|                                                                                     | <b>107</b> | 1.016 (25.8) |
| SPLIT RING                                                                          |            |              |
|                                                                                     | Code       | Ring I.D.    |
|  | <b>52</b>  | .485 (12.3)  |
|                                                                                     | <b>54</b>  | .640 (16.3)  |
|                                                                                     | <b>56</b>  | .750 (19.1)  |
|                                                                                     | <b>58</b>  | .890 (22.6)  |
|                                                                                     | <b>60</b>  | 1.015 (25.8) |

