

660-109

Protective Cover for BNC Plug

BNC Plug Cover



660-109 protective cover fits BNC plug connectors. Aluminum or stainless steel, with stainless steel fittings. Silicone gasket.

PART NUMBER

| | | | | | |
|--------------------------|--|----------|----------|------------|-----------|
| | 660-109 | M | H | 095 | -4 |
| Base P/N | 660-109 | | | | |
| Material/Finish | See Table 1 | | | | |
| Attachment Type | N No Attachment See Table 2 for Attachment Types | | | | |
| Attachment Ring | Omit for Attachment Type N 00 No Ring See Table 3 for Attachment Ring Codes | | | | |
| Attachment Length | Omit for Attachment Type N Length in One Inch Increments | | | | |

TABLE 1 MATERIAL / FINISH

| Aluminum | | Stainless Steel | |
|-----------|--------------------|-----------------|---------------|
| M | Electroless Nickel | Z1 | Passivate |
| NF | Olive Drab Cadmium | ZM | Nickel-plated |
| MT | Nickel-PTFE | | |
| ZR | Black Zinc-Nickel | | |

TABLE 2 ATTACHMENT TYPE











| | |
|----------|---|
| D |  SST Bead Chain .125 (3.2) diameter, size 6, -65 to +200 °C |
| F |  Wire Rope, Blue Nylon Jacket 6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C |
| G |  Black Nylon Rope Very flexible, good abrasion and fuel resistance, .094 (2.4) diameter, -55 to +100 °C |
| H |  Wire Rope, Clear FEP Jacket Clear FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C |
| S |  Sash Chain #8 sash chain, stainless steel. Length tolerance is ± one link .280 (71) |
| T |  SST Wire Rope, No Jacket Good flexibility, good abrasion resistance, .047 (1.2) diameter, passivated, -65 to +200 °C |
| U |  SST Wire Rope, Black Polyurethane Black polyurethane coating, very flexible, excellent abrasion resistance, .080" (2mm) diameter, -55 to +125 °C |

TABLE 3 ATTACHMENT RING

| EYELET | | |
|---|------------|--------------|
| | Code | Eyelet I.D. |
|  | 06 | .125 (3.2) |
| | 01 | .140 (3.6) |
| | 02 | .182 (4.6) |
| | 04 | .197 (5.0) |
| SOLID RING | | |
| | Code | Ring I.D. |
|  | 095 | .312 (7.9) |
| | 100 | .391 (9.9) |
| | 101 | .516 (13.1) |
| | 102 | .583 (14.8) |
| | 103 | .641 (16.3) |
| | 104 | .708 (18.0) |
| | 105 | .766 (19.5) |
| | 106 | .896 (22.2) |
| | 107 | 1.016 (25.8) |
| SPLIT RING | | |
| | Code | Ring I.D. |
|  | 52 | .485 (12.3) |
| | 54 | .640 (16.3) |
| | 56 | .750 (19.1) |
| | 58 | .890 (22.6) |
| | 60 | 1.015 (25.8) |

