


795-008P
 Panel Mount Receptacle, Pin Contacts

- Size #12 Contacts
- All-Aluminum Body
- Three to Eleven Ports
- 40 GHz SMPM Coax
- Environmental
- Scoop-Proof



Three to eleven ports. Size 12 contacts. 795-008 receptacles have machined aluminum housings and fluorosilicone grommet for environmental protection. Size 12 pin contact cavities have beryllium copper retention clips. Use with 40 GHz SMPM coax contacts (P/N 852-099, ordered separately).

CONSTRUCTION

- Shell: aluminum
- Grommet, face seal: fluorosilicone
- Jackpost: SST, passivated
- Contact retainer clip: copper alloy, unplated
- O-ring: fluorosilicone, filled with silver-plated aluminum
- EMI spring: beryllium copper, nickel plated


SPECIFICATIONS

- Operating temperature: -55 °C to +125 °C
- Shock: EIA-364-27 Condition D
- Vibration: EIA-364-28 Condition V Letter E
- Shell-to-shell resistance: 2.5 milliohms max. with ground spring option

COAX CONTACTS


*Not included with 795-008 connector.
 Sold separately.*

for Flexible Coax Cable



- See contacts reference page at the beginning of this section for compatible size #12 socket contacts

JACKPOST AND EMI SPRING



PART NUMBER


		795-008P	12-1RF3	M	E	P	C
Base P/N	795-008P						
Arrangement No.	<p><i>See Table 1</i></p> <p>12-1RF3 3 contacts 12-1RF5 5 contacts 12-1RF6 6 contacts 12-2RF5 5 contacts, two row 12-2RF7 7 contacts, two row 12-2RF9 9 contacts, two row 12-2RF11 11 contacts, two row 12-2RF13 13 contacts, two row 12-2RF15 15 contacts, two row 12-2RF17 17 contacts, two row</p>						
Finish	<p>M Electroless Nickel MT Nickel-PTFE NF Olive Drab Cadmium TZ Tin-Zinc ZR Black Zinc-Nickel</p>						
EMI Spring	<p>E EMI Spring N No Spring</p>						
Jackpost	<p>P Jackpost #8-32, Non-Removable N No Jackpost</p>						
O-ring	<p>C Conductive O-ring N No O-ring</p>						

TABLE 1 ARRANGEMENT NUMBER

Optimized for Size #12 SMPM Contacts

Cable Diameter: .150" Max

Max Frequency: 40 GHz




795-008P
 Panel Mount Receptacle, Pin Contacts


- Size #12 Contacts
- All-Aluminum Body
- Three to Eleven Ports
- 40 GHz SMPM Coax
- Environmental
- Scoop-Proof

SERIES 795 MULTI-PIN RF CONNECTORS


795-008P SINGLE ROW



Arrangement Number	A Max		B Basic		C Basic		D Max		E Max		F Max	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
12-1RF3	2.210	56.13	1.785	45.34	1.388	35.25	1.127	28.63	1.090	27.69	1.983	50.37
12-1RF5	2.840	72.14	2.375	60.33	1.900	48.26	1.516	38.51	1.440	36.58	2.590	65.79
12-1RF6	3.075	78.11	2.611	66.32	2.136	54.25	1.752	44.50	1.675	42.54	2.826	71.78



795-008P DUAL ROW



Arrangement Number	A Max		B Basic		C Basic		D Max		E Max		F Max	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
12-2RF5	2.368	60.15	1.903	48.34	1.428	36.27	1.044	26.52	.968	24.59	2.118	53.80
12-2RF7	2.604	66.14	2.139	54.33	1.664	42.27	1.280	32.51	1.204	30.58	2.354	59.79
12-2RF9	2.840	72.14	2.375	60.33	1.900	48.26	1.516	38.51	1.440	36.58	2.590	65.79
12-2RF11	3.076	78.13	2.611	66.32	2.136	54.25	1.752	44.50	1.676	42.57	2.826	71.78
12-2RF13	3.312	84.12	2.847	72.31	2.372	60.24	1.988	.49	1.912	48.56	3.062	77.77
12-2RF15	3.548	90.11	3.083	78.30	2.608	66.24	2.224	56.48	2.148	54.55	3.298	83.76
12-2RF17	3.784	96.11	3.319	84.30	2.844	72.23	2.460	62.48	2.384	60.55	3.534	89.76

