


961-001 TURBOFLEX, .125" WALL, 4500 VAC

How to Order TurboFlex®					
Sample Part Number	961	-001	-T	-G	-2
Basic No.	TurboFlex with Duraelectric D Jacket				
Wall Thickness	-001 = .125"				
Conductor Material	-T = Tin/Copper (-60 – 150°C) -S = Silver/Copper (-60 – 200°C) -N = Nickel/Copper (-60 – 260°C)				
Wire Size (See Table I)	G, H, I, J, K, L				
Duraelectric D Jacket Color	See Table II				



Voltage Ratings		
P/N	AC Voltage Rating, RMS	DC Voltage Rating
961-001	4500	6300

AWG Code	AWG	Strand / Count / AWG	Cir Mil (nom)	Ø B in. (mm)	DC Resistance @ 20°C (Ohms / 1000 ft.)			Ampacity (Amps) 40°C Ambient	
					Nickel Copper	Tin Copper	Silver Copper	Nickel Copper	Tin/Silver Copper
G	1/0	7 X 7 X 86/36	105350	.431 (10.95)	.1178	.1188	.1107	532	399
H	2/0	7 X 7 X 108/36	132300	.483 (12.27)	.0938	.0946	.0882	591	467
I	3/0	19 X 7 X 51/36	169575	.547 (13.89)	.0738	.0745	.0694	708	546
J	4/0	19 X 7 X 64/36	212800	.613 (15.57)	.0588	.0594	.0553	830	629
K	250 MCM	19 X 7 X 75/36	249375	.663 (16.84)	.0479	.0483	.0450	910	705
L	450 MCM	19 X 7 X 135/36	448875	.890 (22.61)	.0266	.0263	.0250	1320	1020

Weatherproof, halogen free, flame resistant, functional to 260°C		
0	Black	Fed-Std-595C #17038
1	Brown	[TBD]
2	Red	Fed-Std-595C #11120
3	Orange	Fed-Std-595C #12300
4	Yellow	Fed-Std-595C #13591
5	Kelly Green	Fed-Std-595C #14193
6	Blue	Fed-Std-595C #15125
7	Violet	Fed-Std-595C #17142
8	Gray	Fed-Std-595C #26270
9	White	Fed-Std-595C #17875
OG	Dark Olive Green	Fed-Std-595C #34094
DT	Desert Tan	Fed-Std-595C #33446

Consult factory for other specific Fed Std colors

AWG Code	Weight lbs/1000 ft. (nom.)	Ø A in. (mm)	Jacket wall thickness in. (mm)
G	494.50	.681 (17.30)	.125 (3.18)
H	600.00	.733 (18.62)	
I	749.50	.797 (20.24)	
J	916.00	.863 (21.92)	
K	1055.60	.913 (23.19)	
L	1806.20	1.140 (28.96)	

NOTES

1. Bend radius is 3X the outer diameter
2. Cable will be marked with "GLENAIR TURBOFLEX", wire gauge, part number, CAGE 06324.
3. Jacket thickness tolerance is ±10%