


TurboFlex® Product Selection Guide				
TurboFlex® Cable Type	Jacket Type	Part No.	Page No.	
TurboFlex® Copper Conductor (standard)	(.125" jacket)	961-001	10	
	(.093" jacket)	961-002	11	
	Duraelectric™ D accelerated UV/sunlight, fire, and ozone resistance and broad fluid and caustic chemical resistance	(.062" jacket)	961-003	12
		(.032" jacket)	961-004	13
		(2 layer jacket)	961-035	15
	Duraelectric™ D with fabric overbraiding for superior abrasion / temperature protection		961-044	16
	Duraelectric™ D with conductive braided ground shield for high-power applications		961-007	18
	Duraelectric™ L (lightweight) thin wall formula for weight savings and abrasion protection		961-041	20
Duraelectric™ K for ultra-low temperature flexibility and gamma radiation resistance		961-033	22	
Duraelectric™ F for resistance to jet fuels and oils plus low-temperature flexibility		961-051	23	
TurboFlex® Aluminum Conductor	Duraelectric™ D (see description above)	961-010	14	
	Duraelectric™ L (lightweight) thin wall formula for weight savings and abrasion protection	961-042	21	

TURBOFLEX® APPLICATION EXAMPLES




Complex, multibranch TurboFlex® aerospace power cable assembly with lightweight Duraelectric™ L jacketing and overmolding



Point-to-point TurboFlex® power cable assembly with Duraelectric™ D jacketing and overmolding in OSHA safety orange



TurboFlex® power pylon cable assembly with Duraelectric™ D jacketing



Hybrid TurboFlex® power/signal assembly with fire-resistant PTFE-glass overbraid and special Duraelectric™ D overmolding