


"ZERO-CROSSTALK" Series 806 Mil-Aero VersaLink™ Connectors



Signal and Power Contacts for Hybrid VersaLink Insert Arrangements

SERIES 806 VERSALINK CONNECTORS

SIZE 22HD SIGNAL CONTACTS FOR SERIES 806 VERSALINK HYBRID ARRANGEMENTS




Military grade. Heavy gold plating. High-density size #22HD contacts accept #22 to #30 AWG wire. Compatible with Series 806 connectors with size 22HD contact cavities. Crimp termination. Contacts are bulk packaged.

SIZE 22HD CONTACTS FOR SERIES 806 CONNECTORS

Contact Type	Wire Size AWG	Part Number	Wire Cavity		Color Band	Positioner Tool	Crimp Tool	Insert/Extract Tool
			In.	mm.				
Pin	#22-#28	850-094-1	.0335-.0355	0.851-0.902	(none)	859-147	809-015	859-163
Pin	#26-#30	850-094-2	.0229-.0245	0.582-0.622	Blue	859-148		
Socket	#22-#28	850-095-1	.0335-.0355	0.851-0.902	(none)	809-005	809-057	
Socket	#26-#30	850-095-2	.0229-.0245	0.582-0.622	Blue	809-057		

WIRE STRIP LENGTH



CONSTRUCTION

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

SPECIFICATIONS


- Operating temperature: -65°C to +200°C
- Current rating 5 A
- Crimp Tensile Strength:
- Contact Resistance:
- Silver-plated wire, 25°C (AS39029 Table 5)

Wire Size	Axial Load (lbs)
22	12
24	8
26	5
28	3
30	1.5

Wire Size	Test Current Amperes	Max. mV Drop
22	5	73
24	3	45
26	2	52
28	1.5	54
30	1	60

- Meets performance requirements of SAE AS39029/121 and /122

SIZE 20HD POWER CONTACTS FOR SERIES 806 VERSALINK HYBRID ARRANGEMENTS



Military grade. Heavy gold plating. High-density size #20HD contacts accept #20 to #24 AWG wire. Compatible with Series 806 connectors with size 20HD contact cavities. Crimp termination. Bulk packaged.

SIZE 20HD POWER CONTACTS FOR SERIES 806 CONNECTORS

Contact Type	Wire Size AWG	Part Number	Positioner Tool	Crimp Tool	Insert/Extract Tool
Pin	#20-#24	809-204	809-206	809-015 (M22520/2-01)	Metal Tip Tool: 809-203
Socket	#20-#24	809-205			Plastic Tip Tool: 809-203D

WIRE STRIP LENGTH



CONSTRUCTION

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

SPECIFICATIONS

- Operating temperature: -65°C to +200°C
- Wire accommodation: 20, 22, and 24
- Crimp Tensile Strength:
- Contact Resistance:
- silver-plated wire, 25°C (AS39029 Table 5)

Wire Size	Axial Load lbs.
20	20
22	12
24	8

Wire Size	Test Current Amperes	Max. mV Drop
20	7.5	55
22	5	73
24	3	45

- Meets performance requirements of SAE AS39029/121 and /122