


# .062" PITCH COMPLIANT PIN HD Stacker™ GSTBL top-of-stack pin connector




## MATES WITH GSTB AND GSTB (.095)



- Innovative Chevron Contact System (CCS)
- High-density layouts from 40 to 240 contacts
- Polarized insulators
- Keyed guide pin hardware for mis-mate protection



All Glenair HD Stacker™ connectors are equipped with our innovative .062" pitch high-density Chevron Contact System (CCS). Special non-orthogonal socket tines enable both higher density layouts as well as improved signal integrity. The GSTBL is equipped with pin contacts with solder-free press-fit board mounting (no socket contacts).




The GSTBL is used in top-of-stack applications that only require a single-sided mating interface. Shown: GSTBL stack-mating with GSTB.

How to Order GSTBL HD Stacker					
Sample Part Number	GSTBL	-120	-.270	-G	1
Series	GSTBL = Low Profile Stacker				
Number of Contacts	40, 80, 120, 160, 200, 240				
Pin Termination Length	.270, .300, .350, .400, .500, .600, .700, .800, .900, 1.000				
Hardware*	G = Keyed Guide Pin L = Hex Head Jackscrew (Non-Removable)				
Key Position**	G Hardware Only. Omit if Using L Hardware.				
	1	2	3	4	

\* For L hardware, connectors with 40 to 160 positions have #2-56 threads, connectors with 200 to 240 positions have #4-40 threads

\*\* For G hardware, choose Key Position 1 for best availability / fastest delivery



Number of Contacts	A		B	
	in	mm	in	mm
40	0.90	22.86	0.70	17.78
80	1.40	35.56	1.20	30.48
120	1.90	48.26	1.70	43.18
160	2.40	60.96	2.20	55.88
200	2.90	73.66	2.70	68.58
240	3.40	86.36	3.20	81.28