


## 280-028P right angle PC tail pin connectors with low profile mounting flange



Low profile right angle PC tail HiPer-D® pin connectors feature rugged machined aluminum shell and aluminum alloy cover for improved EMI protection. Contacts are non-removable, size #20 or #22. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D® features a resilient face seal for environmental protection and optional ground springs for improved resistance to electromagnetic interference. Threaded holes on the bottom of the connector allow attachment to circuit board. Contacts are potted with epoxy. Glass-reinforced thermoset epoxy insulators, fluorosilicone face seal. 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

B

How To Order	
<b>Sample Part Number</b>	<b>280-028P 4H62 ME G N A</b>
<b>Basic Part Number</b>	<b>280-028P</b>
<b>Shell Size-Contact Arrangement</b>	See Shell Size - Contact Arrangements Table
<b>Shell Finish</b>	<b>ME</b> = Electroless Nickel <b>JF</b> = Cadmium with Yellow Chromate <b>Z1</b> = Passivated Stainless Steel <b>MT</b> = Nickel-PTFE <b>Z2</b> = Gold
<b>Ground Spring</b>	<b>G</b> = Supplied with EMI Ground Spring <b>N</b> = No Ground Spring
<b>Mating Hardware</b>	<b>N</b> = No Hardware (supplied with #4-40 tapped holes) <b>P</b> = #4-40 Female Jackposts
<b>PC Tail Length</b>	<b>A</b> = .125 (3.18) Tail Length <b>B</b> = .250 (6.35) Tail Length

Shell Size - Contact Arrangements		
Shell Size-Contact Arr.	Contact Size and Qty	
	#20	#22
<b>Standard Density</b>		
<b>1S9</b>	9	
<b>2S15</b>	15	
<b>3S25</b>	25	
<b>4S37</b>	37	
<b>5S50</b>	50	
<b>High Density</b>		
<b>1H15</b>		15
<b>2H26</b>		26
<b>3H44</b>		44
<b>4H62</b>		62
<b>5H78</b>		78
<b>6H104</b>		104


Mating Hardware
<p><b>N</b> No Hardware #4-40 Female Threads in Mounting Holes</p> <p>Choose this option for rear panel mounting and order jackpost kit 289-016 separately.</p>
<p><b>P</b> #4-40 Female Jackposts</p>

Materials and Finishes	
Shell	Aluminum alloy
Contacts	Copper alloy, 50 microin. gold plated
Insulators	Thermoset epoxy
Potting Compound	Epoxy
Interfacial Seal	Fluorosilicone rubber
Hardware	300 series stainless steel

Specifications	
Current Rating	#22 5 AMPS, #20 7.5 AMPS
Test Voltage	1000 VAC RMS
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C. to +200° C.
Ingress Protection	IP 67
Shock	300 g.
Vibration, Random	43.92 g.

## 280-028P right angle PC tail pin connectors with low profile mounting flange

### 280-028P DIMENSIONS



Shell Size	A		B		C Basic		D		E	
	in	mm	in	mm	in.	mm	in	mm	in	mm
1	± .015	± 0.38	± .015	± 0.38	.984	24.99	± .005	± 0.13	± .005	± 0.13
2	1.213	30.81	.494	12.55	1.312	33.32	1.054	26.77	.389	9.88
3	1.541	39.14	.494	12.55	1.852	47.04	1.594	40.49	.389	9.88
4	2.088	53.04	.494	12.55	2.500	63.50	2.242	56.95	.389	9.88
5	2.729	69.32	.494	12.55	2.406	61.11	2.139	54.33	.501	12.73
6	2.635	66.93	.605	15.37	2.500	63.50	2.272	57.71	.563	14.30

### NOTES

1. Contacts are factory-installed, non-removable and are potted with epoxy.
2. HiPer-D<sup>®</sup> connectors are available with a wide variety of materials and finishes. See [About Series 28 HiPer-D<sup>®</sup> Shell Plating Options](#) for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
3. For panel cutout dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
4. For printed circuit board mounting dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
5. HiPer-D<sup>®</sup> connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
6. Additional electrical, mechanical and environmental specifications are listed in [HiPer-D<sup>®</sup> Product Specification](#).