




MISSION-CRITICAL  
**INTERCONNECT  
SOLUTIONS**



*Glenair*  
SIGNATURE SERIES

# Mil-Aero / Defense Interconnect Solutions

For Land, Sea, Air, and Space Applications

DECEMBER 2024

TURNKEY  
MIL-AERO/DEFENSE  
WIRE AND CABLE  
INTERCONNECT  
ASSEMBLIES



Military / Aerospace-Grade  
Wire Harnesses and Complex  
Multibranch Cable Assemblies  
Built with Glenair Signature  
Wire and Multiconductor Cable



**MIL-STAR**  
HIGH-PERFORMANCE HOOKUP WIRE AND CABLE

AEROSPACE-GRADE  
**SuperFlex**  
PCB/FLEX CIRCUIT ASSEMBLIES

**SpeedLine**  
High-Speed Protocol Cables

BLUMARK **RF**  
COAX CABLES

**FIBER KING**  
FIBER OPTIC CABLES

**turboflex**  
THE ULTRA FLEXIBLE RUGGED POWER CABLE

Glenair is laser-focused on supplying our military, aerospace, and defense customers with harsh-environment interconnect assemblies built from Glenair MIL-STAR™, SuperFlex™, BluMark RF™, SpeedLine™, TurboFlex®, and FiberKing™ wire and cable.



Supplied in bulk—any length, with no minimum order quantity—or in fully-integrated and connectorized assemblies, Glenair wire and cable brands are optimized for the highest performance in mil-aero / defense applications.

#### FAST DELIVERY AND QUALITY SINCE 1956

- 3.5 million square feet factory capacity
- Mission-critical sea, air, land, and space interconnect product focus
- Vertically-integrated, all key processes controlled in-house
- Massive inventory of material, component parts, and finished goods
- Glenair worldwide QMS: AS9100D SAE / ISO 9001 certified, and customer-audited



MIL-AERO / DEFENSE GRADE


# Mission-critical wire harnesses and interconnect assemblies: built in-house with 100% Glenair wire, cable, contacts, and connectors



## HIGH-SPEED, HIGH-FREQUENCY, HIGH-POWER • ELECTRICAL, OPTICAL, RF, AND FLEX



**MIL-STAR™** “better-than-QPL” wire interconnect assemblies



**SuperFlex™** integrated PCB flex, rigid flex, and optical flex assemblies



**SpeedLine™** high-speed protocol datalink assemblies



**BluMark RF™** high-frequency, low-loss coax assemblies



**FiberKing™** harsh-environment and inside-the-box optical assemblies




**TurboFlex®** high power, high flexibility cable assemblies

## SPECIALTY ENVIRONMENTAL ASSEMBLIES BUILT WITH GLENAIR SIGNATURE WIRE AND CABLE

In addition to conventional land, sea, air, and space interconnect assemblies with overbraiding and overmolding, Glenair is able to supply all of our signature wire and cable brands in specialty harness designs optimized for ultra-harsh environments including high-pressure subsea, high-heat and cryogenics, and space.



High-pressure subsea (Mil-qualified and commercial Oil & Gas industry) 10K PSI electrical and optical cable assemblies



Ultra High Temperature and Cryogenic (ThermaRex™) wired cable assemblies



Space-grade EMI shielded and open-wire bundle assemblies built in ISO 8 and ISO 6 clean rooms

# MIL-STAR™

## GS22759 AEROSPACE-GRADE WIRE



**MIL-STAR High-Performance Hookup Wire and Cable** Glenair has branded its GS22759 high-temperature aerospace-grade wire, and GS27500 multi-conductor cables for aerospace applications, under the MIL-STAR brand. These discrete wires and cables are built in accordance with SAE specifications with a "GS" leadoff in place of both the base specification and the part number for individual slash sheets.

MIL-STAR is a high-performance, better-than-QPL discrete wire and cable specification unique to Glenair. The brand covers both protected (inside-the-box) hookup wire, high-durability open-loom wiring, and multi-conductor shielded and jacketed M27500-type cable.

M22759 single-ended hook-up wires are the industry standard for inside-the-box mil-aero environments and are optimized for size, weight, high-temperature resistance, and low flame propagation. The hundred-plus variants of AS22759 are organized by conductor material and plating, insulation type, wire gage, and single- or dual-wall.


### MIL-STAR™ 22759 OPEN WIRE LOOM AND (PROTECTED) HOOKUP WIRES

AS22759 high-temp single-conductor 600V military and aerospace-grade wire, standard and crosslinked, lightweight single-wall and rugged dual-wall configurations.

#### CROSSLINKED (XL) ETFE SAMPLES


##### GS22759-43-22-9

- Silver-coated copper core, std. weight dual wall XL-ETFE insulation/jacket. High-temp, radiation- and fire-resistant.




##### GS22759-33-24-96

- Silver-coated copper core with XL-ETFE insulation (blue striping). High-temp, low flammability.



##### GS22759-45-12-9 (Light weight)


- Nickel coated copper core with XL-ETFE insulation. High-temp (200°C), fire and chemical resistant.



#### CONVENTIONAL FLUOROPOLYMER SAMPLES


##### GS22759-16-8-9

- Tin-coated copper core with extruded ETFE insulation. Radiation-resistant and temperature tolerant to 150°C.




##### GS22759-87-20-9 (Standard weight)

- Nickel-coated copper, PTFE/Polyimide tape-wrapped. High-temp (260°C), fire and chemical-resistant, low smoke.



##### GS22759-92-20-9 (Light weight)

- Nickel-coated copper, PTFE/thin-wall Polyimide tape-wrapped. High-temp (260°C), fire and chemical-resistant, low smoke.





# Hookup Wire for Aerospace-Grade Harness Assemblies


Better-than-QPL performance • QPL-grade batch testing and documentation

MIL-STAR™ Order Number	Conductor	Plating	Insulation	Insulation Weight	Available Wire Sizes	Temperature Rating
SAE AS22759/16-19, ETFE						
GS22759-16	Copper	Tin	ETFE	Medium	24, 22, 20, 18, 16, 14, 12, 10, 8	150°C
GS22759-17	High-Strength Copper Alloy	Silver	ETFE	Medium	26, 24, 22, 20	150°C
GS22759-18	Copper	Tin	ETFE	Light	24, 22, 20, 18, 16, 14, 12, 10	150°C
GS22759-19	High-Strength Copper Alloy	Silver	ETFE	Light	26, 24, 22, 20	150°C
SAE AS22759/32-35, XL-ETFE						
GS22759-32	Copper	Tin	XL-ETFE	Light	30, 28, 26, 24, 22, 20, 18, 16, 14, 12	150°C
GS22759-33	High-Strength Copper Alloy	Silver	XL-ETFE	Light	30, 28, 26, 24, 22, 20	200°C
GS22759-34	Copper	Tin	XL-ETFE	Normal (Dual Wall)	24, 22, 20, 18, 16, 14, 12, 10, 8	150°C
GS22759-35	High-Strength Copper Alloy	Silver	XL-ETFE	Normal (Dual Wall)	26, 24, 22, 20	200°C
SAE AS22759/41-46, XL-ETFE						
GS22759-41	Copper	Nickel	XL-ETFE	Normal (Dual Wall)	26, 24, 22, 20, 18, 16, 14, 12, 10, 8	200°C
GS22759-42	High-Strength Copper Alloy	Nickel	XL-ETFE	Normal (Dual Wall)	26, 24, 22, 20	200°C
GS22759-43	Copper	Silver	XL-ETFE	Normal (Dual Wall)	26, 24, 22, 20, 18, 16, 14, 12, 10, 8	200°C
GS22759-44	Copper	Silver	XL-ETFE	Light	28, 26, 24, 22, 20, 18, 16, 14, 12	200°C
GS22759-45	Copper	Nickel	XL-ETFE	Light	28, 26, 24, 22, 20, 18, 16, 14, 12	200°C
GS22759-46	High-Strength Copper Alloy	Nickel	XL-ETFE	Light	28, 26, 24, 22, 20	200°C

## CROSS-LINKED ETFE INSULATION

Cross-linked insulation (XL) and standard insulation are two types of dielectric materials used in wire and cable manufacturing. Cross-linking provides the following advantages:

- Improved thermal stability
- Chemical / solvent resistance
- Increased mechanical strength
- Laser-markable
- Longer service life



## RED PLAGUE MITIGATION

Glenair MIL-STAR™ high-temperature hookup wire and cable may be supplied in special 80 microinch silver-plated copper Mod Code configurations (1304A or 1304B) to combat Red Plague corrosion, a pernicious form of copper oxidation that results in the formation of red cuprous oxide ( $\text{Cu}_2\text{O}$ ) and black cupric oxide ( $\text{CuO}$ ). Red Plague corrosion can continue indefinitely, consuming conductor material and causing electrical system failures.

**Mod Code 1304B**


**RED PLAGUE MITIGATION**

# MIL•STAR™

## GS27500 MULTI-CONDUCTOR CABLE

**Glenair MIL-STAR multi-conductor 27500 type cables** are built from in-house manufactured GS22759 hookup wire, available with industry qualification as well as Glenair GS signature part numbering. GS27500 constructions for shielded and unshielded cable are:

<b>Made and tested IAW ANSI/NEMA WC 27500</b>
<b>1-15 22759 primary hook-up wires</b>
<b>Insulation types including crosslinked ETFE</b>
<b>Industry-standard and Glenair signature shielding materials</b>
<b>Standard and signature jacket compounds</b>




### MIL-STAR™ 27500 MULTI-CONDUCTOR CABLES

ANSI/NEMA WC 27500 and Glenair signature multi-conductor cables. Each series supports M22759-16 thru -46 wire types with wire count, gauge, shield, and jacket options as allowed.

#### 968-001-24SC2AR09


- 27500 type with ArmorLite or AmberStrand lightweight microfilament braided shielding



MIL-STAR GS27500 cables may be specified with signature braided shielding including ArmorLite, ArmorLite CF, and AmberStrand. The ability to supply 27500 type cable in accordance with the ANSI/NEMA standard but optimized for SWaP with lighter weight ArmorLite and AmberStrand shielding is a unique Glenair-only capability.

#### GS27500-22TF4T14


- 27500 type with GS22759-17 wire (silver-plated high-strength copper wire, ETFE insulation), and TC shielding.



This configuration of multi-conductor GS27500 cable is built with GS22759 dash 17 inner wires: silver-plated high-strength copper wire with ETFE insulation. The cable is equipped with an overall tinned-copper EMI/RFI shield and standard fluoropolymer ETFE outer jacket. The superior mechanical properties of high-strength conductors contribute to the overall safety, reliability, and mechanical strength of the cable.

#### GS27500-24SC2S23


- 27500 type with GS22759-33 wire (silver-plated high-strength copper wire, XL-ETFE insulation), and silver shielding.



This cross-linked configuration of multi-conductor GS27500 cable is built with GS22759 type dash 33 inner wires: silver-plated high-strength copper wire with cross-linked XL-ETFE insulation. Cable is equipped with an overall silver-plated EMI/RFI shield and cross-linked XL-ETFE outer jacket. This multi-conductor 27500 type cable delivers far superior thermal stability, enhanced chemical resistance, mechanical strength, and electrical properties compared to non-crosslinked versions.



**MIL-STAR GS27500 cable part numbering** replaces the “M” callout with “GS.” From left to right, how to order variables begin with the color code and shield coverage variable, in this case a dash, which indicates default 85% overall shield coverage, with white inner wires and colored stripes. Code A used in this position would denote 85% shield coverage with solid colored wire, Code C would denote 90% shield coverage with white inner wires with colored stripes. The next variable, 22 in our example, is conductor size, followed by the base wire specification (TE) indicating GS22759-16 wire is to be used in this cable buildup. Final variables include the number of inner wire conductors (2), type of overall shielding (T, for Tinned Copper), and finally jacketing material (14, indicating extruded ETFE in white).



Glenair MIL-STAR GS27500 cable may also be constructed with custom inner-conductor cable striping and customer-defined laser marking.

Multi-conductor M27500 type IAW ANSI/NEMA WC 27500							
<b>MIL-STAR Cable Sample Part Number</b>	<b>GS27500</b>	<b>-</b>	<b>22</b>	<b>TE</b>	<b>2</b>	<b>T</b>	<b>14</b>

### BETTER-THAN-QPL MIL-STAR SHIELDING OPTIONS


Glenair signature braided cable shield solutions include single and double layers of metal-clad composite microfilament AmberStrand®, microfilament nickel-clad stainless steel ArmorLite™, and ArmorLite™ CF corrosion-resistant.

MIL-STAR GS27500 SHIELDING OPTIONS		
Single Shield Code	Double Shield Code	Shield Description
<b>AM</b>	<b>AS</b>	AmberStrand®, Round
<b>AR</b>	<b>AL</b>	ArmorLite™, Round
<b>AC</b>	<b>AF</b>	ArmorLite™ CF, Round
<b>U</b>	<b>U</b>	Unshielded



# AEROSPACE-GRADE SuperFlex™ PCB/FLEX CIRCUIT ASSEMBLIES


Turnkey connectorized flex, rigid flex, and rigid PCB assemblies incorporating Glenair's broad range of innovative small form-factor circular and rectangular PC-tail connector solutions for optimized ease-of-assembly and SWaP



Flex circuits—metallic layers of traces, usually copper, bonded to a dielectric layer, like polyimide—are used to interconnect embedded electronic packages, displays, backplanes, and other PCB components. Flex and rigid-flex circuits are frequently superior to conventional wiring as they can be easily routed in three dimensions, are lighter and smaller than discrete wires, and

offer virtually unlimited flex cycles in articulated applications. Flex and rigid-flex circuits are commonly deployed within avionic LRUs and other complex electronic systems, as well as between articulating components, such as disk drive, robotic arms, and other electro-mechanical devices.


Compared with conventional wiring, compact flexible printed circuit assemblies reduce system complexity and assembly time as well as enhance reliability. Due to their low mass and high circuit density, flex circuit assemblies are less susceptible to impact and vibration damage than conventional wire harness assemblies, making them an ideal choice in missile and other reduced form-factor applications.




IPC 6012/6013 Class I, II, III,  
Types 1–4 Certified Production

Glenair recommends commercial customers specify IPC-6012/6013 standards of workmanship, which are fully supported by Glenair. Military customers may alternatively cite specifications IAW MIL-PRF-31032.

## GLENAIR SIGNATURE PC-TAIL CONNECTOR TYPES AVAILABLE IN TURNKEY FLEX ASSEMBLIES




Series MWD Micro-D and  
spring-contact AlphaLink



Series 88  
SuperFly




Series 79  
Micro-Crimp



SuperNine MIL-DTL-38999 type  
flexi with board connector




**Glenair SuperFlex** turnkey connectorized flex, rigid flex, and rigid PCB assemblies begin with our signature flex circuit fabrication and innovation. All SuperFlex assemblies are optimized with ground planes and shields, strain relief features, mounting points for improved resistance to vibration and shock, and are available in multi-layer and double-sided configurations. All terminations backpotted for compliance with conformal coating processes. Optical and electrical solutions available. Special long-length assemblies up to 12 feet.



## MULTIBRANCH SUPERFLEX ASSEMBLIES WITH GLENAIR SIGNATURE CONNECTORS

Aerospace-grade Micro-D flex assembly with NASA EEE-INST-002 screening




High-shock matched-impedance Mighty Mouse assembly with flex circuit



Aerospace-grade Series 28 HiPer-D to Series 80 Mighty Mouse I/O jumper: a tight space-constrained rectangular-to-circular solution




Dual-gang series 20 Super-Twin™ I/O connector to AlphaLink SL PCB connector



Hybrid flex/rigid flex multibranch Micro-D and Series 23 SuperNine flex assembly with discrete RF circuits



Stacked Micro-D I/O connectors with flex jumper to rigid PCB assembly




Flex circuitry is lighter, lower profile, and more flexible than cable bundles



**Fairway-Flex™**  
LONG-LENGTH FLEX ASSEMBLIES



High vibration and shock resistant rigid flex assembly with Glenair Mighty Mouse, Micro-D, and RF connections



# SpeedLine™

## High-Speed Protocol Cables

Glenair supplies a wide range of high-speed shielded twisted pair cabling for use with El Ochito®, VersaLink™, SpeedMaster™, and other of our shielded high-speed connector and contact technologies. High flexibility and high-density reduced-weight cable designs are a specialty. Glenair offers turnkey Cat 8 Ethernet, SuperSpeed USB 3.0, HDMI, SATA, and other solutions for today's most mission-critical application platforms.

Glenair SpeedLine cables are optimized for signal integrity, weight savings, flexibility, and durability. In addition, these aerospace and space-grade cables have been optimized for ease of termination and across-the-board compatibility with our broad range of high-speed contact modules and connectors.



SpeedLine™ high-speed cable assemblies such as this VersaLink cordset for DisplayPort 2.0 and USB 4 are supplied as turnkey tested solutions, ready for immediate use.


- Cat 8 Ethernet, SuperSpeed USB 3.0, HDMI, SATA, and other solutions for mission-critical applications
- Individual foil shielding around each data pair for reduced crosstalk and attenuation
- Up to 200°C high-temperature-rated cable
- Skydrol resistant, RoHS compliant versions
- Ethernet versions meet ANSI/TIA 568-C.2 Category 6A requirement up to 262 feet/80 meters
- Low-skew SuperSpeed USB data pairs have individual braided shields
- LSZH jacketing options including Duraelectric Light and polyurethane



SpeedLine™ high-speed protocol cables: shielded differential data-pair cables for high-datarate Ethernet, USB, SATA, PCIe, DisplayPort, and HDMI protocols


### 963-069-26

- 100 Ohm #26 AWG flat pair shielded cable for use with VersaLink™ connectors
- Performance up to 18 GHz
- -65 to +200 °C rated operating temperature
- FEP jacket, FEP insulation
- Dual shields: Aluminized Kapton tape and #44 AWG silver-plated copper



### 963-066-24

- 100 Ohm #24 AWG 4-pair shielded cable for use with El Ochito contacts
- Performance up to 10 Gigabit Ethernet
- -65 to +200 °C rated operating temperature
- FEP jacket, FEP insulation with PTFE tape wrap
- Outer shield: #40 AWG silver-plated copper



Glenair signature SpeedLine high-speed protocol cables are designed for direct application and use with VersaLink™, SpeedMaster™, El Ochito®, and other of our lightweight, small form-factor high-speed protocol connectors.




# Glenair Signature SpeedLine™ Cables, Shielded Contacts, and Connectors: a complete ecosystem of interconnect technologies for high-speed protocol applications in rugged aerospace-grade systems

Glenair supplies a complete ecosystem of military/aerospace-grade interconnect technology in support of every popular high-speed protocol. Downselect typically begins with protocol identification in accordance with application data rate requirements and standards. For each high-speed protocol, Glenair can supply an exactly-designed, tested, and qualified SpeedLine™ differential data cable, shielded high-speed contact insert, and a signature range of ruggedized, environmentally-sealed connector housings.

## SPEEDLINE HIGH-SPEED DATA CABLE ASSEMBLIES




Glenair SpeedLine high-speed cable assemblies for VersaLink™ include factory-terminated pigtails and double-ended jumpers as well as turnkey Series 806 Mil-Aero and Series 794 Micro-Crimp high-density solutions




Glenair SpeedLine high-speed cable assemblies for El Ocho™ include single- and double-ended jumpers, commercial protocol connector jumpers, and integrated Series 806 Mil-Aero, SuperNine®, and Series 792 Micro-Crimp


## SPEEDLINE-COMPATIBLE HIGH-SPEED DIFFERENTIAL-PAIR SHIELDED CONTACTS



Size #8 differential twinax contacts



Size #8 quadrax contacts



Size #8 El Ocho octaxial



Size #8 SpeedMaster octaxial



VersaLink differential twinax

## SPEEDLINE COMPATIBLE GLENAIR SIGNATURE HIGH-SPEED CONNECTORS



Series 806 Mil-Aero high-speed El Ocho micro miniature



SuperNine MIL-DTL-38999 "Better than QPL" high-speed El Ocho



Speed-Master™ modular 10G+ Ethernet (shown in SuperNine® packaging)



Series 792 Micro-Crimp precision-machined high-speed El Ocho

# BLUMARK RF

## COAX CABLES



**COMING SOON:  
VITA 67.3 RF ASSEMBLIES**

Fully-customizable  
SMPM and SMPs  
assemblies:  
connectors,  
shells, cables, and  
accessories

Glenair is one of just a few interconnect manufacturers that can supply turnkey RF transmission line assemblies—fully connectorized and ready for immediate use—built 100% in-house with Glenair component parts. Glenair high-frequency RF assemblies are typically used in line-replaceable units and chassis that are part of an RF data transmission chain. The rugged, environmental construction of Glenair multi-port RF connector shells and contacts, combined with our high-reliability BluMark RF coax cables, makes these turnkey transmission line solutions ideal for mission-critical air, sea, land, and space applications with exacting size, weight, and frequency requirements.

BLUMARK RF  
COAX CABLES

**GLENAIR TURNKEY RF ASSEMBLIES ARE BUILT WITH AEROSPACE-GRADE  
50 OHM LOW-LOSS COAX CABLES**



Size 047  
40 GHz



Size 086  
40 GHz




Size 130  
40 GHz



Size 160  
40 GHz



Size 200  
26.5 GHz



Size 235  
26.5 GHz



Size 300  
18 GHz

Double-Shielded • Low phase-change  
Fluoropolymer Dielectric • FEP Jacket

Triple-Shielded • Low-Loss PTFE  
Tape-Wrapped Dielectric • FEP Jacket



# TURNKEY RF and Microwave Transmission Assemblies



With Glenair signature multi-port connectors, low-loss cables, and high-frequency contacts

## BLUMARK RF™ COAX CABLES

BluMark RF 50 Ohm Coax Cables are available in seven size categories. These high-frequency, low-loss, flexible cables are suitable for radar and other aerospace applications as well as laboratory test equipment. Jacket options include FEP and radiation-resistant space-grade ETFE. Triple-shielded high-performance cables have expanded PTFE dielectric core for low loss up to 40 GHz. Application selection is based on compatibility with a particular RF / microwave connector type and size, as well as flexibility, EMI screening, weight considerations, temperature tolerance, and altitude.

### 962-032-200



50 ohm size 200 (.204" diameter, .051" conductor)  
26.5 GHz max. frequency low-attenuation cable  
-55 to +200 °C rated operating temperature  
FEP jacket, expanded PTFE dielectric, solid SPC center conductor  
Triple-shielded: Tape/foil/braid shield layers with >90 dB shield effectiveness

### 962-032-160



50 ohm size 160 (.161" diameter, .036" conductor)  
40 GHz max. frequency low-attenuation cable  
-55 to +200 °C rated operating temperature  
FEP jacket, expanded PTFE dielectric, solid SPC center conductor  
Triple-shielded: Tape/foil/braid shield layers with >95 dB shield effectiveness

### 962-032-130



50 ohm size 130 (.131" diameter, .029" conductor)  
40 GHz max. frequency low-attenuation cable  
-55 to +200 °C rated operating temperature  
FEP jacket, expanded PTFE dielectric, solid SPC center conductor  
Triple-shielded: Tape/foil/braid shield layers with >90 dB shield effectiveness

### 962-025-086



50 ohm size 086 (.104" diameter, .020" conductor)  
40 GHz max. frequency low-attenuation cable  
-65 to +165 °C rated operating temperature  
FEP jacket, LPCF dielectric, solid SPC center conductor  
Double-shielded: Tape/braid shield layers


### 962-025-047



50 ohm size 047 (.056" diameter, .011" conductor)  
70 GHz max. frequency low-attenuation cable  
-65 to +165 °C rated operating temperature  
FEP jacket, LPCF dielectric, solid SPC center conductor  
Double-shielded: Tape/braid shield layers

## 50 OHM COAX RF JUMPERS

Series GRF02 50 Ohm Coax Cable "Jumpers" are COTS, cut-to-length cable assemblies with pre-installed connectors at both ends. Turnkey RF jumpers offer excellent flexibility with a bend radius of 6mm or 1/4 in.



# FIBER KING

## FIBER OPTIC CABLES



Turnkey Optical Flex circuit assembly with rugged MT ferrule terminations

Glenair is the worldwide leader in military, aerospace, and harsh-environment fiber optic interconnect assemblies. We manufacture every element in-house, from low-loss simplex, duplex, and multi-line fiber optic cables, to precision termini, military and aerospace-grade connectors, backshells, and tools. Glenair FiberKing fiber optic cables are optimized for reliable, durable performance in military and commercial aviation, space, harsh-environment oil and gas, and multi-termination (MT ribbon) assemblies.


### FIBERKING FIBER OPTIC CABLES

- Lightweight, tight bend-radius fiber optic cable for 10Gb+ avionic networks
- Vibration, radiation, and temperature-resistant space-grade F/O designs
- Ultra harsh-environment (high-pressure, high-temp, water-blocking) oil & gas industry fiber optic cable assemblies
- Ruggedized fiber optic ribbon cable for multi-fiber termination (MT) applications

# TURNKEY Fiber Optic Cables and Harnesses



For rugged mission-critical applications



## THE FIBERKING MIL-AERO (MA) ECOSYSTEM

The FiberKing Mil-Aero (MA) Ecosystem is a complete flight-grade fiber optic interconnect solution for demanding military and commercial aerospace applications. This complete 10Gb+ low-loss fiber optic solution includes single- and multimode stepped and graded-index cables in simplex, duplex, and multi-line configurations. Glenair SuperNine and Glenair Front Release (GFR) fiber optic connectors are Glenair's signature offerings for high-speed, high datarate avionic networks. Cables and connectors are qualified to strict aviation industry standards for vibration, shock, moisture, and LSZH, and are rated to maximum optical loss (dB / km) at 850 nm  $\leq$  5.0 and at 1300 nm  $\leq$  3.0. Multimode cables are OM4 graded-index. Singlemode cables are OS1 stepped-index.



Hybrid optical / electrical assembly for weight reduction in a high-speed datalink application



Harsh environment overmolded MIL-DTL-38999 Series III type composite



High-density Next-Generation (NGCON) fiber optic harness assembly



Specialized MT ribbon fiber low-profile molded breakout capabilities



Cable reels and field-deployment technologies for both Glenair GFOCA and Eye-Beam™ GMA fiber optic systems



GFOCA I/O-to-board assembly with overbraiding for mechanical protection



Inside-the-box MIL-DTL-38999 type I/O connector to board cable harness



# turboflex

THE ULTRA FLEXIBLE RUGGED POWER CABLE




TURNKEY  
**turboflex**  
Flexible Cable Assemblies

TurboFlex is an ultra-flexible and rugged power cable solution—ideal for high-voltage electrical distribution and propulsion applications such as battery plant-to-inverter-to-electric motor cables for eVTOL aircraft. Constructed from rope-lay configuration copper or aluminum wire and jacketed with Glenair signature Duraelectric insulation, TurboFlex cables are optimized for use in an ecosystem of Glenair signature contact and connector technologies. Turnkey connectorized or lugged cable assemblies – fully tested and ready for immediate use – provide reliable high-temperature tolerant performance up to 4500 VAC.



◀ Duraelectric™ is the high-performance TurboFlex® jacketing material. Different compounding formulas are optimized for weight savings, radiation resistance, ultra low temperatures, conductivity, and immersion in chemical or caustic fuels. Available in a broad range of colors including safety orange.

## STANDARD TURBOFLEX R VS. TURBOFLEX M



TurboFlex cables are jacketed with Duraelectric insulation, which contributes significantly to the flexibility of the product. Available wire cores include rope-lay (standard) for maximum flexibility, and M22759 wire (TurboFlex M) with the flight-heritage of a mil-spec core and a slightly larger bend radius, but far superior flexibility compared to standard M22759 wire.

Standard M22759  
mil-spec wire

TurboFlex M:  
mil-spec core,  
Duraelectric  
jacket

Ultra-flexible  
TurboFlex  
rope-lay wire

# TurboFlex ultra-flexible power distribution cable



## Technical overview

### TURBOFLEX CABLE APPLICATION EXAMPLE



This multibranch TurboFlex power and data interconnect assembly for a ruggedized defense application demonstrates the remarkable flexibility and minimal bend radius of large form-factor (up to 450 MCM) TurboFlex cable. Example shown features UV- and chemical-resistant Duralectric jacketing in FED-STD 595C Safety Orange.

### ABOUT TURBOFLEX WITH DURALECTRIC™ D JACKETING

Duralectric™ D is a Glenair Signature elastomeric material used in wire insulation, cable and conduit jacketing, overmolding, and shrink boots. Glenair TurboFlex high-flexibility power distribution cables are supplied with Duralectric jacketing in different wall thicknesses, as well as “tell-tale” dual-layering.

TurboFlex core conductors are available in three aerospace-grade material and temperature configurations:

- T = Tin/Copper (-60° – 150°C),
- S = Silver/Copper (-60° – 200°C)
- N = Nickel/Copper (-60° – 260°C)

A signature configuration of TurboFlex is available with high-temperature shielding and lightweight aluminum conductors.

DURALECTRIC™ D PHYSICAL PROPERTIES		
Property	Typical Result	Test Method
Hardness, Shore A	60	ASTM D2240
Tensile Strength, psi	1100	ASTM D412
Elongation, %	500	ASTM D412
Tear Strength, Die B, ppi	150	ASTM D624
Low Temperature Impact at -65°C	Pass/No Cracks	ASTM D2137
Accelerated UV/Sunlight Resistance, 53 yr. Equiv. Exposure	Pass/Excellent	IEC 60068-2-5
Ozone Resistance	Pass/No Cracks	ASTM D1149
Zero Halogen	Pass	IEC 754-1

DURALECTRIC™ D ELECTRICAL PROPERTIES		
Property	Typical Result	Test Method
Dielectric Strength, kV/mm	19	ASTM D419
Comparative Tracking Index, VAC	> 600	ASTM D3638

DURALECTRIC™ D FIRE RESISTANCE PROPERTIES	
Property	Typical Result
<b>Flammability</b>	
Oxygen Index, %	45
FAR 25.853, 12 Second Vertical	Pass
FAR 25.853, 60 Degree	Pass
FAR 27.1365 b,c	Pass
BSS7230 Method F2	Pass
IEC60614-1	Pass
EN60695-2-12, 850°C Glow-Wire	Pass
UL1685 FT4/IEEE1202	Pass
<b>Smoke Density</b>	
BSS7238	Pass
NES 711	Pass
EN 60695-2-11	Pass
UL1685 FT4/IEEE1202	Pass
<b>Combustion Toxicity</b>	
BSS7239	Pass
NES 713	Pass
SMP800 C	Pass

### GENERAL DURALECTRIC D PERFORMANCE SUMMARY

- Service Temperature Range: -65°C to 260°C
- Fire Resistant and Low Smoke-Zero Halogen (LSZH)
- RoHS materials
- Resistant to common aerospace, military and industrial fluids
- UV resistant





MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Multiport USB hubs,  
cables, and peripheral  
device manager for  
soldier-worn power /  
data network applications



JTAC-TOUGH™

# STAR-PAN™ +

Relentless, ongoing innovation in baseline  
warfighter power and connectivity solutions

The Glenair STAR-PAN™+ data hub and power distribution system has evolved as the baseline warfighter power and data hub of choice—particularly in Joint Terminal Attack Controller (JTAC) applications. STAR-PAN™+ represents over a decade of soldier power and data hub innovation—improving situational awareness, surveillance, intelligence and reconnaissance while optimizing power monitoring, conditioning, and distribution performance. Importantly, all STAR-PAN™+ technologies are designed for optimal size, weight, power, and ruggedized mil-spec performance with battle-tested environmental and EMC sealing and shielding.



STAR-PAN™+ MISSION MANAGER  
Plug-and-play EUD / USB  
peripheral data exchange device

- Versatile 2, 4, and 6-port high-speed hub configurations
- Compatible with USB 1.1, USB 2.0, and SMBus
- Embedded power charging/conditioning electronics in all designs
- Smart power monitoring for longer mission life
- Robust circuit protection
- Sealed IAW the MIL-STD-810 harsh-environment standard
- New MISSION MANAGER for on-the-fly device integration to soldier C4ISR networks

Glenair's Tactical Interconnect Solutions team is backed by six decades of proven, made-in-America interconnect industry performance in service of US and NATO armed forces.



# JTAC-TOUGH™ STAR-PAN™ + Scalable Soldier Networks




Powering soldier connectivity and C4ISR mission success  
with the world's most widely deployed power and data hub system

## STAR-PAN™ + LIGHT FOR STANDARD SOLDIERS



- 1 designated host / EUD port
- 1 battery cable / port
- 1 designated peripheral cable / port (expandable for radio use with adapter cable)

## STAR-PAN™ + II FOR ADVANCED SOLDIERS




- 1 designated host/EUD port
- 1 designated radio peripheral port
- 1 expandable PAN port for up to two USB peripherals

## STAR-PAN™ + IV FOR TACTICAL MISSION SPECIALISTS



- 1 designated host/EUD port
- 1 designated radio peripheral port
- 3 PAN receptacles for up to four peripherals

## STAR-PAN™ + VI FOR JTAC / MISSION COMMANDERS



- 1 designated host/EUD port
- 2 designated radio peripheral ports
- 4 PAN receptacles for up to four peripherals

## OPEN-SYSTEM NETWORK SUPPORT FOR THE COMPLETE RANGE OF C4ISR DEVICES



Radios



Batteries




Targeting



Video



GPS



Host / EUD

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Ten-port base station  
hub with universal  
device charging and  
data uplink capabilities



# STAR-PAN™ X BASE STATION

Warfighter walk-on, walk-off  
connectivity and charging device for  
vehicle and other transport platforms

Integration of soldier C4ISR capabilities on an existing fleet of land, air, and maritime platforms is proving to be a challenge for many NATO members. STAR-PAN™ X 10-Port Base Station is a baseline multi-port data and power hub for platform-based soldier power and C4ISR integration. STAR-PAN X 10-port Base Station supports USB 3.2 Gen 1 high-speed data rates and 8 Amp power delivery. The unit allows soldiers to directly connect portable soldier power and data systems to the transportation platform's network for charging and data sharing—enabling soldiers to refresh critical battery power and access real-time BMS information during transport in a vehicle, helicopter, or vessel.

STAR-PAN X incorporates an embedded MISSION MANAGER with upgraded processing power enabling it to act as a tactical edge computing device running any Battlefield Management System (BMS). STAR-PAN X incorporates all STAR-PAN + standard features as well as select next-generation features including Universal Power Ports, an expanded capability Host / EUD port, and full support for USB 3.2 Gen 1 peripherals.

#### STAR-PAN + STANDARD FEATURES

- Compliance to both US and NATO STANAG 4695 connector interfaces
- Smart battery power management, built-in SMBus to USB conversion
- BMA-agnostic hardware
- Hot-swappable power sourcing, radio-supplied backup power support
- Water immersion IAW MIL-STD-810, IP67-rated dust/water resistant
- Intuitive equipment hookup and operation

# WARFIGHTER-TOUGH STAR-PAN X Base Station



Portable base station unit for convenient  
vehicle-to-soldier data uplink and charging

## SPECIFICATIONS

- **PAN ports for up to ten soldier devices**
- **HDMI and Ethernet ports**
- **Integrated STAR-PAN MISSION MANAGER functionality**
- **Two USB 3.0 ports**
- **Three Universal Power Ports**
- **Glenair power port management**
- **Smart battery charging from auxiliary power**
- **Up to 5A battery power per port, 20A system total**
- **Up to 2A 5 Volt VBUS power per port, 10A across all ports**
- **Precision-machined construction, integrated connectors**

## STAR-PAN X BASE STATION APPLICATIONS


- **Armored personnel carriers**
- **Land and air troop transports**
- **Landing craft and other naval vessels**
- **Command posts and shelters**

## STAR-PAN X CABLE PART NUMBERS

BB259 BATTERY CABLE ADAPTER	<b>TS8-496</b>
AC PWR SUPPLY CABLE ADAPTER	<b>TS8-497</b>
USB 3.0 CABLE ASSEMBLY	<b>TS1-039</b>
CAT 5E ETHERNET CABLE	<b>TS1-040</b>
HDMI TYPE A CABLE ASSEMBLY	<b>TS1-041</b>
USB 2.0 DONGLE	<b>TS3-001</b>
GENERAL-PURPOSE EXTENSION CABLE	<b>TS1-069</b>

## OVERVIEW

STAR-PAN X 10-Port Base Station is a multi-port data and power hub for platform-based C4ISR integration. STAR-PAN X 10-port Base Station provides the same NATO standard interconnect interface as soldier-worn STAR-PAN systems, making it completely interoperable with the existing portfolio of cables and adapters and allowing easy soldier interconnection to the platform's data and power network. With STAR-PAN X, dismounted soldiers can connect to the vehicle power and data accessing on-board radios and sensors via a single cable connection and/or access data through the WiFi network when operating in the vicinity of the vehicle.



**INTEROPERABLE**  
**NATO STANAG 4695**  
Soldier Power Connectors

**STAR-PAN X Base Station**  
Next-generation vehicle network interface design includes HDMI, Ethernet, and USB 3.0 ports, plus three Universal Power Ports.



USB 3.0 Cable Assembly  
TS1-039



Cat5E Ethernet Cable Assembly  
TS1-040



HDMI Type A Cable Assembly  
TS1-041



AC Power Supply Adapter Assembly  
TS8-497



USB 2.0 Dongle  
TS3-001



MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Next-generation USB-C  
warfighter power and  
data hub with fast-  
charging universal  
8 Amp power ports



WARFIGHTER-TOUGH

# STAR-PAN™ NG

Next-Generation STAR-PAN Multiport USB Hub,  
Cable, and Power Management Systems

Glenair's next-generation power and data hub upgrade from the baseline STAR-PAN + series incorporates a broad range of new capabilities in direct response to requests from JTACs, special operations forces, mission commanders, and other military specialists. STAR-PAN NG innovations have resulted in higher current-carrying capabilities, greater versatility in power input support, and real-time plug-and-play USB device integration. Other advanced features include:

- A new 8A per-pin power connector design in the same dimensional package as our original 5 amp series 807 NATO STANAG 4695 push-pull connector. The new connector design features a retractable pin number 7 for backward-compatibility to legacy devices.
- STAR-PAN + hubs utilize dedicated power ports for battery power, auxiliary power, and radio power. New STAR-PAN NG Universal Power Ports (UPP) may be used interchangeably for any format of input or output power. The Universal Power Port interface supports both higher voltage input power and managed 5V output power to charging devices.
- STAR-PAN NG now incorporates an advanced host port with native USB-C "negotiation" and power integration—meaning power pin assignments are in conformance with the new standard, are backward-compatible to previous USB iterations, and deliver higher overall power levels. Daisy chaining of multiple EUD devices for power input is also enabled via the new host port and circuit board.
- Ongoing support of evolving USB protocols requires keeping pace with higher data rates, such as the new USB 3.2 Gen 1 5Gbps standard. STAR-PAN X Base Station, our 10-port "walk-on, walk-off" vehicle / soldier hub features board upgrades and interconnect interfaces in accordance with this new data rate standard.



- Versatile 1, 2, 3, and 4 PAN port-equipped hub configurations
- Universal Power Ports with embedded power charging
- Integrated MISSION MANAGER for plug-and-play device integration
- Circuit board level USB-C power integration and delivery
- Precision-machined hub bodies, IAW MIL-STD-810 harsh-environment, IP67 dust/water resistant
- Support for 5Gb/s data transmission (STAR-PAN X Base Station only)
- Standard NG solutions and custom configurations

Export of STAR-PAN™ outside of the U.S. is controlled by the U.S. Department of Commerce Export Administration. See individual product pages for details. Consult factory for technology / hardware licensing information.

# WARFIGHTER-TOUGH STAR-PAN NG



Next-generation multiport USB hub, cable, and power management systems with 8 amp power and USB-C integration

## STAR-PAN NG SOLDIER HUB SELECTION GUIDE



**STAR-PAN NG 1/2    P/N TS2-011**  
Our smallest hub with one EUD port, one pan port and two universal power ports



**STAR-PAN NG 2/2    P/N TS2-012**  
The next step up with one EUD port, two pan ports and two universal power ports



**STAR-PAN NG 3/3    P/N TS2-013**  
Next-generation design with one EUD port, three pan ports and three universal power ports



**STAR-PAN NG 4/4    P/N TS2-014**  
Next-generation design with one EUD port, four pan ports and four universal power ports

## STAR-PAN NG HUB SELECTION GUIDE

Part No.	Hub	Description
<a href="#">TS2-011</a>	STAR-PAN NG 1/2	1X HOST; 1X PAN; 2X UPP, no PPS on HOST
<a href="#">TS2-012</a>	STAR-PAN NG 2/2	1X HOST; 2X PAN; 2X UPP
<a href="#">TS2-013</a>	STAR-PAN NG 3/3	1X HOST; 3X PAN; 3X UPP; w/ Charging
<a href="#">TS2-014</a>	STAR-PAN NG 4/4	1X HOST; 4X PAN; 4X UPP; w/ Charging
<a href="#">TS2-022</a>	STAR-PAN NG 2/2 WITH MISSION MANAGER	PORTS 1X EUD;2X PAN; 2X UPP MM32
<a href="#">TS2-023</a>	STAR-PAN NG 3/3 WITH MISSION MANAGER	PORTS 1X EUD;3X PAN; 3X UPP MM64
<a href="#">TS2-024</a>	STAR-PAN NG 4/4 WITH MISSION MANAGER	PORTS 1X EUD;4X PAN; 4X UPP MM64



# Tactical Cable Assemblies

STAR-PAN™+, STAR-PAN™ X, and STAR-PAN™ NG compatible

## GENERAL-PURPOSE STAR-PAN™ SYSTEM CABLES



NETT Warrior (C1) extension cable



2-port hub expansion cable



Radio port-to-PAN port adapter cable

## STAR-PAN™ PERIPHERAL DEVICE CABLES



TacROVER-P SIR 2.5 video cable



Radio adapter cable for STAR-PAN IV



PAN port to USB-A adapter cable



DAGR GPS and micro DAGR-V cable



TacROVER-P SIR 2.0 cable



PLRF-15C/25C laser range finder cable

## STAR-PAN™ RADIO DATA / POWER CABLES AND ADAPTERS



RT-1922 Microlight  
SADL radio Cable



AN/PRC-117G  
radio cable



AN/PRC-161 BATS-D  
radio adapter



AN/PRC-148  
radio adapter



AN/PRC-152A  
radio adapter



Harris RF-7850M  
sync serial adapter



# SMALL FORM-FACTOR Tactical Soldier Interconnect Cable Assemblies



With Series 807 Mighty Mouse NW push-pull connectors  
NWPAN-WP-20210223 approved · NATO STANAG 4695 interoperable

## HARSH ENVIRONMENT OVERMOLDED



Overmolded breakout assembly featuring 100% Glenair content; a true turnkey solution



Multibranch cable assembly with Glenair Mighty Mouse, HiPer-D M24308 and customer-supplied power connector



Turnkey overmolded GPS cable assembly with integrated switch



Environmental cable with Glenair Series 804 Mighty Mouse, Series 79, and RF Coax terminations

## ULTRAFLEXIBLE FABRIC OVERBRAID



Non-environmental aircraft cable with integrated circuit breakout box and Mighty Mouse 807 push-pull connectors



Heads-up display (HUD) cable with custom Series 807 Mighty Mouse and low-profile cable routing



Military jet jumper cable with user-serviceable backshells and fabric overbraid for mechanical protection



Hybrid Mighty Mouse and Micro-D aircraft pilot helmet cable assembly

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Series 807 Mighty Mouse NW  
micro miniature connectors  
for dismounted soldier battery  
charging, radio, and PAN  
applications, NSN stock-listed.



**Nett Warrior**

NWPAN-WP-20210223

**APPROVED**

INTEROPERABLE

**NATO STANAG 4695**

Soldier Power Connectors

PUSH-PULL QDC

## Nett Warrior Qualified Power and Data Connectors

Today's warfighters demand quick battery charging and reliable radio operation. Glenair pioneered the original 6-pin Nett Warrior connector, as well as a second-generation 7-pin series with USB-C power integration and delivery. Now Glenair is introducing a signature 10 Amp Crown Ring contact-equipped version for higher-current applications that easily integrates into US / NATO, Nett Warrior, and STAR-PAN+ hub and cable systems.

Glenair STAR-PAN NG hubs and cables—now equipped with 10 Amp Crown Ring contact receptacles—are smart devices capable of managing next-generation high-power equipment as well as lower-power legacy devices.



### SERIES 807 MIGHTY MOUSE NW CONNECTOR LINE

All designs backward-compatible  
with current and legacy Nett Warrior  
hardware

- **Original 6-pin Nett Warrior plugs and receptacles**
- **Backward-compatible 7-pin series with USB-C power integration and delivery**
- **New 10 Amp receptacles for higher-current soldier battery, radio, and PAN C4ISR equipment**
- **Glenair Signature Mighty Mouse 807 NW connectors are available in pigtail and point-to-point cables for all US/NATO soldier C4ISR devices**



# US ARMY AND NATO QUALIFIED Nett Warrior Connectors



For STAR-PAN hub systems, Nett Warrior C4ISR hardware,  
next-gen and legacy radios and batteries




QUALIFIED FOR USE WITH  
ALL STAR-PAN + AND STAR-PAN NG  
POWER / DATA HUBS




## MATERIALS / FINISH

- Shell: Al alloy / ZNU plated
- Contacts: Cu alloy / Au plated
- Insulators: Rigid dielectric
- O-rings: Fluorosilicone


### Series 807 NW Nett Warrior Connector Insert Arrangements



**Original NSN-Listed 6-Pin  
(Nett Warrior Program /  
NATO STANAG 4695 Approved)**



**Backward-Compatible  
7-Pin USB-C Power Series**



**10-Amp STAR-PAN NG Series  
6-6 and 6-7 Arrangements**

## SERIES 807 MIGHTY MOUSE NW CONNECTOR LINE: HOW-TO-ORDER



In-line  
cable plug



Panel-  
mount  
plug



In-line cable  
receptacle



Panel-  
mount  
receptacle

Series 807 NW Plugs (6 pin)	Crimp	PC Tail	Solder Cup	In-Line	Rear Mount Jam Nut	Front Mount Jam Nut
<a href="#">8070-1676-06ZNU6-6PY</a> <a href="#">NSN 5935-01-659-5575</a>	X			X		
<a href="#">807-871-06ZNU6-6PY</a>	X			X		
<a href="#">807-309-06ZNU6-6PY</a>			X	X		
<a href="#">8070-1153-07ZNU6-6EC</a>			X		X	
<a href="#">8070-1153-07ZNU6-6PC</a>		X			X	
<a href="#">8070-1153-00ZNU6-6EC</a>			X			X
<a href="#">8070-1153-00ZNU6-6PC</a>		X				X
Series 807 NW Receptacles (6 socket)	Crimp	PC Tail	Solder Cup	In-Line	Rear Mount Jam Nut	Front Mount Jam Nut
<a href="#">8070-1675-01ZNU6-6SY</a> <a href="#">NSN 5935-01-659-4090</a>	X			X		
<a href="#">8070-1675-07ZNU6-6SY</a>	X				X	
<a href="#">8070-1675-00ZNU6-6SY</a>	X					X
<a href="#">807-874-01ZNU6-6SY</a>	X			X		
<a href="#">807-874-00ZNU6-6SY</a>	X					X
<a href="#">807-874-07ZNU6-6SY</a>	X				X	
<a href="#">807-348-01ZNU6-6SY</a>			X	X		
<a href="#">807-216-07ZNU6-6SY</a>			X		X	
<a href="#">807-216-01ZNU6-6SY</a>			X	X		
<a href="#">807-216-00ZNU6-6SY</a>			X			X
<a href="#">807-216-07ZNU6-6DY</a>		X			X	
<a href="#">807-216-01ZNU6-6DY</a>		X		X		
<a href="#">807-216-00ZNU6-6DY</a>		X				X
Series 807 NW Plugs (7 pin)	Crimp	PC Tail	Solder Cup	In-Line	Rear Mount Jam Nut	Front Mount Jam Nut
<a href="#">8070-1676-06ZNU6-7PY</a>	X			X		
<a href="#">807-871-06ZNU6-7PY</a>	X			X		
Series 807 NW Receptacles (7 socket)	Crimp	PC Tail	Solder Cup	In-Line	Rear Mount Jam Nut	Front Mount Jam Nut
<a href="#">8070-1675-01ZNU6-7SY</a>	X			X		
<a href="#">8070-1675-07ZNU6-7SY</a>	X				X	
<a href="#">8070-1675-00ZNU6-7SY</a>	X					X
<a href="#">807-874-01ZNU6-7SY</a>	X			X		
<a href="#">807-874-00ZNU6-7SY</a>	X					X
<a href="#">807-874-07ZNU6-7SY</a>	X				X	
<a href="#">8070-1299-ZNU6-7DY</a>		X				X
Series 807 NW Receptacles (10 Amp)	Pigtail Assembly	PC Tail	Solder Cup	In-Line	Rear Mount Jam Nut	Front Mount Jam Nut
<a href="#">8071-6924</a>	X			X		
<a href="#">8070-3151-07ZNU6-6SY</a>		X			X	



MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS






## Mighty Mouse SealTac™ Spring Contact Push- Pull Connectors and Jumpers



The Mighty Mouse Series 86 SealTac is a durable, environmentally-sealed push-pull connector with outstanding user ergonomics. Receptacle target-contact designs are fully sealed, easy to maintain and clean, and immersible to 30 PSI / IP68 in the unmated condition. Spring pin contacts (plug side) are rated to 2 Amps and can withstand virtually unlimited mating cycles.

- High-durability unlimited life-cycle performance
- 30 PSI open-face / IP68-level sealing (box side)
- Ergonomic keyed push-pull mating
- High-density micro miniature form factor
- Maintenance-free spring contact inserts
- Integrated EMI/RFI ground spring and shield termination band porch
- High vibration and shock resistant
- Full qualification testing complete and available

### SHELL SIZE / CONTACT ARRANGEMENTS


		
<p>06-7 shell size 6, 7 contacts</p>	<p>07-10 shell size 7, 10 contacts</p>	<p>08-19 shell size 8, 19 contacts</p>

# SERIES 86 SealTac Tactical Push-Pull Connectors



Spring-pin equipped Mighty Mouse harsh-environmental


## SERIES 86 SEALTAC APPLICATIONS



C4ISR soldier devices



Rugged computers and hand-helds



Power and data hubs



Tactical communications gear



Helmet quick-disconnects

## CONNECTOR SELECTION GUIDE

### IN-LINE RECEPTACLES



#### 860-051-01

Series 86 spring contact push-pull in-line receptacle for cable applications

### IN-LINE PLUG



#### 860-050-06

Series 86 target contact push-pull in-line cable plug

### JAM-NUT PLUG



#### 860-050-07

Series 86 target contact push-pull jam-nut mount plug

### CABLE JUMPER Receptacle-to-receptacle



#### 861-001

Series 86 spring contact push-pull receptacle-to-receptacle overmolded cable jumper

### CABLE JUMPER Plug-to-plug



#### 861-002

Series 86 target contact push-pull plug-to-plug overmolded cable jumper

### CABLE JUMPER High-speed HDMI



#### 861-003

Series 86 target contact push-pull plug or spring contact push-pull receptacle-to-HDMI overmolded cable jumper

### CABLE JUMPER High-speed USB 3.0



#### 861-004

Series 86 target contact push-pull plug or spring contact push-pull receptacle-to-USB 3.0 overmolded cable jumper

## SERIES 86 SEALTAC™ PERFORMANCE SUMMARY

	Performance	Specification
DWV	500 Vac	EIA 364-20
IR	5 GΩ, 200 Vdc	EIA 364-21
Temperature Range	-55°C / +125°C	
Contact Ω	40 mΩ	EIA-364-23 (26 AWG wire included)
Durability	2500 cycles min	EIA-364-09
Mating Force	8 lbs (size 06) 12 lbs (size 08)	EIA-364-13
Random Vibration		MIL-STD-810H, method 514.8, Annex E, figure 514.8E-1. One hour each axis, longitudinal and perpendicular axes
Shock		Mil-Std-810, method 516, Procedure I (40 G's, 11ms). 3 shocks X 3 axes X 2 directions = 18 shocks
Water Immersion	30 psi, 30 minutes, 100 MΩ min	EIA 364-21, mated and unmated (open face)



MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Mighty Mouse micro  
miniature connector series  
for optimized SWaP




Mighty Mouse vs. 38999: less than  
half the size and weight.

**Mighty Mouse connectors:**  
Reducing the size and weight  
of tactical interconnect systems  
for over 25 years. The most  
widely deployed mil-aero micro  
miniature circular in the world.

- 8 coupling styles and 67 contact arrangements from 1 – 130 contacts
- MIL-DTL-38999 caliber performance
- Size #23, #22, #20, #20HD, #16, #12, #8 signal, power, RF, and high-speed contacts
- Discrete connectors and turnkey cable assemblies

#### FULL RANGE OF SUPPORTED CONTACTS, 67 CONTACT ARRANGEMENTS



67 arrangements,  
from 1–130 contacts



# SERIES 80 MICRO MINIATURE Mighty Mouse Connectors and Cables



Awesome performance, itty-bitty package

## CHOOSE FROM 8 DIFFERENT COUPLING DESIGNS



Series 800  
UN thread



Series 801  
double-start ACME thread



Series 802  
AquaMouse UNEF thread



Series 803  
bayonet coupling



Series 804  
quick-disconnect



Series 824  
locking quick-disconnect



Series 805  
triple-start thread, size #23  
contact layouts



Series 806  
modified triple-start, size #22HD  
and #20HD layouts

## AVAILABLE MIGHTY MOUSE CONNECTOR CLASSES



IP67  
environmental



Glass-to-metal seal  
hermetic



**CODE RED**  
Lightweight hermetic



EMI/RFI  
Filter



EMP Transient Voltage  
Suppression



Bulkhead feed-thrus and  
penetrators



Sav-Con<sup>®</sup>  
connector savers



High-frequency  
RF / Microwave



High-speed  
Ethernet



Single- and multimode  
fiber optic

## AVAILABLE NEXT-GENERATION TACTICAL CONNECTOR SERIES



Low-profile COBRA  
right-angle



MouseBite spring-contact  
series with thumb lock



Mighty Mouse Series 807  
Nett Warrior











Mighty Mouse 3.2  
USB-C Gen 1



Mighty Mouse not small enough?  
Meet the toughest, smallest, and  
highest-speed connector we've  
got—ideal for soldier-wearable  
C4ISR equipment.

- Push-pull version with high / low force release option
- Threaded version for secure mating
- Hybrid contact system
- First mate / last break power contacts
- Layouts and contact spacing optimized for high-speed

PRINTED CIRCUIT BOARD PLUG AND RECEPTACLES

QUICK-DISCONNECT						THREADED	
							
Right Angle, Rear Panel Mount	Right Angle, Rear Panel Mount, PCB Mounting Holes	Vertical, Rear Panel Mount	Vertical, Rear Panel Mount, PCB Mounting Holes	Vertical, Rear Panel Mount, Ground Pins	Vertical Plug, Rear Panel Mount	Vertical, Rear Panel Mount	Right Angle, Rear Panel Mount



SERIES 88

# SuperFly® Nano miniature Soldier System Connectors and Cordsets



Tactical nano miniature connectors and cables

## NANO MINIATURE SUPERFLY® CORDSETS AND PIGTAILS



Overmolded threaded plug and receptacle



Threaded pigtail plug and receptacle



Quick-disconnect overmolded cordset



Quick-disconnect pigtail plug and jam nut receptacle

- IP67 immersion rated
- High-reliability contacts: 5 Amp, 3 Amp, and 1 Amp
- High shock and vibration
- Robust EMI shielding

- Designed for high speed data applications
- Pre-wired, epoxy-sealed cordsets
- Straight and 90° PC tail receptacles

- 27 Contact arrangements
- Front or rear panel mounting
- Aluminum or stainless steel
- Accepts #22 to #32 AWG wire

### CONTACT ARRANGEMENTS

Series 88 SuperFly connectors are available in 27 contact arrangements with 1 Amp, 3 Amp, 5 Amp contacts, and mixed-contact hybrid arrangements

1 AMP						
B7N (7) 1A	C10N (10) 1A	E19N (19) 1A	F22N (22) 1A	G31N (31) 1A	H37N (37) 1A	J44N (44) 1A

3 AMP					
D3M (3) 3A	E4M (4) 3A	F7M (7) 3A	G10M (10) 3A	K19M (19) 3A	L22M (22) 3A

COMBO 1 AMP & 5 AMP			
D2W2N (2) 1A, (2) 5A	F4W4N (4) 1A, (4) 5A	H6W14N (14) 1A, (6) 5A	J7W19N (19) 1A, (7) 5A

5 AMP CONTACTS			
E3W (3) 5A	F4W (4) 5A	G7W (7) 5A	H10W (10) 5A

COMBO 1 AMP & 3 AMP					
C2M2N (2) 1A, (2) 3A	E4M4N (4) 1A, (4) 3A	F4M8N (8) 1A, (4) 3A	G6M10N (10) 1A, (6) 3A	G6M12N (12) 1A, (6) 3A	K13M19N (19) 1A, (13) 3A




MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS

# SUPERFLY DATALINK



The Nano miniature Shielded Octaxial  
Interconnect for High-Speed Datalink Protocols



High speed, harsh environment SuperFly® Datalink connectors—shielded for 10Gb Ethernet, SuperSpeed USB, HDMI, SATA, and DisplayPort protocols—deliver outstanding signal integrity and save significant size and weight compared to Quadrx solutions.

## PANEL MOUNT CONNECTOR



Panel mount SuperFly Datalink receptacles feature straight or right angle printed circuit board terminals. SuperFly Datalink board mount jacks are epoxy-sealed and are compatible with conformal coatings.



Quick Disconnect



Threaded Coupling



Straight PC Tails



Right Angle PC Tails

# SERIES 882 SuperFly® Datalink



The high-speed nano miniature connector  
for harsh environment defense applications


## SUPERFLY DATALINK

The High-Speed Ultraminiature  
Connector for Harsh  
Environments




- Ultra-small size
- Shielded Octaxial contacts
- Combo arrangement for HDMI 2.0 and DisplayPort 1.2
- 40Gb Ethernet, SATA and SuperSpeed USB
- Up to 10 Gbps per pair
- PCB or cable termination
- Threaded or Quick-disconnect
- Environmentally protected
- Aerospace-grade performance
- Panel-mount connectors fully-sealed for compatibility with conformal coatings used in board assembly

### PUSH-PULL QUICK-DISCONNECT



Push-pull SuperFly Datalink receptacle connectors feature a canted coil spring for secure mating and excellent EMI protection. A fluorosilicone O-ring provides watertight sealing when mated.

### THREADED-COUPLING CABLE CONNECTOR



Cable connectors feature gold-plated crimp contacts, precision insulators, integral backshell, sealing grommet, and machined shells. Cable connectors are available as unassembled kits or ready-to-use factory-terminated cordsets.



## Glenair Signature MIL-DTL-32139 type Nano miniature circular connectors



Glenair Nano Circular—the smallest and lightest harsh-environment connector in the business. From left to right: D38999 Series III, Mighty Mouse Series 805, Glenair SuperFly, and Nanominiature Series 89 Nano Circular—all with similar pin count

The M32139 Nano circular is the smallest and lightest harsh-environment connector in the business. 1 Amp contacts are set on .025" centers and terminated to 30 AWG wire or PCB tails. Glenair supplies both breakaway and threaded mating configurations with optimal size and weight reduction (SWaP).

- Push-pull and threaded mating
- Metal shell: aluminum or stainless steel
- High vibration and shock gold alloy TwistPin contact system
- Prewired pigtails and PCB thru-hole
- Straight and right-angle thru-hole PCB versions

### THE NANO TWISTPIN ADVANTAGE



Transverse cross-section of a TwistPin contact crimped to solid wire



- Gas-tight crimp joint
- Better shock and vibration performance
- Corrosion proof contact alloy



Optimal SWaP for tactical warfighter applications



High density nano · signature TwistPin contacts · cable and PCB

## PRODUCT SELECTION GUIDE AND PERFORMANCE SPECIFICATIONS

Pre-wired and PCB thru-hole mount circular nano plug and receptacle connectors with threaded or breakaway interfaces. Available receptacle mounting configurations include front panel mount, rear panel mount and inline.

	<b>892-007 Breakaway Plug</b>		<b>892-005 Inline Threaded Receptacle</b>
	<b>892-004 Inline Breakaway Receptacle</b>		<b>892-001 Front Panel Mount Threaded Receptacle</b>
	<b>892-000 Front Panel Mount Breakaway Receptacle</b>		<b>892-003 Rear Panel Mount Threaded Receptacle</b>
	<b>892-002 Rear Panel Mount Breakaway Receptacle</b>		<b>893-009 Rear Panel Mount, Threaded Receptacle with PC Tails</b>
	<b>893-008 Rear Panel Mount, Breakaway Receptacle with PC Tails</b>		<b>893-011 Rear Panel Mount, Threaded Receptacle with Right-Angle PC Tails</b>
	<b>893-010 Rear Panel Mount, Breakaway Receptacle with Right-Angle PC Tails</b>		<b>899-013, 899-014, 899-016 and 899-017 Threaded and Breakaway Circular EMI Covers</b>
	<b>892-006 Threaded Plug</b>		<b>600-189 Spanner Nut Socket drive for rear panel mount circular connectors</b>

SERIES 89 NANO MINIATURE CIRCULAR CONNECTOR PERFORMANCE			
Contact Spacing	.025" (0.64mm) Contact Centers	Contact Resistance	71 Millivolt Drop Maximum
Wire Accommodation	#30-#32 AWG	Shock, Vibration	100g's, 20 g's
Current Rating	1 AMP Max	Durability	200 Mating Cycles
DWV	250 VAC RMS Sea Level	Corrosion Resistance	48 Hours Salt Spray
Insulation Resistance	5000 Megohms Minimum	Mating Force	5 Ounce Max, 0.4 Ounce Min
Operating Temperature	-55° C. to +125° C.		

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS

# HiPer 55116

QPL and high-performance MCOTS 55116  
Audio / Radio Connector Technology



Series 152 HiPer 55116 connectors offer significant performance advantages for modern soldier communication systems

Integrated banding  
porch/shrink boot  
groove

<10 mΩ contact  
resistance

1000 hour+ salt spray  
corrosion-resistant

Integrated EMI  
ground spring

Fully intermateable and interoperable  
with MIL-DTL-55116 connectors

- Intermateable and interoperable with standard MIL-DTL-55116 connectors
- Low contact resistance: Less than 10 milliohms
- Integrated EMI ground spring provides improved 2.5 milliohm shell-to-shell conductivity performance
- IP68 rated sealing in mated and unmated condition, prevents water ingress into radio equipment
- 1,000 hour+ salt spray corrosion resistance
- Integrated cable shield termination band porch
- Superior 100 pound cable pull test rating

## GLENAIR DLA QUALIFIED SERIES 151 STANDARD MIL-DTL-55116 AUDIO CONNECTORS




151-001 MIL-DTL-55116 QPL  
audio plug with wire strain relief



151-002 MIL-DTL-55116 QPL  
audio plug/overmold adapter



151-003 MIL-DTL-55116 QPL  
radio-mount jam nut receptacle



151-004 MIL-DTL-55116 QPL  
in-line receptacle, strain relief



# SERIES 152 INTERMATEABLE HiPer 55116 Radio Connectors and Cables



Superior environmental, EMC, and durability performance

## SERIES 152 HIPER 55116 CONNECTOR SELECTION GUIDE



Audio plug, field serviceable, with wire strain relief and rigid contacts, crimp and solder cup



Overmolded audio plug cordset with wire strain relief



Audio plug with shield termination porch, overmolding adapter and rigid contacts, crimp and solder cup



Overmolded audio plug cordset



In-line receptacle with shield termination porch, overmolding adapter, and non-rigid spring contacts, crimp and solder cup



Overmolded in-line audio receptacle cordset



Radio-mount jam nut audio receptacle with non-rigid spring contacts or PC tails and optional ground pins



Filtered radio-mount jam nut audio receptacle with non-rigid spring contacts, solder cup, or PC tails



Special adapter configurations and protective covers




MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



SuperSeal RJ45 and USB field  
connectors. Now available  
for USB SuperSpeed 3.0



Military-grade, ruggedized field  
connectors that deliver improved  
environmental sealing, EMI/RFI grounding,  
and a broader range of wire termination  
options for RJ45 and USB –  
now available for USB  
SuperSpeed 3.0



Available ruggedized memory stick  
32GB, 64GB, and 128GB versions

- New SuperSpeed USB 3.0 protocol support
- Superior sealing—IP67 unmated—for complete system protection against water, sand and dust
- Highly durable SuperSeal™ insert design, provides enhanced operating temperature, increased life-cycle, and rugged vibration and shock performance
- Crimp, solder-cup, PC tail and cable assemblies

# SuperSpeed USB 3.0 Ruggedized connectors and cables



MIL-DTL-38999 Series III USB / RJ45 field connectors

## NEW SUPERSPEED USB 3.0 RUGGEDIZED FIELD CONNECTORS



## TURNKEY SUPERSPEED USB 3.0 CABLE ASSEMBLIES AND JUMPERS




### Glenair SuperNine USB 3.0 cable jumpers, SuperSeal to standard USB Type A and Micro-B connectors

SuperSeal USB 3.0 connectors are available as turnkey cable jumpers. Rugged field connector styles—including plug, wall mount and jam-nut receptacles—may be cabled with commercial 3.0 connector types including male Type A, female Type A, and male Micro B. Assemblies may be ordered with straight or right angle cable exit. In addition, the USB 3.0 insert may be ordered in horizontal or vertical orientation to provide protection against mis-mating. Maximum overall length is 15 feet.

## SUPPORTED USB 3.0 CONNECTOR TYPES



## USB ORIENTATION OPTIONS





MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Series 970 PowerTrip™  
reduced size and weight  
power connectors for extreme  
environments




## Reduced size and weight power connectors



Lightweight plug with ratcheting coupling nut and LouverBand contacts



Keyed receptacle with superior sealing and EMI shielding



- Fast, easy mating with triple-start ACME thread: 360° turn for full mating
- Reduced size and weight compared to 5015/VG95234 solutions
- LouverBand sockets for improved current ratings and longer life, up to 2000 mating cycles
- Splined backshell interface for improved backshell attachment and EMI shielding
- Ratcheting coupling nut for secure mating
- Operating temperature -65° C to +200° C
- Hermetic and filter options available

The Series 970 PowerTrip™ offers improved performance compared to standard 5015 type power connectors: higher density and lighter weight packaging, rapid mating and demating triple-start threaded coupling, and extremely rugged splined and threaded backshell attachment interface



# SERIES 970 PowerTrip™ Connectors and Cables



The power connector for extreme environments

## SERIES 970 POWERTRIP™ CONNECTOR STYLES



Plug  
970-001



Square Flange  
Receptacles  
970-003



Jam Nut Receptacles  
970-004




Cable Receptacles  
970-005



Feed-Thru Bulkhead  
970-006




Hermetic Feed-Thru  
Bulkhead  
970-007



SERIES 970 POWERTRIP™ SPECIFICATIONS	
Current Rating	Up to 225 A.
Dielectric Withstanding Voltage	2000 VAC
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C. to +200° C.
Shock	300 g.
Vibration	37 g.
Shielding Effectiveness	65 dB minimum from 1GHz to 10GHz.
Durability	2000 mating cycles

## CONTACT RESISTANCE AFTER 1000 MATING CYCLES



## ABOUT THE POWERTRIP CONTACT SYSTEM

Series 970 contacts are precision-machined using high conductivity copper alloy. A stamped and formed spring ("LouverBand") is installed into the socket contact. The spring is made from 6 mil copper alloy. Testing has demonstrated that this contact system outperforms conventional aerospace-grade contact systems. The LouverBand spring provides many points of electrical contact with the mating pin, as opposed to a few "high spots" on a conventional four-finger contact as shown in the figure below. The size #8 PowerTrip socket contact has a total of 18 louvers. The #4 has 27 louvers, and the #1/0 has 42 louvers. The LouverBand design offers lower voltage drop for reduced joule heating. In addition to its electrical advantages, the LouverBand also is mechanically superior to four-finger contacts. The LouverBand spring has consistent, stable normal force, even when subjected to thousands of mating cycles and temperature extremes.



Conventional contact on the left,  
LouverBand contact on the right



LouverBand socket  
contact cutaway

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



DLA, Navy, and TACOM-  
Qualified environmental  
heat-shrink boots and  
molded shapes



For advanced abrasion  
protection, environmental  
sealing, splicing, and wire  
protection

NAVSEA-Qualified  
Heavy-Wall Boot  
5617649



ALSO AVAILABLE: AUTOSHRINK COLD-SHRINK BOOTS

**AUTOSHRINK™**



Autoshrink D  
UV-resistant / LSZH



Autoshrink F  
Advanced fluid resistant



Autoshrink S  
Subsea



Autoshrink T  
High-temperature-tolerant




# ENVIRONMENTAL Heat-Shrink and Autoshrink™ Boots and Molded Shapes



Abrasion protection · environmental sealing · splicing

## COMPLETE RANGE OF ENVIRONMENTAL HEAT-SHRINK BOOTS AND MOLDED SHAPES



### GLENAIR SERIES 77 "FULL NELSON" TACOM APPROVED SHRINK BOOTS

Description	Military Part Number	Glenair Part Number	Raychem Part Number	Hellermann Part Number	Description	Military Part Number	Glenair Part Number	Raychem Part Number	Hellermann Part Number
Heat Shrinkable Low Profile 3-Entry "Y" Transition	12273148-1**	770-009Y*05	381A301-**	492H412-*	Heat Shrinkable Straight Lipped 2-Entry Long Tail Boot	12273147-1**	770-020S*02	202F211-**	313F322-*
	12273148-2**	770-009Y*06	381A302-**	492H413-*		12273147-2**	770-020S*03	202F221-**	313F332-*
	12273148-3**	770-009Y*07-01	381A303-*01	492H414-*01		12273147-3**	770-020S*04	202F232-**	313F343-*
	12273148-4**	770-009Y*08-01	381A304-*01	492H415-*01		12273147-4**	770-020S*05	202F242-**	313F353-*
	12273148-5**	770-009Y*07	381A303-**	—		12273147-5**	770-020S*06	202F253-**	313F364-*
Heat Shrinkable Low Profile 3-Entry "T" Transition	12273162-1**	770-012T*01	301A511-**	412H622-*	Heat Shrinkable 90° Lipped 2-Entry Long Tail Boot	12273147-6**	770-020S*07	202F263-**	313F374-*
	12273162-2**	770-012T*02	301A512-**	412H623-*		12273147-7**	770-020S*08	202F274-**	313F385-*
	12273162-3**	770-012T*03	301A513-**	412H624-*		12273176-1**	770-021A*02	222F211-**	333F322-*
	12273162-4**	770-012T*04	301A514-**	412H625-*		12273176-2**	770-021A*03	222F221-**	333F332-*
	12273163-1**	770-014*09	462A421-**	573H532-*		12273176-3**	770-021A*04	222F232-**	333F343-*
Heat Shrinkable Low Profile 4-Entry 3:1 Transition	12273163-2**	770-014*10	462A422-**	573H533-*	Heat Shrinkable 90° Lipped 2-Entry Long Tail Boot	12273176-4**	770-021A*05	222F242-**	333F353-*
	12273163-3**	770-014*11	462A423-**	573H534-*		12273176-5**	770-021A*06	222F253-**	333F364-*
	12273163-4**	770-014*12	462A424-**	573H535-*		12273176-6**	770-021A*07	222F263-**	333F374-*
	12273164-1**	770-019SB*01	202E334-**	313E445-*		12273176-7**	770-021A*08	222F274-**	333F385-*
	12273164-2**	770-019SB*02	202E344-**	313E455-*	M85049-QUALIFIED BOOTS				
Heat Shrinkable Adapter Shim Boot	12273164-3**	770-019SB*03	202E336-**	313E447-*					
	12273164-4**	770-019SB*04	202E346-**	313E457-*					
Heat Shrinkable Convoluted Strain Relief 2-Entry Boot	12273242-1**	770-022C*01	202C611-**	313C722-9					
	12273242-2**	770-022C*02	202C621-**	313C732-9					
	12273242-3**	770-022C*03	202C632-**	313C743-9					
	12273242-4**	770-022C*04	202C642-**	313C753-9					
	12273242-5**	770-022C*05	202C653-**	313C764-9					
	12273242-6**	—	202G621-**	—					
	12273242-7**	—	202G632-**	—					
	12273242-8**	—	202C642-**	—					
	12273242-9**	—	202C653-**	—					

M85049/140 (straight), /141 (right-angle), and /142 (transitions)

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS

**HighSpeed**

VersaLink™, SpeedMaster™, El Ochito®,  
and other Signature high-speed  
datalink connectors



**SpeedLine**  
High-Speed Protocol Cables

Glenair high-speed datalink  
assemblies are proudly made  
with Signature SpeedLine  
high-speed cable

Glenair Signature high-speed interconnects  
are optimized for all popular datalink protocol  
standards



#### RF / HIGH-SPEED DATALINK CONTACTS



Size #8 differential  
twinax contacts



Size #8  
quadrax contacts

Size #8 spring-loaded  
BMB microwave contacts



Size #12 SMPM type  
spring-loaded coaxial



G-LinkRF  
SMA contact adapter



# SIGNATURE High-Speed Datalink Interconnect Solutions



Up to 28 Gbps

**El  
Ochito**

THE OCTAXIAL SIZE #8 CONTACT FOR GbE/10GbE ETHERNET, USB 3.0, HDMI, AND MORE

Crimp Ferrule

Dielectric Sleeve

Socket Contacts

Contact Organizer

Insulator

Front Insulator

Spline

Alignment Key

Outer Body

**El Ochito®:**  
The high-speed octaxial contact with patented data pair isolation

Discrete contacts for D38999 Series III, Series 806 Mil-Aero, SuperNine®, ARINC 600, and Series 79 for both #24 and #26 gauge cable

Turnkey jumpers with Cat 6A #24 or #26 gauge flexible aerospace cable

Series 79 right-angle PCB connector with El Ochito white (Ethernet), blue (USB 3.0), and red (100 Ohm HDMI, DVI, SATA, and PCI)




Series 882  
SuperFly Datalink  
El Ochito nanominiature

Series 806 Mil-Aero  
high-speed El Ochito  
micro miniature

SuperNine MIL-DTL-38999  
"Better than QPL"  
high-speed El Ochito

Series 792 Micro-Crimp  
precision-machined  
high-speed El Ochito

## GLENAIR SIGNATURE HIGH-SPEED CONNECTOR SERIES



VersaLink micro miniature differential twinax with Signature Series 806, 795, and Micro-D packaging

High-Speed Micro-D  
TwistPin contact  
10+Gb/sec. (example  
insert with four high-  
speed signal pairs)

GMMD modular high-  
speed Micro-D  
RF / 10GbE connector

Speed-Master™ modular  
10G+ Ethernet (shown in  
SuperNine® packaging)

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



The advanced-performance MIL-DTL-38999  
Series I, II, III, and IV type connectors




Wide range of signature PC  
tail standoff designs, all with  
superior sealing and resistance to  
vibration and shock

SuperNine<sup>®</sup> is a "Better-than-QPL" MIL-DTL-38999 Series I, II, III, and IV connector family with outstanding durability, sealing, ease of shield termination, PC tail configurations, environmental and hermetic classes, connector savers, as well as off-the-shelf EMI/EMP filter connectors and more—all with Glenair's legendary service, support, and product availability.

#### SUPERNINE SERIES I AND SERIES II BAYONET-LOCK CONNECTORS



SuperNine  
Series I



SuperNine  
Series II



SuperNine Series I (scoop-proof) and Series II (low-profile) bayonet-lock connectors (available now in Class G space-grade)



## SUPERNINE MIL-DTL-38999 SERIES III QPL COMPOSITE CLASSES J AND M




- DLA-qualified composite classes J (Cad / O.D.) and M (Electroless Nickel)
- QPL and Glenair signature series
- Available integrated banding porch with 50% weight savings
- D38999/26 plug and D38999/20 wall-mount receptacle
- 100% molded composite (not machined) for superior strength and durability
- 30% glass-filled PEEK
- 20% weight savings versus standard metal connector

## ADVANCED-PERFORMANCE SUPERNINE PLUGS AND RECEPTACLES



Anti-decoupling, high vibration  
ratcheting coupling nut IAW Bell Helicopter  
299-100-B29 vibration testing



Glass-to-metal sealed and lightweight  
CODE RED encapsulant sealing  
hermetic-class connectors



SuperNine PowerPlay high-voltage  
connectors with temperature-tolerant  
Crown Ring contacts



High-temperature and cryogenic  
ThermoRex solutions



High-speed El Ochoito Octaxial solutions for  
10Gb Ethernet, USB 3.0 and SATA



High-frequency RF and hybrid  
RF/signal configurations

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



The advanced-performance MIL-DTL-38999  
Series IV breech-lock connector



From vertical launch fire-control, tracking, and multi-target missile systems to rugged industrial applications, Glenair "Better-than-QPL" SuperNine and DLA-qualified D38999 Series IV connectors are the ultimate solution for positive and reliable breech-locking performance.

- QPL manufacturer of MIL-DTL-38999 Series IV Class F, W and G connectors
- "Better-than-QPL" SuperNine Series IV offers advanced performance and features beyond the Mil-spec
- Optimized for SWAMP area applications
- Quick-disconnect 90° breech coupling mechanism
- Visual, audible and tactile full-mate indicators
- Integrated EMI grounding fingers
- -65°C to 200°C operating temperature range



# QPL QUALIFIED AND MCOTS EQUIVALENT MIL-DTL-38999 Series IV, Breech Coupling



Anti-decoupling, vibration and shock resistant  
DLA qualified and Glenair SuperNine derivatives

## SUPERNINE SERIES IV "BETTER-THAN-QPL" FEATURES AND BENEFITS

- Secure breech-lock mating connector meets D38999 shock and vibrate
- Integral banding porch eliminates need for back-end accessories
- Improved plug ground fingers deliver outstanding EMI performance—equal to D38999 Series III
- Glenair Signature Tin-Zinc finish class is RoHS compliant and cadmium compatible
- Precision-machined key/keyway polarization for reliable mismatching protection
- Scoop-proof design prevents pin damage and short circuits
- Fully tooled for all MIL-STD-1560 insert arrangements
- Contact options include size #22D, #20, #16, #12, and High-Speed Twinax, QuadraX, and Octaxial EI Ochito Size #8 plus hybrid arrangements
- 500 mating cycles exceeds MIL-DTL-38999 specification

## 38999 SERIES IV ACCESSORIES



QPL accessories including protective covers and dummy receptacles



Series IV solutions are available in environmental and hermetic class configurations in shell sizes from 11–25 supporting a popular range of MIL-STD-1560 insert arrangements



Glenair's complete Series IV solution includes support for power, signal, and hybrid insert arrangements including shielded coax, #22, #20, #16 and #12 contacts


## "BETTER-THAN-QPL" SUPERNINE SERIES IV CONNECTOR DESIGNS



Sav-Con® connector saver, black zinc-nickel finish



Dual-flange panel-mount feedthrough




Panel-mount receptacle with sealed PC-tails



Plug with wing-lock coupling and EMI ground fingers

## SUPPORTED CRIMP-CONTACT SHELL STYLES




Plug



Wall-Mount Receptacle



Box-Mount Receptacle



Jam-Nut Receptacle



In-Line Receptacle




All diode-equipped  
EMP inserts and planar  
array EMI filter inserts  
produced in-house

## Planar filter array and TVS diode connectors diodes in standard catalog as well as build-to-order configurations

**Table I: Capacitor Array Code /  
Capacitance Range**

Class	Pi - Circuit (pF)	C - Circuit (pF)
X	160,000 - 240,000	80,000 - 120,000
Y	80,000 - 120,000	40,000 - 60,000
Z	60,000 - 90,000	30,000 - 45,000
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300
J	70-120	35-60



Planar filter arrays and TVS diodes may  
also be incorporated into rectangular  
connector packaging such as the  
Micro-D and Series 79 Micro-Crimp  
devices shown here.

- Planar, multilayer ceramic capacitive filters, with and without transient voltage suppression diodes
- Space-grade plating and outgassing processing
- C and Pi electrical configurations
- PC tail, crimp or solder cup termination
- 35 – 240,000 pF capacitance
- Fast and reliable diode burn-in and test services
- Turnkey in-house manufacturing of all filter connector elements and processes



# SPACE-GRADE EMI/EMP Filter connectors



Innovative designs · total vertical integration




Extended-shell  
PC-tail cylindrical filter  
with threaded standoff



Special-purpose  
filter connector cable  
adapter (Sav-Con®)



Custom reduced-length  
sidecar filter connector design



Series 80 Mighty Mouse  
PC-tail filter receptacle



Series 80 Mighty Mouse  
solder-cup filter receptacle  
with integrated banding porch



MIL-DTL-38999 type  
crimp-contact termination  
filter receptacle



MIL-DTL-38999 Series  
III type EMP TVS diode-  
equipped filter connector



MIL-DTL-83723 type filter  
connector, gold-plated for atomic  
oxygen corrosion resistance



Quick-disconnect circular with  
solder-free contact filter array

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Best-of-Class Hermetic  
Seal Connector Design



Resolve gas, moisture, and particle  
ingress problems with  
conventional glass-sealed  
hermetic or advanced  
**CODE RED** lightweight  
encapsulant-sealed  
designs.





#### ALL SOLUTIONS DELIVER

- Superior pressure resistance to 32,000+ PSI
- Higher resistance to extreme operating temperatures to 260°+ C
- Superior mechanical strength
- No material breakdown or aging over time
- Helium leak rate  $<1 \times 10^{-7}$  cc/sec to  $1 \times 10^{-10}$

**CODE RED**

#### LIGHTWEIGHT HERMETIC SEALING

Lightweight hermetic encapsulant sealing solution with  $1 \times 10^{-7}$  leak rate performance. Available today in Mighty Mouse 806 Mil-Aero, M24308/9 D-Sub and D38999/23.



Aluminum shell CODE RED hermetic connectors and copper contacts reduce weight and improve electrical performance compared to heavier-duty glass-to-metal seal hermetic solutions.



# ADVANCED PERFORMANCE Glass-Sealed Hermetic Connectors




Thousands of same-day-availability part numbers

## UNIQUE HERMETIC OFFERINGS AND CATALOG (COTS) SOLUTIONS



Coax, Triax, Quadrix and  
hybrid-contact layouts



Rectangular hermetics including  
Series 28 HiPer-D and Series 79



El Ocho high-speed octaxial contacts  
in a lightweight CODE-RED sealed  
bulkhead feed-thru



Triax hermetic



Hermetic Sav-Con  
feed-thrus and gender  
changers



Dual-flange PC tail  
hermetic



Hermetic with crimp-  
removable contacts



Hermetic bulkhead  
penetrators



Hermetic receptacles with  
integrated band porch

# MIL-AERO/ DEFENSE INTERCONNECT SOLUTIONS

SERIES  
**806**  
MIL-AERO

Series 806 Mil-Aero: Advanced performance, reduced size and weight



Two mating styles available:  
Triple-start stub ACME and  
bayonet-lock

Innovative design meets key performance benchmarks for harsh vibration, shock, and environmental settings—as well as high-altitude, unpressurized aircraft zones with aggressive voltage ratings and altitude immersion standards.

## SIZE AND WEIGHT SAVING SOLUTIONS: CATALOG OR CUSTOM



High-availability catalog solutions plus custom designs such as this unique Quadrax implementation

- Next-generation small form factor aerospace-grade circular connector
- Designed for harsh application environments including SWAMP-zone sensors, flight navigation electronics, and flight deck avionics
- Integrated anti-decoupling technology
- High density 20HD, 22HD, RF, power, and high-speed contact arrangements
- Hermetic and filter versions
- +200°C temperature rating



# Series 806 Mil-Aero Ultraminiature Circular Connectors



For harsh mil-aero applications IAW MIL-DTL-38999

## SERIES 806 MIL-AERO: FEATURES / SPECIFICATIONS

- **Supported wire sizes:**  
#20HD contacts  
20–24 AWG  
#22HD contacts  
22–28AWG
- **Dielectric withstanding voltage**  
#20HD layouts:  
1800 VAC  
#22HD layouts: 1300 VAC
- **Reduced pitch triple-start modified anti-decoupling stub ACME mating threads**
- **“Triple ripple” wire sealing grommet (75,000 ft. rated)**
- **Integral Nano-Band shield termination platform**
- **EMI shielding effectiveness per D38999M para. 4.5.28 (65 dB min. leakage attenuation @ 10GHz)**
- **10,000 amp indirect lightning strike**
- **MIL-S-901 Grade A high impact shock**




## AVAILABLE LIGHTWEIGHT ALUMINUM “CODE RED” HERMETICS

CODE RED is a lightweight encapsulant sealing and assembly process with 50% package-weight savings compared to glass-to-metal seal Kovar/stainless steel solutions. Non-outgassing CODE RED (IAW NASA/ESA) provides durable hermetic sealing with  $1 \times 10^{-7}$  leak rate performance. Gold-plated copper contacts deliver outstanding low-resistance current carrying capacity.




**CODE RED**

## SERIES 806 MIL-AERO PLUG




## SERIES 806 MIL-AERO RECEPTACLE



## SMALLER AND LIGHTER WITH EQUAL D38999 PERFORMANCE?

### High-Density Layouts

Twice as many contacts in a smaller package




### “Top Hat” Insulator

High voltage rating, foolproof alignment



### Triple Ripple Wire Seal

Reliable 75,000 ft. altitude immersion






## Advanced-Performance HiPer-D Connectors: Aerospace-Grade M24308 Intermateable



HiPer-D: the advanced-performance M24308 intermateable with one-piece precision-machined shells and enhanced shielding, sealing, and high temperature and vibration tolerance

- Advanced temperature, vibration and EMC/ electrical performance
- 11 standard and 20 combo insert arrangements
- High temperature epoxy insulators
- Watertight sealing
- Rugged machined one-piece shell


### STANDARD AND HIGH DENSITY HiPer-D® - CUTAWAY





Precision-machined · shielded · sealed

Glenair HiPer-D M24308 D-sub connectors are ideally suited for both high-altitude and exoatmospheric applications including jet aircraft avionic systems and military defense on-board satellite computers. Connectors are supplied with auxiliary grounding fingers, fully-sealed inserts, accommodation for precision-machined backshells, and are fabricated with materials and production processes designed to eliminate the broad range of electrical, mechanical, and environmental failure modes endemic in stamped-and-formed connector packaging.



HIPER-D HIGH-PERFORMANCE D-SUB VS. MIL-STD-24308		
Specification / Feature	M24308	HiPer-D
Temperature	-55°C to +125°C	-65°C to +200°C
Insulator	Thermoplastic	Thermoset Epoxy
Shell	Steel (Brass)	Aluminum (SST)
Voltage	1000 VAC	1000 VAC
Grounding	Dimples in shell (not in Mil-Spec)	Nickel-plated Copper Alloy EMI spring
Environmental	No	Yes
Vibration, sine	20 g	60 g
Vibration, random	N/A	43 g
Shock	50 g	300 g
Bolt-on backshells	No	Yes

## HIPER-D M24308 COMBO-DS FOR POWER, SIGNAL, AND RF APPLICATIONS

- Size #8 power and 50 ohm or 75 ohm RF contacts
- Mixed layouts with #8's and #20's
- 200°C continuous operating temperature
- 20 tooled layouts
- Crimp and PC tail terminations



## HIGH-SPEED HIPER-D HIGH-PERFORMANCE M24308


Crimp contact non-environmental connectors with #8 contacts for high-speed data transmission

- One-piece rugged machined aluminum shell
- Two to five size 8 Coax, Twinax, or Quadrx contacts
- Common ground plane (no insulators)
- Available in straight and right angle PCB versions
- Non scoop-proof solution. For scoop-proof rectangular connector requirements, see Series 792



NEXT-GENERATION  
MICRO  
MINIATURE  
CONNECTORS

**SERIES**  
**791**™ High-density, crimp-contact,  
power and signal connectors  
with precision-machined micro  
miniature packaging



Originally designed for NASA's Orion project, the 791's small size and blind mate capability make it a perfect choice for 2U and 3U electronics modules. Applications include radars, satcom, exoatmospheric vehicles, flight avionics, power distribution units, and satellite instrumentation.




Polarized / keyed shells prevent mis-mating and allow designers to specify identical layouts side-by-side without risk of circuit damage.

- Next-generation small form factor aerospace-grade rectangular connector
- Scoop-proof recessed pin contacts
- 37 arrangements, 12 shell sizes for the ultimate in versatility
- Rugged aluminum alloy dual-lobe shell
- Environmental
- EMI shielded
- Blind mating




**SERIES™** High-speed El Ochito® variants of  
**792** Glenair Signature micro miniature  
crimp-contact rectangular  
connectors



**El Ochito®**

The Series 792 connector brings high-speed data-rate performance to the Glenair Series 79 rectangular family. Size 8 cavities accept standard Quadrax or El Ochito® shielded octaxial contacts, making it a perfect choice for radars, weapons systems, mission computers and displays, communications gear, and more.



- High-speed Ethernet, USB 3.0, HDMI
- Printed circuit board and cable connectors
- Scoop-proof interface
- 12 arrangements, 6 shell sizes for the ultimate in versatility
- Rugged aluminum alloy dual-lobe polarized shells
- Environmentally sealed
- Integrated EMI shielding and grounding
- Blind mating

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS




High-density, solder-free, compliant pin  
board-to-board stackable connectors




HD Stacker: the innovative  
mission-critical board-to-board  
connector with fail-safe signal  
integrity and rugged, reliable  
harsh-environment performance

- High-density .0625" pitch Chevron Contact System: 55% more contacts per connector size
- PCIe 3.0 capable
- Performance up to 10.5 Gbps
- Polarized insulator and hardware options
- Solder free "eye of the needle" compliant tail for press fit installation
- High-temp PPS insulator meets NASA outgassing requirements
- Available wired / flex jumpers
- Available between-board spacers up to 1 inch



Solder-free press-fit  
(compliant pin) board  
mounting



.0625" pitch contact spacing:  
highest available density




Polarized shells and keyed  
guide pin hardware prevent  
mis-mating



High-density, rugged, solder-free compliant pin board-to-board stackable connectors

## HD STACKER™ POSITION AND MATING COMPATIBILITY GUIDE



## QUALIFICATION TESTING / HIGH-SPEED PERFORMANCE

Stacker connectors were qualified in accordance with MIL-DTL-55302G testing for:

- Contact engagement/separation
- Contact retention
- DWV
- Electrical resistance
- Mechanical vibration and shock
- Insulation resistance
- Thermal shock
- Contact resistance
- Humidity

High-frequency electrical performance tests were performed for: Insertion loss, return loss, crosstalk, and time domain performance metrics including impedance and eye pattern. Complete test reports are available at [www.glenair.com/test-reports-and-technical-information](http://www.glenair.com/test-reports-and-technical-information)



MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



MIL-DTL-83513 and  
Glenair Signature  
Micro-D Connectors  
and Splice-Free  
Cable Assemblies



The world leader in Micro-D  
connectors: from COTS  
to custom, backshells to  
hardware, Glenair has it all



TwistPin equipped MIL-DTL-83513 Micro-D connectors and  
cables offer outstanding mating performance, durability, low  
contact resistance, and same-day availability


- High density TwistPin contacts on .050" centers
- Turnkey multibranch and complex cable assemblies
- 9 to 130 contact arrangements
- Single row, multi-row, low profile and high density insert arrangements
- QPL and commercial versions



Splice-free Micro-D and Nano  
cable assemblies

#### The Micro TwistPin Advantage

Seven strands of TwistPin BeCu wire make direct contact with the machined socket, assuring low resistance, plenty of contact wipe, and superior shock and vibration performance.





# MIL-DTL-83513 AND COMMERCIAL Micro-D Connectors



Mission-critical mating performance  
industry-leading selection and availability


## MATERIAL CLASSES AND QUALIFICATIONS




Environmental



Hermetic



EMI / RFI Filter




Space-Grade

## TERMINATION STYLES



Flex



PCB



Pigtail




Solder

## WIRED / CABLED CONFIGURATIONS




Shielded



Uninsulated



Insulated




Back-to-Back

## PCB DESIGNS



Vertical



Horizontal



Surface-Mount



Shrouded

## SPECIAL-PURPOSE DESIGNS




High-Temperature



Sav-Con®



Latching MicroStrip



Combo

# MIL-AERO/ DEFENSE INTERCONNECT SOLUTIONS



MIL-DTL-32139 QPL and Glenair Signature  
Nano miniature connector designs



Turnkey solutions from  
shielded cable assemblies  
to discrete wire-to-board  
interconnects

The M32139 Nano is the smallest and lightest mil-spec connector in the business. 1 Amp contacts are set on .025" centers and terminated to 30 AWG wire or PCB tails. Glenair supplies both standard QPL designs as well as a broader range of signature offerings.

- Single and double row
- Metal shell, aluminum, titanium or stainless steel
- TwistPin contact system
- Gold alloy contact, unplated
- Thru-hole and surface-mount PCB versions

## THE NANO TWISTPIN ADVANTAGE



Transverse cross-section  
of a TwistPin contact crimped  
to solid wire



- Gas-tight crimp joint
- Better shock and vibration performance
- Corrosion proof contact alloy





# SERIES 89 Nano miniature Connectors



Nano high density · single- and dual-row · cable and PCB

SERIES 89 NANO MINIATURE CONNECTOR PERFORMANCE	
Contact Spacing	.025" (0.64mm) Contact Centers
Wire Accommodation	#30-#32 AWG
Current Rating	1 AMP Max
DWV	250 VAC RMS Sea Level
Insulation Resistance	5000 Megohms Minimum
Operating Temperature	-55° C. to +125° C.
Contact Resistance	71 Millivolt Drop Maximum
Shock, Vibration	100g's, 20 g's
Durability	200 Mating Cycles
Corrosion Resistance	48 Hours Salt Spray
Mating Force	5 Ounce Max, 0.4 Ounce Min

## HOW SMALL ARE THEY?



**D-Subminiature Connector**  
25 Contacts  
on 0.109 Inch Spacing



**Micro-D Connector**  
25 Contacts  
on 0.050 Inch Spacing



**Nano Connector**  
25 Contacts  
on 0.025 Inch Spacing




Also available: aerospace-grade Nano circulars


## Nano Circular Connectors and Accessories




## Nano Rectangular Single-Row Connectors and Accessories




## Nano Rectangular Dual-Row Connectors and Accessories




## MIL-DTL-32139 Qualified Connectors and Accessories



## NANO MINIATURE CONTACT ARRANGEMENTS



# MIL-AERO/ DEFENSE INTERCONNECT SOLUTIONS




## Glenair High Density (GHD) and other Aerospace-Grade Fiber Optic Connection Systems



Our extensive portfolio of high-speed, high-datarate fiber optic connection systems for military defense applications includes QPL'd MIL-T-29504 termini for Mil-standard 38999 fiber optic connectors, ARINC 801 fiber optic connectors and qualified termini, NAVSEA-qualified 28876 fiber optic connectors and qualified termini, and Glenair Signature High-Density (GHD).

### DESIGNED FOR

- Low mass
- Dynamic vibration and shock resistance
- Extreme temperature resistance
- Environmentally sealed
- Flammability, toxicity, low-smoke
- Indirect lightning strike
- Ease-of-maintenance
- Uncompromised reliability



GHD's high-density cavity spacing is achieved with an innovative front-release terminus design that incorporates a high-force spring and compression bushing that enables low-loss performance even in high-vibration / high-shock applications.




# AEROSPACE AND DEFENSE Fiber Optic Interconnect Systems




Ruggedized, harsh-environment solutions


## ALSO-AVAILABLE MIL-STANDARD TECHNOLOGY: MT FERRULE FIBER OPTICS



## ALSO-AVAILABLE MIL-STANDARD TECHNOLOGY: MIL-PRF-28876 AND NGCON FIBER OPTICS




## ALSO-AVAILABLE MIL-STANDARD TECHNOLOGY: ULTRA-LOW dB LOSS ARINC 801 FIBER OPTICS




## ALSO-AVAILABLE MIL-STANDARD TECHNOLOGY: TIGHT-TOLERANCE MIL-DTL-38999 SERIES III TYPE



MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



Aerospace backshell and  
accessory designs for  
weight reduction and life-  
of-aircraft durability



Innovative solutions to EWIS  
environmental sealing, wire  
management, strain relief, and EMC  
shield termination Glenair is the go-to  
design partner for innovative  
solutions to electrical wire  
interconnect system  
(EWIS) problems in  
airframe applications.



Composite thermoplastic backshells and strain  
reliefs reduce weight and improve durability.

#### GLENAIR: MASTERS OF THE BACKSHELL UNIVERSE

- High-performance circular connector accessories for every environmental, mechanical and electromagnetic shielding requirements
- Tens of thousands of innovative part numbers in inventory ready for same-day shipment
- Fast turnaround on made-to-order accessories, typically only two to three weeks
- Constant, relentless backshell innovation



# NEW INNOVATIONS IN Connector Backshells and Accessories



Unique, problem-solving backshells and connector accessories for aerospace applications

## HIGH-TEMP, LIGHTWEIGHT COMPOSITE THERMOPLASTIC ACCESSORIES



Split-shell and snap-lock banding backshells

Dummy stowage shorting plugs and receptacles

Piggyback boot band-in-a-can

Drop-in EMI/RFI shield termination configurations

## DROP-IN FOLLOWER FOR DIRECT TERMINATION OF OVERALL OR INDIVIDUAL WIRE SHIELDING



Two drop-in-follower designs, solid and slotted are available for all Swing-Arm styles (A, B, and C).

## SWING-ARM AND SWING-ARM FLEX WITH OPTIONAL INTEGRATED SHIELD SOCK



For fast and reliable EMI/RFI shield termination of individual wire and overall cable shielding

## INNOVATIVE NEW EWIS TECHNOLOGIES



Self-locking protective covers

Split-shell snap-lock rectangular composite backshells

Heat shrink boot / wire routing clamp assembly

Leonardo's ProSeal spring-loaded protective covers

Lightweight SpliceSaver single- and multi-wire series

Lightweight Dummy Contact Sealing Plugs (DCSP)

# MIL-AERO/ DEFENSE INTERCONNECT SOLUTIONS




## Qualified MIL-DTL-28840 Connectors and Accessories: Every Slash Sheet, No Gaps



- All sizes and platings in-stock and ready for immediate shipment
- High density, scoop proof contact arrangements
- Flange mount, box mount, jam-nut and in-line receptacles
- Straight, 45° and 90° strain reliefs and backshell assemblies
- Sav-Con® connector savers and bulkhead feedthrus
- Contact and connector assembly tools

MIL-DTL-28840 qualified connectors and accessories. Splined connector-to-backshell interface is ideally suited for heavy backshells and cables

### QUALIFIED CADMIUM-FREE AND COMPATIBLE TIN-ZINC (TZ) PLATING FOR CLASS CODE L AND M (CLASS T AND TJ) NAVY LAND AND MARITIME APPLICATIONS.



L - Class T: Aluminum, Tin-Zinc Plate over Electroless Nickel, Non-Reflective

- New DLA-qualified replacement for Cadmium
- High conductivity and shielding performance in harsh maritime conditions
- High corrosion resistance
- Compatibility with legacy cadmium-plated connectors and environmental shrink boots
- RoHS-compliant material
- Test reports available upon request



# QUALIFIED MIL-DTL-28840 Connectors and Accessories




With in-stock same-day availability

**MIL-DTL-28840 • FULLY-QUALIFIED • EVERY SLASH SHEET • NO GAPS • IN-STOCK AVAILABILITY**

 <p><b>Contacts</b> M39029/83 pin and /84 socket</p>	 <p><b>Clamps</b> M28840/1 straight M28840/2 90° M28840/3 45°</p>	 <p><b>Conduit</b> M28840/4 Metal-Core</p>
 <p><b>Conduit Fittings</b> M28840/5 Backshell for Metal Core Conduit M28840/6 EMI/RFI Environmental Backshell M28840/25 90° EMI Conduit Adapter M28840/27 45° EMI Conduit Adapter M28840/30 Metal Conduit Coupler, Styles A and B M28840/22 Metal Conduit Bushing M28840/23 "E Nut"</p>	 <p><b>Backshells</b> M28840/8 90° EMI/RFI Environmental M28840/ 45° EMI/RFI Environmental Backshell</p>	 <p><b>Connectors</b> M28840/10 Wall Mount Receptacle Connector M28840/11 In-Line Receptacle Connector M28840/12 Box Mount Receptacle Connector M28840/14 Jam Nut Mount Receptacle Connector M28840/16 Plug Connector</p>
 <p><b>Connector / Backshell Assemblies</b> M28840/17 Plug Connector / Straight Strain Relief M28840/18 Plug Connector with 90° Strain Relief M28840/19 Plug Connector with 45° Strain Relief M28840/20 Recept., Straight EMI/RFI Backshell M28840/21 In-Line Recept., St. EMI/RFI Backshell M28840/26 Plug, with Straight EMI/RFI Backshell M28840/28 90° Adapter Assembly Plug M28840/29 Plug with 45° EMI/RFI Backshell</p>	 <p><b>Protective Covers</b> M28840/13 Protective Receptacle Cover M28840/15 Protective Plug Cover</p>	 <p><b>Tools and Accessories</b> M28840/7 Dummy Stowage Receptacle M28840/24 Mounting Gasket</p>

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



QPL and Glenair  
Signature  
MIL-PRF-28876  
Fiber Optic  
Connection System



Qualified MIL-PRF-28876 fiber optic connectors and MIL-PRF-29504 termini—navy approved, in stock, and ready for immediate shipment



M28876/11 jam nut receptacle



M28876/7 plug with backshell



M28876/2 receptacle with backshell

- Connectors qualified to the complete requirements of MIL-PRF-28876: plugs, wall-mount receptacles, jam-nut receptacles, and in-line receptacles
- Multiple shell sizes and insert arrangements, including 2, 4, 6, 8, 18 and 31 channel layouts
- Backshells in straight, 45° and 90° configurations
- Corrosion-resistant and environmentally sealed
- Qualified MIL-PRF-29504/14 and /15 pin and socket termini and /03 dummy terminus
- Same-day availability



# QPL AND COMMERCIAL MIL-PRF-28876



## NAVSEA-qualified fiber optic connection system

CONNECTOR/BACKSHELL TYPES			
Connector Type	Backshell Type	MIL-Spec	Commercial Connector Type Code
Wall Mount Receptacle	None	M28876/1	03
	Straight	M28876/2	13
	45°	M28876/3	23
	90°	M28876/4	33
In-Line Receptacle	Straight	M28876/5	15
Plug	None	M28876/6	06
	Straight	M28876/7	16
	45°	M28876/8	26
	90°	M28876/9	36
Jam Nut Receptacle	None	M28876/11	04
	Straight	M28876/12	14
	45°	M28876/13	24
	90°	M28876/14	34




Qualified QPL-29504  
pin and socket termini

TEST DESCRIPTION	PERFORMANCE REQUIREMENTS/ SPECIFICATIONS
Optical Insertion Loss, Multimode	-0.3 dB Typical (62.5/125)
Optical Insertion Loss, Singlemode	-0.3 dB Typical (9/125)
Optical Back Reflection, Singlemode	Better than -40 dB - PC Polish • Better than -50 dB - Enhanced PC Polish
Operating Temperature	-28°C to +65°C (MIL-Spec Epoxy and Cable) -55°C to +125°C (alternative Epoxy and Cable)
Temperature (Thermal) Shock	-40°C to +70°C, 5 Cycles
Temperature Cycling	-28°C to +65°C, 5 Cycles
Temperature/Humidity Cycling	-10°C to +65°C, 10 Cycles, 240 hours, 98% RH
Temperature Life Aging	+110°C, 240 hours, Dry Air
Mating Durability	500 cycles
Vibration - Sinusoidal	10 g Peak, 5-500 Hz sin./ 10.2 g RMS, 50-2000 Hz random
Impact	8 Drops from 8 feet
Crush Resistance	281 lbs, 7 Cycles
Cable Pull Out Force - Termini	Termini: 22 lbs min for 1 minute Connector: 162 lbs min for 10 minutes
Fluid Immersion	Turbine Fuel, Isopropyl Alcohol, Hydraulic Fluid, Lubricating Oil, Coolant, Tap- and seawater, 24 hrs
Water Pressure	32 feet for 48 hours at +10°C to +35°C
Mechanical Shock (High Impact)	MIL-S-901, Grade A, Type B, Class I
Corrosion Resistance (Salt Spray)	500 hours
Sand and Dust	12 hours
Flammability	0.75 inch flame for 10 sec. mated, 1.50 inch flame for 60 sec. unmated
*Performance Specifications/Requirements based on the use of MIL-PRF-24792 Epoxy and MIL-PRF-85045 Simplex and Breakout Shipboard Optical Fiber.	

QUALIFIED FIBER OPTIC TERMINI			
Type	Military Part Number	A Dia (Microns)	Typical Fiber Type
Pin Termini	M29504/14-4131C	126.0	Multi Mode
	M29504/14-4132C	127.0	Multi Mode
	M29504/14-4135C	142.0	Multi Mode
Socket Termini	M29504/15-4171C	126.0	Multi Mode
	M29504/15-4172C	127.0	Multi Mode
	M29504/15-4175C	142.0	Multi Mode
Dummy Terminus	M29504/03-4038		
Crimp sleeve is supplied with terminus assembly and may be ordered separately (see Table II). For terminus less crimp sleeve, omit <b>C</b> from end of part number. Consult factory for additional sizes.			

Terminated and tested  
MIL-PRF-28876 fiber optic  
cable assembly



MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



## SeaKing™ 700 Dry-Mate Underwater Connectors and Mil-Qualified / MCOTS Cable Assemblies



Mil-qualified high-pressure,  
high-speed overmolded  
cable assembly



Discrete connectors,  
overmolded cables, and PBOF  
assemblies available

SeaKing 700 is an innovative underwater connector series that eliminates a broad range of mechanical design weaknesses found in many of today's high-pressure subsea connector families. From its double O-ring seals and retractable engaging nut, to its multi-keyed mating interface, the SeaKing underwater connector represents a far more reliable approach to subsea power and signal connectivity.


- High density, small form-factor connector
- Dual O-ring seals ensure high-pressure performance for every leak path
- Signal, power, RF, and optical insert arrangements
- Stainless steel with anti-galling marine bronze engaging nut or cathodic delamination-free PEEK
- Full-mate inspection ports
- Easy O-ring replacement
- Key and keyway polarization




# 10K PSI / 700 BAR SeaKing™ High-Pressure Subsea Connectors



Electrical · Optical · Power · Turnkey Cables



## SEAKING PEEK, SEAKING POWER, AND SEAKING FIBER OPTIC CONFIGURATIONS



# MIL-AERO/ DEFENSE INTERCONNECT SOLUTIONS

## ARMORLITE™

### Braided Ground Straps: Glenair Signature and QPL Solutions for ESD, Lightning Strike, and Electrical Power Applications

From ultra low-resistance ESD bonds to large form-factor power distribution busbars—Glenair does it all


Glenair flexible braided straps are critical components in harsh sea, air, and space environments. They are used to establish reliable ground path connections, dissipate lightning strike energy, and prevent the build-up of electrostatic discharge. Special large form-factor straps are also employed in busbar applications for electrical power distribution up to 1000 Amps.

Glenair supplies a complete range of lugged flexible braided bonding, grounding, and power distribution solutions with lightweight ArmorLite microfilament material as well as low-resistance plated copper. In addition to high-availability catalog designs, we are also able to supply custom solutions in virtually any form factor, wire gauge, amperage, resistance, and mounting-lug configuration. Straps may also be supplied with and without insulation jacketing in wire rope (jumper) and flat profiles. Mil-qualified (QPL) straps are available for both topside and submarine applications.



#### PRODUCT LINE OFFERINGS

- Durable, low-resistance ground straps with highly conductive or dissipative performance
- Lightweight, low-resistance flexible bond straps for ESD dissipation
- Heavy-duty variants for low-voltage, high-current power distribution busbar applications
- Glenair signature and qualified military standard designs



Ultra flexible, lightweight ArmorLite microfilament ground straps and bonds

Flat and round cross-section straps, plus wire rope jumpers

High current AC and DC flexible busbars and shunts

Harsh-environment insulation and jacketing available for enhanced user safety and short-circuit prevention



SERIES 107


# Braided Ground Straps




Mil-spec and Glenair Signature lightweight designs

107-086 GROUND STRAPS FOR SUBMARINE APPLICATIONS

- Materials and design in accordance with Commercial Item Description A-A-59569 for grounding bonds
- Low-profile nickel-plated copper lugs with configurable mounting hole size options
- Nickel-plated copper braid material conforms to ASTM B355




M24749 TYPE IV MIL-SPEC AND GLENAIR SIGNATURE “BETTER THAN QPL” CONFIGURATIONS



- Meets the rigorous specifications of MIL-DTL-24749 Rev. C with width, length, and lug configuration options beyond standard mil-spec straps
- Tested to survive 1000 hours salt spray
- Unique Stainless Steel/Nickel hybrid braid
- Lightweight, durable, configurable crimp lugs: square, radiused, straight, single- and double-right-angle versions

VARIABLE LUG / HOLE / STRAP CONFIGURATION OPTIONS AVAILABLE ON ALL STYLES



Choose single-layer straps or dual-layer for strength and electrical performance.



Available black or clear sleeving over strap. Square or radiused lugs and variable hole sizes.



Straight, single right-angle, and dual right-angle configurable lugs.


GROUND CONTROL EARTH BOND SYSTEM



The Ground Control Earth Bonding system is an efficient, easy-to-use method to create an electrical bond between structures and equipment for the secure passage of high intensity current in case of electrical short circuit.

How To Order	
600-120	Hydraulic Setting Tool for 1/4" Earth Bonds
600-123	Hydraulic Setting Tool for 3/8" Earth Bonds
600-124	Hydraulic Setting Tool for M6 Earth Bonds
600-125	Hydraulic Setting Tool for M10 Earth Bonds
The tools feature one hand operation and ram retract mechanism actuated by release trigger. Consult factory for control gauges and earth bond part numbers for each material type and size.	

MIL-AERO/  
DEFENSE  
INTERCONNECT  
SOLUTIONS



US Navy Qualified Helical  
Metal-Core Conduit for  
Above- and Below-Deck  
Shipboard Wire Routing  
Applications



## Improved sealing and shielding: the ultimate in highly flexible, crush-proof EMI/EMP wire protection

- Hermetically sealed, flexible metal-core conduit for shipboard wire interconnect applications
- UV-resistant “BlueJacket” jacketing over Brass, Stainless Steel, or Nickel Iron Alloy conduit
- Turnkey, factory-terminated assemblies for fast-turnaround dockside maintenance cycles
- All materials deliver superior EMC performance as well as crush resistance and environmental sealing compared to legacy systems

*Glenair*  
SIGNATURE SERIES



**Part Number  
750-098**



### *Select for superior crush resistance and corrosion protection*

Highly flexible crush-proof metal conduit in stainless steel with Viton, Neoprene, or Bluejacket protective covering

**Part Number  
750-192**



### *Select for low-frequency EMC protection in and around motors and control equipment*

Nickel-iron conduit material plus shielding and jacketing



# MIL-PRF-24758A NAVSEA-APPROVED Metal-Core Conduit Wire Protection Systems




US Navy Qualified Brass, CRES, and Nickel-Iron, with  
Glenair Signature "BlueJacket" jacketing




- Qualified to MIL-PRF-24758A(SH)
- User-installable and factory terminated configurations
- Innovative fitting design with advanced environmental sealing, EMI shield termination and rotatable coupling nut
- Adapters for all shipboard interfaces—fully compatible with legacy MIL-C-24758 conduit system components


Do it once, do it right with Glenair Signature MIL-PRF-24758A wire protection conduit systems



90°





Single Ended Assembly



Double Ended Assembly

Straight



45°

MIL-PRF-24758A  
Configuration Options:  
Choose from high-  
performance user-  
installable fittings or  
lighter-weight factory  
terminated assemblies



## FITTINGS AND ADAPTERS FOR USER-INSTALLED APPLICATIONS



Composite  
conduit splice  
fitting



Stainless steel  
conduit feed-thru  
fitting



Low-Profile  
RP Plus  
System



Heavy-duty  
environmental  
conduit-to-panel fitting



Heavy-duty  
environmental  
conduit-to-connector fitting

# Glenair Mil-Spec Interconnect Technologies



**Qualified Products:** Glenair is a Mil-Aero connector supplier. Our product quality begins in engineering (the largest team in the high-performance interconnect business) and is realized in our “made in the USA” vertically-integrated manufacturing cells. One of the key ways we ensure both areas are functioning smoothly is to submit designs and manufactured specimens into the military QPL process administered by NAVSEA and the Defense Logistic Agency of the US government. These certification exercises are multi-year activities that test every aspect of an interconnect component’s performance.



MIL-DTL-38999 Series III  
Environmental Connectors



MIL-DTL-38999 Series IV  
Environmental Connectors



MIL-DTL-28840 Shipboard  
Connectors and Accessories



MIL-DTL-38999 Series I, II, III, and IV  
Hermetic Connectors




MIL-DTL-24308  
Hermetic Connectors



MIL-DTL-28876  
Shipboard Fiber Optic



MIL-DTL-83513 Micro-D  
Connectors and Accessories



MIL-DTL-32139 Nanominiature Connectors  
and Accessories



MIL-DTL-29504 Fiber Optic Termini and  
AS39029 Electrical Contacts





MIL-DTL-55116 Radio / Audio Connectors



807 NW Nett Warrior  
Qualified Tactical Connectors



STAR-PAN Power / Data Hubs and  
Tactical Cordsets



M85049 (AS85049) Backshells and  
Connector Accessories



MIL-DTL-83723 Backshells and Connector  
Accessories



M81511 (AS81511) Protective Covers and  
Connector Accessories



M85049/140 TACOM-Approved and Navy-  
Qualified 5617649 Shrink Boots



MIL-PRF-24758 NAVSEA-Qualified Conduit  
and Fittings



M85049 Composite Backshells and Covers  
for MIL-DTL-38999

## GLENAIR'S COMMITMENT TO QUALITY

Glenair is proud of the quality and reliability we build into our broad range of mission-critical interconnect solutions—from discrete connectors to complex cable assemblies and embedded systems. Glenair is the biggest “made in the USA” interconnect supplier in the high-reliability industry, but we also operate factories in the UK, Italy, and Germany to serve the unique requirements of those markets. Glenair’s Worldwide Quality System is ISO 9001 and AS9100 certified and registered. We also hold many discrete product and operations certifications for specialty, high-performance markets including space, nuclear power, and rail. In addition to world-class quality, we are laser-focused on customer service and committed to being the easiest manufacturer in our industry to do business with. Here are just some of our key customer service principles:



- Lightning-fast turnarounds on quotes and special orders
- Worldwide sales and technical support in every major market
- Full-spectrum, “no gap” product lines
- No dollar or quantity minimums
- ISO 9001 and AS9100 certified
- Huge same-day shipment inventory
- Generous NRE, RMA, and sample request policies
- Abundant engineering and technical support
- No attitudinal constraints when it comes to customer convenience and service



**GLENAIR GLENDALE:**  
Complete vertical integration  
of manufacturing resources—  
at home in Southern California  
since 1956




Glenair operates the largest high-reliability interconnect manufacturing operation in the United States, allowing us to fully support our broad range of land, sea, air, and space customers.







Glenair SoCal's most important asset: highly technical staff, fully empowered with all the right facilities and operation resources.







### **SAME-DAY SHIPMENT STOCKING**

Immediate availability for high-demand connectors and tooling.




### **HARNESS ASSEMBLIES**

For Micro-D, Nanominiature, and fiber optic connectors and cable assemblies.



### **IN-HOUSE TESTING CAPABILITIES**

Glenair UK operates an independently accredited BS9000:CECC:IECQ test lab for internal and third-party product development / design verification and connector qualification including pure air standards.



Glenair UK complex integrated system for an exoatmospheric application with custom machined connectors and complex cabling







**GLENAIR UK:**  
Mission-critical connectors  
and assemblies for UK and  
European markets with  
a special focus on micro  
and Nanominiature flexi  
assemblies



## **GLENAIR ITALIA:**

Manufacturing harsh-environment military, nuclear, and aerospace interconnect technologies for power, high-speed Ethernet, and hermetic seal applications.



### **HIGH-CAPACITY CNC MACHINING CENTERS**

Allow Glenair BLQ to provide lightning-fast turnaround on small and custom orders as well as large production runs, all with superior surface finishes and better part quality.



### **ADVANCED HERMETIC SEAL AND CONNECTOR PLATING CAPABILITIES**

Space-compliant gold and nickel plating performed in-house. Hermetic seal connector fabrication with performance levels to  $1 \times 10^{-7}$  helium leak rates.





### TOTAL VERTICAL INTEGRATION

Includes In-house rubber and thermoplastic injection molding.



### IN-HOUSE TEST LAB

With capabilities for both high-voltage as well as high-speed signal product qualification. Credentials include ISO 17025 and others.





## **GLENAIR SALEM:**


Our space systems business unit in Salem, Germany, includes ample production space for precision machining and assembly, 300 m<sup>2</sup> ISO 8 and ISO 6 clean rooms, an ISO 5 flow chamber (certified to ESD Standard 61340-5-1), with accommodation for large mock-up and integration projects.






## CLEAN ROOM ASSEMBLY

**With both environmental filtering and electrostatic discharge protection.**




## SPACE-GRADE HARNESS FABRICATION AND INTEGRATION

**In-house or at customer facility.**



## ELECTRO-MECHANICAL

**Fabrication of space-grade interconnect technologies including HDRM (release nut) mechanisms.**



# MISSION-CRITICAL INTERCONNECT SOLUTIONS



**3D Parts  
Models**

**3dparts.glenair.com**



## Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912

sales@glenair.com • **www.glenair.com**

### Glenair East

20 Sterling Drive  
Wallingford, CT  
06492

Telephone:

203-741-1115

Fax:

203-741-0053

sales@glenair.com

### Glenair UK Ltd

40 Lower Oakham Way  
Oakham Business Park  
Mansfield, Notts  
NG18 5BY England

Telephone:

+44-1623-638100

sales@glenair.co.uk

### Glenair Microway Systems

7000 North Lawndale Avenue  
Lincolnwood, IL  
60712

Telephone:

847-679-8833

Fax:

847-679-8849

### Glenair Nordic AB

Gustav III:s Boulevard 42  
SE-169 27 Solna  
Sweden

Telephone:

+46-8-50550000

sales@glenair.se

### Glenair GmbH

Schaberweg 28  
61348 Bad Homburg  
Germany

Telephone:

06172 / 68 16 0

Fax:

06172 / 68 16 90

info@glenair.de

### Glenair Iberica S.L.

Av. De Manoteras, 24 – 2º  
28050 Madrid  
Spain

Telephone:

+34 915 562 687

sales@glenair.es

### Glenair Italia S.p.A.

Via Del Lavoro, 7  
40057 Quarto Inferiore –  
Granarolo dell'Emilia  
Bologna, Italy

Telephone:

+39-051-782811

Fax:

+39-051-782259

info@glenair.it

### Glenair France SARL

7, Avenue Parmentier  
Immeuble Central Parc #2  
31200 Toulouse  
France

Telephone:

+33-5-34-40-97-40

Fax:

+33-5-61-47-86-10

sales@glenair.fr

### Glenair Korea

6-21Tapsil-ro 58beon-gil  
Giheung-gu, Yongin-si  
Gyeonggi-do  
Republic of Korea

Telephone:

+82-07-5067-2437

Fax:

+82-504-375-4549

sales@glenair.kr

### Glenair Japan

40F, Nagoya Lucent Tower,  
6-1, Ushijima-cho,  
Nishi-ku, Nagoya, 451-6040  
Japan

Telephone:

+81-52-569-2521

Fax:

+81-52-569-2523

sales@glenair.jp